

**Compression Style, Pneumatic**

Compression, Compress-Align®, Poly-Tite, Hi-Duty, Metru-Lok™

**A****Push-to-Connect, Pneumatic**

Prestolok, PrestoWeld , Global Connect

**B****Integrated Fittings**

Right Angle Flow Controls, Metric Right Angle Flow Controls, In-Line Flow Controls, Metric In-Line Flow Controls, Slow Start, Metric Slow Start, Blocking, Metric Blocking, Metric Combination, Metric Pressure Sensor, Metric Pressure Reducing, Metric Silencer

**C****Thermoplastic Fittings and Valves**

TrueSeal™ Thermoplastic Push-In Fittings, Fast &amp; Tite® Thermoplastic Fittings, Par-Barb® Thermoplastic Fittings

**D****Flare Fittings**

45° Flare, Inverted Flare, Access Valves

**E****Adapters**

Pipe, Metric Adapters, ISO Port Adapters, Garden Hose

**F****Barbed Fittings**

Dubl-Barb®, Hose Barbs

**G****Compression Style, Transportation**

NTA®, Transmission Fittings, Air Brake, Air Brake Hose Ends, Vibra-Lok

**H****Push-to-Connect, Transportation**

Prestomatic, PTC, Metric Prestomatic

**I****Cartridges & Manifolds**

SAE Cartridges, Manifolds

**J****Valves**

Ball Valves, Plug Valves, Needle Valves, Truck Valves, Lanyard Valve, Shutoff Cocks, Drain Cocks

**K****Tube Fabricating Equipment**

Cutters, Benders, Flaring Tools, Tool Kits, Swaging Tools, Ratchet Wrenches, Deburring Tools, Sawing Vise

**L****Accessories**

Bins, Bags, Copper Tubing

**M****General Technical****N****Numerical Index**

Numerical Index, Parker Safety Guide, Offer of Sale

**O**

<b>Compression Style Pneumatic..... A1</b>	<b>Barbed Fittings ..... G1</b>
Compression Fittings..... A5	Dubl-Barb <sup>®</sup> Fittings.....G3
Compress-Align <sup>®</sup> Fittings..... A13	Hose Barb Fittings.....G9
Parker Metru-Lok <sup>™</sup> Fittings..... A20	
Poly-Tite Fittings ..... A30	<b>Compression Style Transportation ..... H1</b>
Hi-Duty Flareless Tube Fittings..... A42	Air Brake-NTA <sup>®</sup> Fittings..... H4
	Transmission Fittings ..... H11
<b>Push to Connect Pneumatic..... B1</b>	Air Brake-AB Fittings ..... H13
Prestolok Fittings..... B6	Air Brake Hose Ends ..... H18
PrestoWeld Fittings ..... B35	Vibra-Lok Fittings..... H22
Global Connect Fittings ..... B41	
	<b>Push to Connect Transportation ..... I1</b>
<b>Integrated Fittings ..... C1</b>	Prestomatic Air Brake Push-In Fittings.....I4
Right Angle Flow Control Valves..... C4	PTC Composite Push-In Air Brake Fitting .....I14
Metric Right Angle Flow Control Valves..... C8	Metric Prestomatic Air Brake Push-In Fittings .....I18
Slow Start Flow Control Valves..... C14	
Blocking Valves..... C17	<b>Cartridges &amp; Manifolds ..... J1</b>
In-Line Flow Control Valves ..... C21	Prestomatic SAE Encapsulated Cartridges.....J3
Non-Return Valves..... C31	Brass Manifold.....J5
	Presto Manifold.....J6
<b>Thermoplastic Fittings and Valves..... D1</b>	
TrueSeal <sup>™</sup> Thermoplastic Push-In Fittings ..... D4	
Fast & Tite <sup>®</sup> Thermoplastic Fittings..... D22	
Par-Barb <sup>®</sup> Thermoplastic Fittings..... D28	
<b>Flare Fittings..... E1</b>	
SAE 45° Flared Fittings ..... E4	
Inverted Flared Fittings..... E14	
Access Valves..... E18	
<b>Adapters.....F1</b>	
Pipe Fittings..... F4	
Parker Brass Metric Adapters..... F12	
ISO Port Adapters ..... F17	
Garden Hose Fittings..... F20	

<b>Valves</b> .....	<b>K1</b>	<b>Tube Fabricating Equipment</b> .....	<b>L1</b>
Brass Ball Valves Series 500 .....	K4		
Male/Female Ball Valves Series 501 .....	K8	<b>Accessories</b> .....	<b>M1</b>
Brass Panel Mount Ball Valves Series 502.....	K11		
Female/Female Straight Thread Brass Ball Valve Series 506.....	K14	<b>General Technical</b> .....	<b>N1</b>
Solder End Ball Valves Series 509 .....	K16	Manufacturing Techniques.....	N2
Male/Female Straight Thread Ball Valves Series 510 .....	K18	Tubing Compatibility Chart .....	N3
Brass Ball Valves Series 520.....	K21	Tube Line Fabrication Guide for Leak Free Systems.....	N3
Brass Ball Valves Series 533 3-Way Diversion / Series 540 4-Way .....	K23	Thread Specifications.....	N5
90° Ball Valves Series 590/591.....	K25	Flaring Instructions .....	N6
Brass Hose Barb Ball Valves Series 500HB.....	K27	Thread Designations and Standards for Threads Used in Fluid Connectors.....	N7
Brass Ball Valves Series 600 Six Port Diversion ..	K28	Straight Thread Size Comparison Chart.....	N8
Carbon Steel Ball Valves Series 500CS/502CS ...	K30	S.A.E. Part Index .....	N9
Carbon Steel Ball Valves Series 506CS .....	K34	SAE Standards (Current).....	N9
High Pressure Carbon Steel Ball Valves Series 500HP, 506HP, 507HP.....	K36	U.L. Listed Fittings .....	N10
Stainless Steel Ball Valves Series 501SS .....	K40	Flow Curves.....	N11
Stainless Steel Ball Valves Series 502SS .....	K42	Metric Fitting Nomenclature.....	N14
Rotary Actuator Ball Valves Series ACT.....	K45	Flare and Thread Profiles .....	N15
Parker Metric Ball Valves Series BVGC.....	K50	Pressure Conversions .....	N16
Parker Metric Ball Valves Series BVGL .....	K52	English/Metric Conversions .....	N17
Parker Metric Ball Valves Series BVGPLOCK .....	K54	Fluid Compatibility Guide.....	N18
Parker Metric Ball Valves Series MBVG .....	K57		
Micro Ball Valve Series 708 / 709 .....	K59	<b>Numerical Index</b> .....	<b>O1</b>
Mini Ball Valves Series 200/608/609 .....	K64		
Plug Valves Series PV .....	K66	<b>Parker Safety Guide</b> .....	<b>O8</b>
Needle Valves, Truck Valves, Lanyard Valve .....	K68		
Drain Cocks/Ground Plug Shutoff .....	K74	<b>Offer of Sale</b> .....	<b>O10</b>

