



Solenoid Valve Replacement Part Kits and Gaskets Cross Reference Chart

BULLETIN 230-10-5
July 1998
Supersedes July 1996

| USED IN VALVE TYPE | | | TETRASEAL or O-RING NUMBER | INTERNAL PARTS KIT ¹ | | COIL KIT |
|--|--|---|--|--|--------------------|---------------|
| WITHOUT MANUAL LIFT STEM | WITH MANUAL LIFT STEM | OLD TYPE NUMBER | | CURRENT NUMBER | OBSOLETE NUMBER | |
| XPM | — | — | 641-1 | — | — | MKC-1 |
| A3, E3, E5 | — | — | — | — | — | MKC-1 |
| — | — | 10-S, 10-F, 10-P | — | — | — | MKC-2 |
| B6S1, B6F1, B6P1, E6 | MB6S1, MB6F1, MB6P1, ME6 | — | 641-1 | KS-B6/E6 | — | MKC-1 |
| B9S2, B9F2, B9P2, E9 | MB9S2, MB9F2, MB9P2, ME9 | — | 641-3 | KS-B9/E9 | — | MKC-2 |
| OB9S2, OB9F2, OB9P2, OE9 | — | — | 641-3 | KS-OB9/OE9 | — | OMKC-2 |
| B10S2, B10F2, E10 | MB10S2, MB10F2, ME10 | — | Before 1/98 — 641-4 After 12/97 — 14000-3 | KS-B10/E10 | — | MKC-2 |
| OB10S2, OB10F2, OE10 | — | — | Before 6/98 — 641-4 After 5/98 — 14000-3 | KS-OB10/OE10 | — | OMKC-2 |
| B14S2, B14P2, E14 | MB14S2, MB14F2, ME14 | — | Before 1/98 — 641-4 After 12/97 — 14000-3 | KS-B14/E14 | — | MKC-2 |
| OB14S2, OB14P2, OE14 | — | — | Before 4/98 — 641-4 After 3/98 — 14000-3 | KS-OB14/OE14 | — | OMKC-2 |
| DB14S2, DB14P2, DE14 | DMB14S2, DMB14P2, DME14 | — | Before 1/98 — 641-4 After 12/97 — 14000-3 | KS-DB14 | — | MKC-2 |
| B19S2, B19P2, E19 | MB19S2, MB19P2, ME19 | — | Before 1/98 — 641-5 After 12/97 — 14000-4 | KS-B19/E19 | — | MKC-2 |
| OB19S2, OB19P2, OE19 | — | — | Before 4/98 — 641-5 After 3/98 — 14000-4 | KS-OB19/OE19 | — | OMKC-2 |
| DB19S2, DB19P2, DE19 | DMB19S2, DMB19P2, DME19 | — | Before 1/98 — 641-5 After 12/97 — 14000-4 | KS-DB19 | — | MKC-2 |
| B25S2, B25P2, E25 | MB25S2, MB25P2, ME25 | — | 2645-000 | KS-B25/E25 | — | MKC-2 |
| OB25S2, OB25P2, OE25 | — | — | 2645-000 | KS-OB25/OE25 | — | OMKC-2 |
| B33S2, B33P2, E33 | MB33S2, EMB33S2, ME33 | — | 641-3 & 2645-000 ³ | KS-B33/E33 | — | MKC-2 |
| OB33S2, OB33P2, OE33 | — | — | 641-3 & 2645-000 ³ | KS-OB33/OE33 | — | OMKC-2 |
| E34 | ME34 | — | 641-3 & 2645-000 | KS-E34 | — | MKC-2 |
| OE34 | — | — | 641-3 & 2645-000 | KS-OE34 | — | OMKC-2 |
| E42 | ME42 | — | 641-3 & 938-1 | KS-E42 | — | MKC-2 |
| OE42 | — | — | 641-3 & 938-1 | KS-OE42 | — | OMKC-2 |
| XUP | — | — | 641-1 | KS-XUP | — | OMKC-1 |
| XRN | — | — | 641-3 | KS-XRN | — | OMKC-2 |
| XRM | — | — | 641-4 | KS-XRM | — | OMKC-2 |
| XPO | — | — | 641-5 | KS-XPO | — | OMKC-2 |
| — | MA5A3 | 35-P | 1328-22 & (2) 106-004 | KS-MA5 | KS-35 | KC-3 or HKC-3 |
| A17S3, A17P3 | MA17S3, MA17P3, MA17A3 | 43-S, 43-P, 83-P | 1328-22 & (2) 106-003 | KS-A17 ² , KS-MA17 ² | KS-43, KS-83 | KC-3 or HKC-3 |
| DA17S3, DA17P3 | DMA17S3, DMA17P3 DMA17A3 | 43-S, 43-P, 83-P | 1328-22 | KS-DA17 | KS-4303, KS-8303 | KC-3 or HKC-3 |
| B32, B32P3, C32S3 | MA32S3, MA32P3, MB32S3 MB32P3, MC32S3 | 90-P, 90-S, 9001-S 9001-P, 9005-S | 530 & (2) 546 | KS-MA32 | KS-90 | KC-3 or HKC-3 |
| DB32S3, DB32P3, DC32S3 | DMA32S3, DMA32P3, DMB32S3, DMB32P3, DMC32S3 | 9002, 9002-P, 9003-S, 9003-P, 9006-S | 530 & (2) 546 | KS-DMA-32 | KS-9002 | KC-3 or HKC-3 |
| B42, EB42 | MA42S3, MA42P3, MB42S3 | 100 | 938-1 & (2) 929 | KS-MA42 | KS-100 | KC-3 or HKC-3 |
| — | MA50S3, MA50P3 | 110 | 883 & (2) 894 | KS-MA50 | KS-110 | KC-3 or HKC-3 |
| W3P1 | — | — | 1328-14 | KS-W3 | — | MKC-1 |
| RW3P1 | — | — | 1328-14 | KS-RW3 | — | MKC-1 |
| W6P1 | — | — | 641-1 | KS-W6 | — | MKC-1 |
| W14P2 | — | — | 641-4 | KS-W14 | — | MKC-2 |
| W19P2 | — | — | 641-5 | KS-W19 | — | MKC-2 |
| W25P2 | — | — | 2645-000 | KS-W25 | — | MKC-2 |
| R183P1, KR183P1 R184P1, KR184P1 | — | — | 638-132 | KS-R18 | — | MKC-1 |
| BR183P1, KBR183P1 BR184P1, KBR184P1 | — | — | 638-132 | KS-BR18 | — | MKC-1 |
| R246P1 | — | — | 638-132 | KS-R24 | — | MKC-1 |
| BR246P1, KBR246P1 | — | — | 638-132 | KS-BR24 | — | MKC-1 |

¹ Internal parts kits showing both an old number and a new number are identical and are interchangeable.

² KS-A17 and KS-MA17A are interchangeable.

³ Also need 621-008 O-RING

3-Way Heat Reclaim, Split Condenser & Hot Gas Defrost Valve Replacement Part Kits and Gaskets Cross Reference Chart

| USED IN VALVE TYPE | TETRASEAL NUMBER | O-RING NUMBER | INTERNAL PARTS KIT | COIL KIT |
|---|------------------|---------------|--------------------|----------|
| | | | CURRENT NUMBER | |
| 8D7B/8D7C 8D9B/8D9C | 2645-000 | 623-128 | KS-8D | MKC-1 |
| 8D7B-SC/8D7C-SC 8D9B-SC/8D9C-SC | 2645-000 | 623-128 | KS-8D-SC | MKC-1 |
| 8D7B-CV 8D9B-CV | 2645-000 | — | — | MKC-1 |
| 12D11B/12D11C 12D13B/12D13C 12D17B/12D17C | 2645-000 | 623-137 | KS-12D | MKC-1 |
| 12D11B-SC/12D11C-SC 12D13B-SC/12D13C-SC 12D17B-SC/12D17C-SC | 2645-000 | 623-137 | KS-12D-SC | MKC-1 |
| 12D11B-CV 12D13B-CV 12D17B-CV | 2645-000 | (2)623-137 | KS-12D-CV | MKC-1 |
| 16D17B/16D17C | — | 1335-235 | KS-16D | MKC-2 |
| 16D17B-SC/16D17C-SC | — | 1335-235 | KS-16D-SC | MKC-2 |
| 16D17B-CV | — | (2)1335-235 | KS-16D-CV | MKC-2 |
| 8D & 12D PILOT | 641-1, 2645-000 | — | KS-8D/12DP | MKC-1 |
| 8D-SC & 12D-SC PILOT | 641-1, 2645-000 | — | KS-8D/12DP-SC | MKC-1 |
| 10G | 2645-000 (2) | — | KS-10G | MKC-1 |
| 10G-B PILOT | 641-1 | — | KS-10GP-B | MKC-1 |
| 10G-C PILOT | 641-1 | — | KS-10GP-C | MKC-1 |
| 16D PILOT | 641-3 | — | KS-16DP | MKC-2 |
| 16D-SC PILOT | 641-3 | — | KS-16DP-SC | MKC-2 |

Solenoid Valve Enclosing Tube Kit Cross Reference Chart

| ENCLOSING TUBE KIT NUMBER | *VALVE TYPE |
|---------------------------|---|
| KE-3 | (R)W3 |
| KE-6 | (M)B6/E6, W6, 10G |
| KE-9 | (M)B9/E9, C(M)B9/C(M)E9 (M)E34, (M)E42, 16D/16D-SC |
| KE-25 | (M)B25/(M)E25, W25 |
| KE-33 | (M)B33/(M)E33 |
| KE-8D/12D | 8D/12D, 8D-SC, 12D-SC |
| KE-MA5/MA17 | MA5A3/MA17A3 |
| KE-MA32 | MA32 |
| KE-MA42 | MA42, EMB42 |
| KE-MA50 | MA50 |
| KE-18/24 | R18, KR18, KBR18, R24 KR24, KBR24 |

*Enclosing tube kit includes:

- Enclosing Tube
- Coil Housing Screw
- Tetraseal or O-Ring

Coil Kits for Obsolete Solenoid Valves

| OLD TYPE NUMBER | COIL KIT |
|--|-----------------|
| W24P3 | KC-3 or HKC-3 |
| A6S1, A6F1,A6P1 | MKC-1 |
| A9S2, A9F2,A9P2 | MKC-2 |
| A10S2, A10F2 | MKC-2 |
| A14S2, A14P2 | MKC-2 |
| 12-S, 12-F, 12-P | KC-12 or HKC-12 |
| 1210S, 1210F, 1210P | KC-12 or HKC-12 |
| 1240S, 1240F, 1240P | KC-12 or HKC-12 |
| 14-S, 14-F, 14-P | MKC-2 |
| 20-S | KC-12 or HKC-12 |
| 73-S, 73-P | KC-12 or HKC-12 |
| 7303-S, 7303-P | KC-12 or HKC-12 |
| A24S3, A24P3 | KC-3 or HKC-3 |
| DA24S3, DA24P3 | KC-3 or HKC-3 |
| W7P1 | MKC-2 |
| 4303-S, 4303-P, 8303-P 4306-P, 4308-P | KC-3 or HKC-3 |

