



















Pneumatic Quick Coupling Interchange Guide

Six Common Pneumatic Profiles and their Connecting Couplers



Pneumatic Quick Coupling Interchange Style	Connects with Parker Coupler	Sleeve Type	Series Image	Features/Options
	20 Series	Manual		<ul style="list-style-type: none"> • Grip ring sleeve option • Sleeve lock option
	30 Series	Push to Connect		<ul style="list-style-type: none"> • Grip ring sleeve
	HF Series	Push to Connect		<ul style="list-style-type: none"> • Heavy duty option
	Tool-Mate PBH (std) PBS (exhaust)	Push to Connect		<ul style="list-style-type: none"> • Non-marring • Exhaust with sleeve lock version
	E-z-mate	Push to Connect		<ul style="list-style-type: none"> • Exhaust with sleeve lock

Pneumatic Quick Coupling Interchange Style	Connects with Parker Coupler	Sleeve Type	Series Image	Features/ Options
Tru-Flate Automotive industry 	10 Series	Manual Sleeve		<ul style="list-style-type: none"> • Grip ring option • Sleeve lock option
ARO 210 Textile/furniture/carpet industry 	50 Series	Manual Sleeve		<ul style="list-style-type: none"> • Sleeve lock option
	HA Series	Push to Connect		<ul style="list-style-type: none"> • Sleeve lock option
Lincoln (long stem) Older lubrication lines 	70 Series	Manual Sleeve		<ul style="list-style-type: none"> • Sleeve lock option
European High Flow Higher flow in smaller size Breathing air lines 	RF Series	Push to Connect		<ul style="list-style-type: none"> • High flow • European interchange
	Tool-Mate PER (std) PES (exhaust)	Push to Connect		<ul style="list-style-type: none"> • Non-marring • Exhaust with sleeve lock version
Schrader Twist-Lock Breathing air lines 	TL Series	Push to Connect		<ul style="list-style-type: none"> • Sleeve lock