



- ◆ An Eco-Friendly, non-asphalt based product
- ◆ Hot or Cold Applications
- ◆ Temperature range is 325°F to -20°F
- ◆ Stops dripping caused by condensation
- ◆ Adheres to most clean, dry surfaces
- ◆ Self Adhering to itself for multiple layers
- ◆ Will NOT Crack or DRY out

Parker's Premium Hi-Temp Cork Tape may be used for either hot or cold temperature applications within its continuous duty service temperature range. It can be used on pipes, tubes, or other surfaces in commercial or residential buildings, A/C units, refrigerated units, or similar types of applications.



Made in the USA