

Lightraulics® Hollow Piston Roundline Cylinders

Dimensions - Standard Version

	Passage	Stroke	A	B	C	D	E	F
100t	83	150	83	124	165	208	357	370
	83	200	83	124	165	208	357	420
125t	90	150	90	144	190	237	386	370
	90	180	90	144	190	237	386	400
	90	250	90	144	190	237	386	470
140t	105	150	105	149	200	251	401	374
	105	250	105	149	200	251	401	474
180t	110	150	110	168	225	276	426	384
	110	250	110	168	225	276	426	484
270t	130	150	130	208	270	335	485	403
	130	250	130	208	270	335	485	503
	130	300	130	208	270	335	485	553
370t	145	150	145	238	310	385	535	403
	145	250	145	238	310	385	535	503
430t	110	150	110	238	310	385	535	403
495t	140	150	140	258	340	425	576	403
500t	200	300	200	303	380	489	640	571
	200	350	200	303	380	489	640	621

All dimensions are in millimeters unless otherwise stated. In line with our policy of continuous product improvement, specifications in this catalogue are subject to change without notice. Please enquire for exact dimensions when placing order.

