

**PVC PRESSURE HOSE
AIR / WATER**



HSY SAFETY YELLOW

Safety Yellow is a high quality air/water hose that is suitable for a variety of applications. This tough flexible product is used in general industry with pneumatic tools, and in general air transfer applications. It is also used in agriculture for water transfer and is suitable for small fire pumps. It can also be used as an above ground air/water transfer hose in coal mines.



FEATURES:

- ◆ Clearly visible yellow cover
- ◆ Excellent flexibility
- ◆ Factory coiled, bagged or plastic wrapped for effective display & storage
- ◆ Special blend of stabilizers provides optimum UV resistance
- ◆ Meets AS/NZS 2554 - Class B
- ◆ Kink resistance
- ◆ Australian Made

ID (mm)	OD (mm)	Working Pressure (psi)	Min Bend Radius (mm)	Weight (kg/mtr)	Coil Lengths (Mtrs)	Part No
6.0	12.0	250psi	65	0.11	20, 100, 300	HSY-006-***
8.0	14.0	250psi	75	0.13	20, 100, 300	HSY-008-***
10.0	17.0	290psi	85	0.19	20, 100, 200	HSY-010-***
12.5	19.0	250psi	100	0.21	20, 100, 200	HSY-012-***
20.0	28.0	230psi	150	0.40	20, 100	HSY-020-***
25.0	33.0	230psi	180	0.51	20, 100	HSY-025-***
32.0	42.0	230psi	220	0.76	20, 40	HSY-032-***
38.0	50.0	230psi	250	1.06	20, 40	HSY-038-***
50.0	63.0	290psi	320	1.51	20, 40	HSY-050-***

ID & OD dimensions are subject to the following tolerances:
6-20mm +/- 0.4mm, 25-32mm +/- 0.6mm, 38-50mm +/- 1.0mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	PVC
Colour:	Yellow cover and Black tube
Ink Branding:	M PARKER (SIZE)MM SAFETY YELLOW AIR/WATER HOSE WP (1.6) MPa AS/NZS 2554/B AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.