

PVC PRESSURE HOSE FOOD & MULTIPURPOSE



NTP PETROL RESISTANT/FOOD CONTACT

The Parker Petrol Resistant/Food Contact Hose is the original translucent dual purpose hose, this product has excellent petrol resistance and a non toxic PVC tube that allows its dual application. It has a distinctive red and gold tracer which is identified in the market by the products many users, who enjoy its flexible and kink resistant performance. Conforms to AS/NZS 2070 for Food Contact requirement. This product can also be used for air transfer applications.



FEATURES:

- ◆ Identifiable Red & Gold tracer
- ◆ Excellent flexibility
- ◆ Petrol resistant
- ◆ Kink resistant
- ◆ Meets AS/NZS 2070
- ◆ Australian made

ID (mm)	OD (mm)	Working Pressure (psi)	Min Bend Radius (mm)	Weight (kg/mtr)	Coil Lengths (Mtrs)	Part No
6.0	12.0	250psi	65	0.11	20, 60, 100, 300	NTP-006-***
8.0	14.0	250psi	75	0.13	20, 50, 100, 300	NTP-008-***
10.0	15.0	250psi	85	0.15	20, 30, 100, 200, 300	NTP-010-***
12.5	19.0	250psi	100	0.19	20, 30, 100, 200	NTP-012-***
16.0	22.0	250psi	130	0.22	20, 100, 150	NTP-016-***
20.0	27.5	250psi	150	0.35	20, 100	NTP-020-***
25.0	34.0	250psi	180	0.55	20, 50, 100	NTP-025-***
32.0	42.0	145psi	220	0.78	20, 30, 40	NTP-032-***
38.0	49.0	145psi	250	0.91	10, 20, 40	NTP-038-***
50.4	63.0	145psi	320	1.36	20, 30, 40	NTP-050-***

ID & OD dimensions are subject to the following tolerances:
6-20mm +/- 0.4mm, 25-32mm +/- 0.6mm, 38-50mm +/- 1.0mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Virgin PVC
Colour:	Clear tube / cover
Ink Branding:	PARKER (SIZE)MM NTP WP 1.7 MPa FOOD CONTACT AS2070/ PETROL RESISTANT AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.