


# CBI2

Male Elbow  
Intru-Lok / NPTF



Y\* – Across wrench flats

TUBE FITTING PART #	END SIZE		T TUBE END UN/UNF-2A	D DRILL (in.)	D1 DRILL (in.)	K (in.)	M (in.)	N (in.)	XX AFTER ASSY (in.)	Y (in.)	Dynamic Pressure (x 1,000 PSI)
	1 (in.)	2 NPTF									-B
2 CBI2	1/8	1/8 - 27	5/16 - 24	0.093	0.188	0.19	0.59	0.69	0.49	5/16	1.5
3 CBI2	3/16	1/8 - 27	3/8 - 24	0.125	0.188	0.23	0.61	0.69	0.49	3/8	1.5
4 CBI2	1/4	1/8 - 27	7/16 - 20	0.203	0.188	0.23	0.63	0.69	0.55	3/8	1.5
4-4 CBI2	1/4	1/4 - 18	7/16 - 20	0.203	0.281	0.23	0.73	0.92	0.75	9/16	1.5
5 CBI2	5/16	1/8 - 27	1/2 - 20	0.234	0.188	0.25	0.66	0.72	0.60	9/16	1.5
5-4 CBI2	5/16	1/4 - 18	1/2 - 20	0.234	0.281	0.25	0.75	0.97	0.75	9/16	1.5
6 CBI2	3/8	1/4 - 18	9/16 - 18	0.282	0.281	0.25	0.78	0.97	0.75	9/16	1.5
6-2 CBI2	3/8	1/8 - 27	9/16 - 18	0.282	0.188	0.25	0.72	0.81	0.65	9/16	1.5
6-6 CBI2	3/8	3/8 - 18	9/16 - 18	0.282	0.406	0.25	0.86	1.00	0.87	3/4	1.5
6-8 CBI2	3/8	1/2 - 14	9/16 - 18	0.282	0.531	0.25	1.00	1.38	0.90	5/8	1.5
8 CBI2	1/2	3/8 - 18	3/4 - 16	0.422	0.406	0.31	0.88	1.00	0.87	3/4	1.5
8-4 CBI2	1/2	1/4 - 18	3/4 - 16	0.422	0.281	0.31	0.88	1.06	0.82	3/4	1.5
8-8 CBI2	1/2	1/2 - 14	3/4 - 16	0.422	0.531	0.31	1.09	1.38	1.01	7/8	1.5

Dimensions and pressures for reference only, subject to change.

