


F4OMX

Male Connector – BSPP
37° Flare / BSPP-ORR



TUBE FITTING PART #	END SIZE		T TUBE END UN/UNF-2A	C4 (mm)	D (mm)	D2 (mm)	L5 (mm)	LL (mm)	Dynamic Pressure (x 1,000 PSI)			
	1								2 BSPP	S	SS	B
	(mm)	(in.)										
4F4OMX	6	1/4	1/8 - 28	7/16 - 20	17	4.4	4.4	28.3	22.5	5.0	5.0	3.3
4-4F4OMX	6	1/4	1/4 - 19	7/16 - 20	19	4.4	4.4	32.2	22.7	5.0	5.0	3.3
4-6F4OMX	6	1/4	3/8 - 19	7/16 - 20	22	4.4	4.4	33.1	23.7	5.0	5.0	3.3
4-8F4OMX	6	1/4	1/2 - 14	7/16 - 20	30	4.4	4.4	38.6	26.0	5.0	5.0	3.3
5-4F4OMX	8	5/16	1/4 - 19	1/2 - 20	19	6.0	6.0	32.2	22.7	5.0	5.0	3.3
5-6F4OMX	8	5/16	3/8 - 19	1/2 - 20	22	6.0	6.0	33.1	33.7	5.0	5.0	3.3
6F4OMX	10	3/8	1/4 - 19	9/16 - 18	19	7.5	7.5	32.5	22.7	5.0	5.0	3.3
6-6F4OMX	10	3/8	3/8 - 19	9/16 - 18	22	7.5	7.5	33.4	23.7	5.0	5.0	3.3
6-8F4OMX	10	3/8	1/2 - 14	9/16 - 18	30	7.5	7.5	38.0	26.0	5.0	5.0	3.3
8-4F4OMX	12	1/2	1/4 - 19	3/4 - 16	19	9.9	7.5	35.0	25.7	5.0	5.0	3.3
8F4OMX	12	1/2	3/8 - 19	3/4 - 16	22	9.9	9.9	35.9	26.7	5.0	5.0	3.3
8-8F4OMX	12	1/2	1/2 - 14	3/4 - 16	30	9.9	9.9	41.4	28.8	5.0	5.0	3.3
8-12F4OMX	12	1/2	3/4 - 14	3/4 - 16	36	9.9	9.9	42.2	29.8	4.0	4.0	2.6
10-6F4OMX	14, 15, 16	5/8	3/8 - 19	7/8 - 14	24	12.3	9.9	39.1	29.8	5.0	5.0	3.3
10F4OMX	14, 15, 16	5/8	1/2 - 14	7/8 - 14	30	12.3	12.3	43.1	31.3	5.0	5.0	3.3
12-8F4OMX	18, 20	3/4	1/2 - 14	1 1/16 - 12	30	15.5	12.3	46.7	34.1	5.0	5.0	3.3
12F4OMX	18, 20	3/4	3/4 - 14	1 1/16 - 12	36	15.5	15.5	47.5	34.9	4.0	3.6	2.3
12-16F4OMX	18, 20	3/4	1 - 11	1 1/16 - 12	46	15.5	15.5	52.6	36.7	4.0	3.6	2.3
16-12F4OMX	25	1	3/4 - 14	1 5/16 - 12	36	21.5	15.5	48.5	35.9	4.0	3.6	2.3
16F4OMX	25	1	1 - 11	1 5/16 - 12	46	21.5	21.5	53.6	37.7	4.0	3.6	2.3
16-20F4OMX	25	1	1 1/4 - 11	1 5/16 - 12	50	21.5	21.5	54.7	39.7	3.6	2.5	1.6
20F4OMX	30, 32	1 1/4	1 1/4 - 11	1 5/8 - 12	50	27.5	27.5	56.0	41.0	3.6	2.5	1.6
24-20F4OMX	38	1 1/2	1 1/4 - 11	1 7/8 - 12	50	33.0	27.5	60.4	44.5	3.0	2.0	1.3
24F4OMX	38	1 1/2	1 1/2 - 11	1 7/8 - 12	55	33.0	33.0	61.1	45.1	3.0	2.0	1.3

Note: If F4OMX is not available, use F42EDMX.

Dimensions and pressures for reference only, subject to change.

