


# WFTX

Male Bulkhead Connector  
37° Flare / NPTF

WFTX-WLN – Body with locknut



W\* – Bulkhead pilot dia. recommended clearance hole +.015 over W dia.

D1\*\* – May exist due to manufacturer's option.

TUBE FITTING PART #	HOSE FITTING PART #	END SIZE		T TUBE END UN/UNF-2A	C HEX (in.)	C2 HEX (in.)	D DRILL (in.)	D1 DRILL (in.)	I1 (in.)	L (in.)	LL AFTER ASSY (in.)	W DIA (in.)	MAX BULKHEAD WALL THICKNESS (in.)	Dynamic Pressure (x 1,000 PSI)		
		1 (in.)	2 NPTF											-S	-SS	-B
4 WFTX	0153-2-4N	1/4	1/8 - 27	7/16 - 20	11/16	11/16	0.172	0.172	1.20	1.88	1.65	0.44	0.38	6.0	6.0	3.3
4-4 WFTX	0153-4-4N	1/4	1/4 - 18	7/16 - 20	11/16	11/16	0.172	0.281	1.20	2.10	1.84	0.44	0.38	6.0	6.0	3.3
6 WFTX	0153-4-6N	3/8	1/4 - 18	9/16 - 18	13/16	13/16	0.297	0.281	1.28	2.18	1.81	0.56	0.44	6.0	6.0	3.3
6-6 WFTX	0153-6-6N	3/8	3/8 - 18	9/16 - 18	13/16	13/16	0.297	0.406	1.28	2.16	1.78	0.56	0.44	6.0	6.0	3.3
6-8 WFTX	0153-8-6N	3/8	1/2 - 14	9/16 - 18	7/8	13/16	0.297	0.531	1.28	2.41	1.95	0.56	0.44	6.0	6.0	3.3
8 WFTX	0153-6-8N	1/2	3/8 - 18	3/4 - 16	1	1	0.391	0.406	1.44	2.34	1.96	0.75	0.44	6.0	6.0	3.3
8-8 WFTX	0153-8-8N	1/2	1/2 - 14	3/4 - 16	1	1	0.391	0.531	1.44	2.60	2.10	0.75	0.44	6.0	6.0	3.3
10 WFTX	0153-8-10N	5/8	1/2 - 14	7/8 - 14	1 1/8	1 1/8	0.484	0.531	1.58	2.74	2.25	0.88	0.44	5.0	5.0	3.3
12 WFTX	0153-12-12N	3/4	3/4 - 14	1 1/16 - 12	1 3/8	1 3/8	0.610	0.719	1.75	2.95	2.47	1.06	0.44	5.0	5.0	2.6
16 WFTX	0153-16-16N	1	1-11 1/2	1 5/16 - 12	1 5/8	1 5/8	0.844	0.938	1.75	3.14	2.57	1.31	0.44	4.5	4.5	2.0

Dimensions and pressures for reference only, subject to change.

