

025-RAC Series

Diesel/Gasoline Fuel Filter



Racor supplies quality filtration products for engines that effectively remove water and harmful contaminants from fuel. Various products are available for engine applications and the 025-RAC Series is an addition to the family.

This product has a die cast aluminum mounting head. The rugged collection bowl is transparent for easy water detection. The replacement element or strainer is easily serviced. Inlet and outlet ports are 1/4" female npt.



Contact Information:

Parker Hannifin Corporation
Racor Division
P.O. Box 3208
3400 Finch Road
Modesto, CA 95353
phone 800 344 3286
209 521 7860
fax 209 529 3278
racor@parker.com

www.parker.com/racor

Product Features:

- Patented design means no inferior elements can fit.
- Heavy duty construction in a compact package.
- Die cast mounting head with anti-rotational numb for single bolt installation.
- Aquabloc® media for superior performance and element life.
- Easy servicing with spin-in element and bowl.
- 15 GPH for diesel and 30 GPH flow rate for gasoline.



ENGINEERING YOUR SUCCESS.

Product Information and Specifications



Diesel or gasoline fuel powered stationary or mobile equipment

- Pressure washer
- Light tower
- Gensets
- Turf
- Construction

Specification	025-RAC-01	025-RAC-02
Maximum Flow Rate	Gasoline - 25 GPH (95 LPH) Diesel - 15 GPH (57 LPH)	Gasoline - 25 GPH (95 LPH)
Inlet/Outlet Port Size	1/4"-18 NPTF	1/4"-18 NPTF
Replacement Elements	S2501	S2502
Micron Rating (nominal)	250	10
Minimum Service Clearance	Below-3.0 in. (7.6 cm)	Below-3.0 in. (7.6 cm)
Depth	2.1 in. (5.3 cm)	2.1 in. (5.3 cm)
Width	2.3 in. (5.8 cm)	2.3 in. (5.8 cm)
Height	4.3 in. (10.9 cm)	4.3 in. (10.9 cm)
Weight (Dry)	0.3 lb (0.14 kg)	0.3 lb (0.14 kg)
Clean Pressure Drop	0.35 PSI (0.02 bar)	0.35 PSI (0.02 bar)
Ambient Temperature Range	-40o to +250oF (-40o to +121oC)	