



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
0.500	1.000	0.276	0.630	LWE-0500-1000-1-1
0.500	1.063	0.276	0.630	LWE-0500-1063-1-1
0.500	1.125	0.276	0.630	LWE-0500-1125-1-1
0.500	1.188	0.276	0.630	LWE-0500-1188-1-1
0.500	1.250	0.276	0.630	LWE-0500-1250-1-1
0.500	1.313	0.276	0.630	LWE-0500-1313-1-1
0.500	1.375	0.276	0.630	LWE-0500-1375-1-1
0.500	1.438	0.276	0.630	LWE-0500-1438-1-1
0.500	1.500	0.276	0.630	LWE-0500-1500-1-1
0.500	1.563	0.276	0.630	LWE-0500-1563-1-1
0.500	1.625	0.276	0.630	LWE-0500-1625-1-1
0.500	1.688	0.276	0.630	LWE-0500-1688-1-1
0.500	1.750	0.276	0.630	LWE-0500-1750-1-1
0.500	1.813	0.276	0.630	LWE-0500-1813-1-1
0.500	1.875	0.276	0.630	LWE-0500-1875-1-1
0.500	1.938	0.276	0.630	LWE-0500-1938-1-1
0.500	2.000	0.276	0.630	LWE-0500-2000-1-1
0.563	1.063	0.276	0.630	LWE-0563-1063-1-1
0.563	1.125	0.276	0.630	LWE-0563-1126-1-1
0.563	1.188	0.276	0.630	LWE-0563-1188-1-1
0.563	1.250	0.276	0.630	LWE-0563-1251-1-1
0.563	1.313	0.276	0.630	LWE-0563-1313-1-1
0.563	1.375	0.276	0.630	LWE-0563-1376-1-1
0.563	1.438	0.276	0.630	LWE-0563-1438-1-1
0.563	1.500	0.276	0.630	LWE-0563-1501-1-1
0.563	1.563	0.276	0.630	LWE-0563-1563-1-1
0.563	1.625	0.276	0.630	LWE-0563-1626-1-1
0.563	1.688	0.276	0.630	LWE-0563-1688-1-1
0.563	1.750	0.276	0.630	LWE-0563-1750-1-1
0.563	1.813	0.276	0.630	LWE-0563-1813-1-1
0.563	1.875	0.276	0.630	LWE-0563-1875-1-1
0.563	1.938	0.276	0.630	LWE-0563-1938-1-1
0.563	2.000	0.276	0.630	LWE-0563-2000-1-1
0.563	2.063	0.276	0.630	LWE-0563-2063-1-1
0.625	1.125	0.276	0.630	LWE-0625-1125-1-1
0.625	1.188	0.276	0.630	LWE-0625-1188-1-1
0.625	1.250	0.276	0.630	LWE-0625-1250-1-1
0.625	1.313	0.276	0.630	LWE-0625-1313-1-1
0.625	1.375	0.276	0.630	LWE-0625-1375-1-1
0.625	1.438	0.276	0.630	LWE-0625-1438-1-1
0.625	1.500	0.276	0.630	LWE-0625-1500-1-1
0.625	1.563	0.276	0.630	LWE-0625-1563-1-1
0.625	1.625	0.276	0.630	LWE-0625-1625-1-1
0.625	1.688	0.276	0.630	LWE-0625-1688-1-1
0.625	1.750	0.276	0.630	LWE-0625-1750-1-1
0.625	1.813	0.276	0.630	LWE-0625-1813-1-1
0.625	1.875	0.276	0.630	LWE-0625-1875-1-1
0.625	1.938	0.276	0.630	LWE-0625-1938-1-1
0.625	2.000	0.276	0.630	LWE-0625-2000-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
0.625	2.063	0.276	0.630	LWE-0625-2063-1-1
0.625	2.125	0.276	0.630	LWE-0625-2125-1-1
0.688	1.188	0.276	0.630	LWE-0688-1188-1-1
0.688	1.250	0.276	0.630	LWE-0688-1250-1-1
0.688	1.313	0.276	0.630	LWE-0688-1313-1-1
0.688	1.375	0.276	0.630	LWE-0688-1375-1-1
0.688	1.438	0.276	0.630	LWE-0688-1438-1-1
0.688	1.500	0.276	0.630	LWE-0688-1500-1-1
0.688	1.563	0.276	0.630	LWE-0688-1563-1-1
0.688	1.625	0.276	0.630	LWE-0688-1625-1-1
0.688	1.688	0.276	0.630	LWE-0688-1688-1-1
0.688	1.750	0.276	0.630	LWE-0688-1750-1-1
0.688	1.813	0.276	0.630	LWE-0688-1813-1-1
0.688	1.875	0.276	0.630	LWE-0688-1875-1-1
0.688	1.938	0.276	0.630	LWE-0688-1938-1-1
0.688	2.000	0.276	0.630	LWE-0688-2000-1-1
0.688	2.063	0.276	0.630	LWE-0688-2063-1-1
0.688	2.125	0.276	0.630	LWE-0688-2125-1-1
0.688	2.188	0.276	0.630	LWE-0688-2188-1-1
0.750	1.250	0.276	0.630	LWE-0750-1250-1-1
0.750	1.313	0.276	0.630	LWE-0750-1313-1-1
0.750	1.375	0.276	0.630	LWE-0750-1375-1-1
0.750	1.438	0.276	0.630	LWE-0750-1438-1-1
0.750	1.500	0.276	0.630	LWE-0750-1500-1-1
0.750	1.563	0.276	0.630	LWE-0750-1563-1-1
0.750	1.625	0.276	0.630	LWE-0750-1625-1-1
0.750	1.688	0.276	0.630	LWE-0750-1688-1-1
0.750	1.750	0.276	0.630	LWE-0750-1750-1-1
0.750	1.813	0.276	0.630	LWE-0750-1813-1-1
0.750	1.875	0.276	0.630	LWE-0750-1875-1-1
0.750	1.938	0.276	0.630	LWE-0750-1938-1-1
0.750	2.000	0.276	0.630	LWE-0750-2000-1-1
0.750	2.063	0.276	0.630	LWE-0750-2063-1-1
0.750	2.125	0.276	0.630	LWE-0750-2125-1-1
0.750	2.188	0.276	0.630	LWE-0750-2188-1-1
0.750	2.250	0.276	0.630	LWE-0750-2250-1-1
0.813	1.313	0.276	0.630	LWE-0813-1313-1-1
0.813	1.375	0.276	0.630	LWE-0813-1375-1-1
0.813	1.438	0.276	0.630	LWE-0813-1438-1-1
0.813	1.500	0.276	0.630	LWE-0813-1500-1-1
0.813	1.525	0.276	0.630	LWE-0813-1525-1-1
0.813	1.563	0.276	0.630	LWE-0813-1563-1-1
0.813	1.688	0.276	0.630	LWE-0813-1688-1-1
0.813	1.750	0.276	0.630	LWE-0813-1750-1-1
0.813	1.813	0.276	0.630	LWE-0813-1813-1-1
0.813	1.875	0.276	0.630	LWE-0813-1875-1-1
0.813	1.938	0.276	0.630	LWE-0813-1938-1-1
0.813	2.000	0.276	0.630	LWE-0813-2000-1-1
0.813	2.063	0.276	0.630	LWE-0813-2063-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
0.813	2.125	0.276	0.630	LWE-0813-2125-1-1
0.813	2.188	0.276	0.630	LWE-0813-2188-1-1
0.813	2.250	0.276	0.630	LWE-0813-2250-1-1
0.813	2.313	0.276	0.630	LWE-0813-2313-1-1
0.875	1.813	0.276	0.630	LWE-0875-1813-1-1
0.875	1.875	0.276	0.630	LWE-0875-1875-1-1
0.875	1.938	0.276	0.630	LWE-0875-1938-1-1
0.875	2.000	0.276	0.630	LWE-0875-2000-1-1
0.875	2.063	0.276	0.630	LWE-0875-2063-1-1
0.875	2.125	0.276	0.630	LWE-0875-2125-1-1
0.875	2.188	0.276	0.630	LWE-0875-2188-1-1
0.938	1.438	0.276	0.630	LWE-0938-1438-1-1
0.938	1.500	0.276	0.630	LWE-0938-1500-1-1
0.938	1.563	0.276	0.630	LWE-0938-1563-1-1
0.938	1.625	0.276	0.630	LWE-0938-1625-1-1
0.938	1.688	0.276	0.630	LWE-0938-1688-1-1
0.938	1.750	0.276	0.630	LWE-0938-1750-1-1
0.938	1.813	0.276	0.630	LWE-0938-1813-1-1
0.938	1.875	0.276	0.630	LWE-0938-1875-1-1
0.938	1.938	0.276	0.630	LWE-0938-1938-1-1
0.938	2.000	0.276	0.630	LWE-0938-2000-1-1
0.938	2.063	0.276	0.630	LWE-0938-2063-1-1
0.938	2.125	0.276	0.630	LWE-0938-2125-1-1
0.938	2.188	0.276	0.630	LWE-0938-2188-1-1
0.938	2.250	0.276	0.630	LWE-0938-2250-1-1
0.938	2.313	0.276	0.630	LWE-0938-2313-1-1
0.938	2.375	0.276	0.630	LWE-0938-2375-1-1
0.938	2.438	0.276	0.630	LWE-0938-2438-1-1
1.000	1.500	0.276	0.630	LWE-1000-1500-1-1
1.000	1.563	0.276	0.630	LWE-1000-1563-1-1
1.000	1.625	0.276	0.630	LWE-1000-1625-1-1
1.000	1.688	0.276	0.630	LWE-1000-1688-1-1
1.000	1.750	0.276	0.630	LWE-1000-1750-1-1
1.000	1.813	0.276	0.630	LWE-1000-1813-1-1
1.000	1.875	0.276	0.630	LWE-1000-1875-1-1
1.000	1.938	0.276	0.630	LWE-1000-1938-1-1
1.000	2.000	0.276	0.630	LWE-1000-2000-1-1
1.000	2.063	0.276	0.630	LWE-1000-2063-1-1
1.000	2.125	0.276	0.630	LWE-1000-2125-1-1
1.000	2.188	0.276	0.630	LWE-1000-2188-1-1
1.000	2.250	0.276	0.630	LWE-1000-2250-1-1
1.000	2.313	0.276	0.630	LWE-1000-2313-1-1
1.000	2.375	0.276	0.630	LWE-1000-2375-1-1
1.000	2.438	0.276	0.630	LWE-1000-2438-1-1
1.000	2.500	0.276	0.630	LWE-1000-2500-1-1
1.063	1.563	0.276	0.630	LWE-1063-1563-1-1
1.063	1.625	0.276	0.630	LWE-1063-1625-1-1
1.063	1.688	0.276	0.630	LWE-1063-1688-1-1
1.063	1.750	0.276	0.630	LWE-1063-1750-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
1.063	1.813	0.276	0.630	LWE-1063-1813-1-1
1.063	1.875	0.276	0.630	LWE-1063-1875-1-1
1.063	1.938	0.276	0.630	LWE-1063-1938-1-1
1.063	2.000	0.276	0.630	LWE-1063-2000-1-1
1.063	2.063	0.276	0.630	LWE-1063-2063-1-1
1.063	2.125	0.276	0.630	LWE-1063-2125-1-1
1.063	2.188	0.276	0.630	LWE-1063-2188-1-1
1.063	2.250	0.276	0.630	LWE-1063-2250-1-1
1.063	2.313	0.276	0.630	LWE-1063-2313-1-1
1.063	2.375	0.276	0.630	LWE-1063-2375-1-1
1.063	2.438	0.276	0.630	LWE-1063-2438-1-1
1.063	2.500	0.276	0.630	LWE-1063-2500-1-1
1.063	2.563	0.276	0.630	LWE-1063-2563-1-1
1.125	1.625	0.276	0.630	LWE-1125-1625-1-1
1.125	1.688	0.276	0.630	LWE-1125-1688-1-1
1.125	1.750	0.276	0.630	LWE-1125-1750-1-1
1.125	1.813	0.276	0.630	LWE-1125-1813-1-1
1.125	1.875	0.276	0.630	LWE-1125-1875-1-1
1.125	1.938	0.276	0.630	LWE-1125-1938-1-1
1.125	2.000	0.276	0.630	LWE-1125-2000-1-1
1.125	2.063	0.276	0.630	LWE-1125-2063-1-1
1.125	2.125	0.276	0.630	LWE-1125-2125-1-1
1.125	2.188	0.276	0.630	LWE-1125-2188-1-1
1.125	2.250	0.276	0.630	LWE-1125-2250-1-1
1.125	2.313	0.276	0.630	LWE-1125-2313-1-1
1.125	2.375	0.276	0.630	LWE-1125-2375-1-1
1.125	2.438	0.276	0.630	LWE-1125-2438-1-1
1.125	2.500	0.276	0.630	LWE-1125-2500-1-1
1.125	2.563	0.276	0.630	LWE-1125-2563-1-1
1.125	2.625	0.276	0.630	LWE-1125-2625-1-1
1.188	1.688	0.276	0.630	LWE-1188-1688-1-1
1.188	1.750	0.276	0.630	LWE-1188-1750-1-1
1.188	1.813	0.276	0.630	LWE-1188-1813-1-1
1.188	1.875	0.276	0.630	LWE-1188-1875-1-1
1.188	1.938	0.276	0.630	LWE-1188-1938-1-1
1.188	2.000	0.276	0.630	LWE-1188-2000-1-1
1.188	2.063	0.276	0.630	LWE-1188-2063-1-1
1.188	2.125	0.276	0.630	LWE-1188-2125-1-1
1.188	2.188	0.276	0.630	LWE-1188-2188-1-1
1.188	2.250	0.276	0.630	LWE-1188-2250-1-1
1.188	2.313	0.276	0.630	LWE-1188-2313-1-1
1.188	2.375	0.276	0.630	LWE-1188-2375-1-1
1.188	2.438	0.276	0.630	LWE-1188-2438-1-1
1.188	2.500	0.276	0.630	LWE-1188-2500-1-1
1.188	2.563	0.276	0.630	LWE-1188-2563-1-1
1.188	2.625	0.276	0.630	LWE-1188-2625-1-1
1.188	2.688	0.276	0.630	LWE-1188-2688-1-1
1.250	1.750	0.276	0.630	LWE-1250-1750-1-1
1.250	1.813	0.276	0.630	LWE-1250-1813-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
1.250	1.875	0.276	0.630	LWE-1250-1875-1-1
1.250	1.938	0.276	0.630	LWE-1250-1938-1-1
1.250	2.000	0.276	0.630	LWE-1250-2000-1-1
1.250	2.063	0.276	0.630	LWE-1250-2063-1-1
1.250	2.125	0.276	0.630	LWE-1250-2125-1-1
1.250	2.188	0.276	0.630	LWE-1250-2188-1-1
1.250	2.250	0.276	0.630	LWE-1250-2250-1-1
1.250	2.313	0.276	0.630	LWE-1250-2313-1-1
1.250	2.375	0.276	0.630	LWE-1250-2375-1-1
1.250	2.500	0.276	0.630	LWE-1250-2500-1-1
1.250	2.625	0.276	0.630	LWE-1250-2625-1-1
1.250	2.750	0.276	0.630	LWE-1250-2750-1-1
1.313	1.813	0.276	0.630	LWE-1313-1813-1-1
1.313	1.875	0.276	0.630	LWE-1313-1875-1-1
1.313	1.938	0.276	0.630	LWE-1313-1938-1-1
1.313	2.000	0.276	0.630	LWE-1313-2000-1-1
1.313	2.063	0.276	0.630	LWE-1313-2063-1-1
1.313	2.125	0.276	0.630	LWE-1313-2125-1-1
1.313	2.188	0.276	0.630	LWE-1313-2188-1-1
1.313	2.250	0.276	0.630	LWE-1313-2250-1-1
1.313	2.313	0.276	0.630	LWE-1313-2313-1-1
1.313	2.375	0.276	0.630	LWE-1313-2375-1-1
1.313	2.438	0.276	0.630	LWE-1313-2438-1-1
1.313	2.500	0.276	0.630	LWE-1313-2500-1-1
1.313	2.563	0.276	0.630	LWE-1313-2563-1-1
1.313	2.625	0.276	0.630	LWE-1313-2625-1-1
1.313	2.688	0.276	0.630	LWE-1313-2688-1-1
1.313	2.750	0.276	0.630	LWE-1313-2750-1-1
1.313	2.813	0.276	0.630	LWE-1313-2813-1-1
1.375	1.875	0.276	0.630	LWE-1375-1875-1-1
1.375	1.938	0.276	0.630	LWE-1375-1938-1-1
1.375	2.000	0.276	0.630	LWE-1375-2000-1-1
1.375	2.063	0.276	0.630	LWE-1375-2063-1-1
1.375	2.125	0.276	0.630	LWE-1375-2125-1-1
1.375	2.250	0.276	0.630	LWE-1375-2250-1-1
1.375	2.375	0.276	0.630	LWE-1375-2375-1-1
1.375	2.500	0.276	0.630	LWE-1375-2500-1-1
1.375	2.625	0.276	0.630	LWE-1375-2625-1-1
1.375	2.750	0.276	0.630	LWE-1375-2750-1-1
1.375	2.813	0.276	0.630	LWE-1375-2813-1-1
1.375	2.875	0.276	0.630	LWE-1375-2875-1-1
1.438	1.938	0.276	0.630	LWE-1438-1938-1-1
1.438	2.000	0.276	0.630	LWE-1438-2000-1-1
1.438	2.063	0.276	0.630	LWE-1438-2063-1-1
1.438	2.125	0.276	0.630	LWE-1438-2125-1-1
1.438	2.188	0.276	0.630	LWE-1438-2188-1-1
1.438	2.250	0.276	0.630	LWE-1438-2250-1-1
1.438	2.313	0.276	0.630	LWE-1438-2313-1-1
1.438	2.375	0.276	0.630	LWE-1438-2375-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
1.438	2.438	0.276	0.630	LWE-1438-2438-1-1
1.438	2.500	0.276	0.630	LWE-1438-2500-1-1
1.438	2.563	0.276	0.630	LWE-1438-2563-1-1
1.438	2.625	0.276	0.630	LWE-1438-2625-1-1
1.438	2.688	0.276	0.630	LWE-1438-2688-1-1
1.438	2.750	0.276	0.630	LWE-1438-2750-1-1
1.438	2.813	0.276	0.630	LWE-1438-2813-1-1
1.438	2.875	0.276	0.630	LWE-1438-2875-1-1
1.438	2.938	0.276	0.630	LWE-1438-2938-1-1
1.500	2.000	0.276	0.630	LWE-1500-2000-1-1
1.500	2.063	0.276	0.630	LWE-1500-2063-1-1
1.500	2.125	0.276	0.630	LWE-1500-2125-1-1
1.500	2.188	0.276	0.630	LWE-1500-2188-1-1
1.500	2.250	0.276	0.630	LWE-1500-2250-1-1
1.500	2.313	0.276	0.630	LWE-1500-2313-1-1
1.500	2.375	0.276	0.630	LWE-1500-2375-1-1
1.500	2.438	0.276	0.630	LWE-1500-2438-1-1
1.500	2.500	0.276	0.630	LWE-1500-2500-1-1
1.500	2.563	0.276	0.630	LWE-1500-2563-1-1
1.500	2.625	0.276	0.630	LWE-1500-2625-1-1
1.500	2.688	0.276	0.630	LWE-1500-2688-1-1
1.500	2.750	0.276	0.630	LWE-1500-2750-1-1
1.500	2.813	0.276	0.630	LWE-1500-2813-1-1
1.500	2.875	0.276	0.630	LWE-1500-2875-1-1
1.500	2.938	0.276	0.630	LWE-1500-2938-1-1
1.500	3.000	0.276	0.630	LWE-1500-3000-1-1
1.563	2.063	0.276	0.630	LWE-1563-2063-1-1
1.563	2.125	0.276	0.630	LWE-1563-2125-1-1
1.563	2.188	0.276	0.630	LWE-1563-2188-1-1
1.563	2.250	0.276	0.630	LWE-1563-2250-1-1
1.563	2.313	0.276	0.630	LWE-1563-2313-1-1
1.563	2.375	0.276	0.630	LWE-1563-2375-1-1
1.563	2.438	0.276	0.630	LWE-1563-2438-1-1
1.563	2.500	0.276	0.630	LWE-1563-2500-1-1
1.563	2.563	0.276	0.630	LWE-1563-2563-1-1
1.563	2.625	0.276	0.630	LWE-1563-2625-1-1
1.563	2.688	0.276	0.630	LWE-1563-2688-1-1
1.563	2.750	0.276	0.630	LWE-1563-2750-1-1
1.563	2.813	0.276	0.630	LWE-1563-2813-1-1
1.563	2.875	0.276	0.630	LWE-1563-2875-1-1
1.563	2.938	0.276	0.630	LWE-1563-2938-1-1
1.563	3.000	0.276	0.630	LWE-1563-3000-1-1
1.563	3.063	0.276	0.630	LWE-1563-3063-1-1
1.625	2.125	0.315	0.669	LWE-1625-2125-1-1
1.625	2.188	0.315	0.669	LWE-1625-2188-1-1
1.625	2.250	0.315	0.669	LWE-1625-2250-1-1
1.625	2.313	0.315	0.669	LWE-1625-2313-1-1
1.625	2.375	0.315	0.669	LWE-1625-2375-1-1
1.625	2.438	0.315	0.669	LWE-1625-2438-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
1.625	2.500	0.315	0.669	LWE-1625-2500-1-1
1.625	2.563	0.315	0.669	LWE-1625-2563-1-1
1.625	2.625	0.315	0.669	LWE-1625-2625-1-1
1.625	2.688	0.315	0.669	LWE-1625-2688-1-1
1.625	2.750	0.315	0.669	LWE-1625-2750-1-1
1.625	2.813	0.315	0.669	LWE-1625-2813-1-1
1.625	2.875	0.315	0.669	LWE-1625-2875-1-1
1.625	2.938	0.315	0.669	LWE-1625-2938-1-1
1.625	3.000	0.315	0.669	LWE-1625-3000-1-1
1.625	3.063	0.315	0.669	LWE-1625-3063-1-1
1.625	3.125	0.315	0.669	LWE-1625-3125-1-1
1.688	2.188	0.315	0.669	LWE-1688-2188-1-1
1.688	2.250	0.315	0.669	LWE-1688-2250-1-1
1.688	2.313	0.315	0.669	LWE-1688-2313-1-1
1.688	2.375	0.315	0.669	LWE-1688-2375-1-1
1.688	2.438	0.315	0.669	LWE-1688-2438-1-1
1.688	2.500	0.315	0.669	LWE-1688-2500-1-1
1.688	2.563	0.315	0.669	LWE-1688-2563-1-1
1.688	2.625	0.315	0.669	LWE-1688-2625-1-1
1.688	2.688	0.315	0.669	LWE-1688-2688-1-1
1.688	2.750	0.315	0.669	LWE-1688-2750-1-1
1.688	2.813	0.315	0.669	LWE-1688-2813-1-1
1.688	2.875	0.315	0.669	LWE-1688-2875-1-1
1.688	2.938	0.315	0.669	LWE-1688-2938-1-1
1.688	3.000	0.315	0.669	LWE-1688-3000-1-1
1.688	3.063	0.315	0.669	LWE-1688-3063-1-1
1.688	3.125	0.315	0.669	LWE-1688-3125-1-1
1.688	3.188	0.315	0.669	LWE-1688-3188-1-1
1.750	2.250	0.315	0.669	LWE-1750-2250-1-1
1.750	2.313	0.315	0.669	LWE-1750-2313-1-1
1.750	2.375	0.315	0.669	LWE-1750-2375-1-1
1.750	2.438	0.315	0.669	LWE-1750-2438-1-1
1.750	2.500	0.315	0.669	LWE-1750-2500-1-1
1.750	2.563	0.315	0.669	LWE-1750-2563-1-1
1.750	2.625	0.315	0.669	LWE-1750-2625-1-1
1.750	2.688	0.315	0.669	LWE-1750-2688-1-1
1.750	2.750	0.315	0.669	LWE-1750-2750-1-1
1.750	2.813	0.315	0.669	LWE-1750-2813-1-1
1.750	2.875	0.315	0.669	LWE-1750-2875-1-1
1.750	2.938	0.315	0.669	LWE-1750-2938-1-1
1.750	3.000	0.315	0.669	LWE-1750-3000-1-1
1.750	3.063	0.315	0.669	LWE-1750-3063-1-1
1.750	3.125	0.315	0.669	LWE-1750-3125-1-1
1.750	3.188	0.315	0.669	LWE-1750-3188-1-1
1.750	3.250	0.315	0.669	LWE-1750-3250-1-1
1.813	2.313	0.315	0.669	LWE-1813-2313-1-1
1.813	2.375	0.315	0.669	LWE-1813-2375-1-1
1.813	2.438	0.315	0.669	LWE-1813-2438-1-1
1.813	2.500	0.315	0.669	LWE-1813-2500-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
1.813	2.563	0.315	0.669	LWE-1813-2563-1-1
1.813	2.625	0.315	0.669	LWE-1813-2625-1-1
1.813	2.688	0.315	0.669	LWE-1813-2688-1-1
1.813	2.750	0.315	0.669	LWE-1813-2750-1-1
1.813	2.813	0.315	0.669	LWE-1813-2813-1-1
1.813	2.875	0.315	0.669	LWE-1813-2875-1-1
1.813	2.938	0.315	0.669	LWE-1813-2938-1-1
1.813	3.000	0.315	0.669	LWE-1813-3000-1-1
1.813	3.063	0.315	0.669	LWE-1813-3063-1-1
1.813	3.125	0.315	0.669	LWE-1813-3125-1-1
1.813	3.188	0.315	0.669	LWE-1813-3188-1-1
1.813	3.250	0.315	0.669	LWE-1813-3250-1-1
1.813	3.313	0.315	0.669	LWE-1813-3313-1-1
1.875	2.375	0.315	0.669	LWE-1875-2375-1-1
1.875	2.438	0.315	0.669	LWE-1875-2438-1-1
1.875	2.500	0.315	0.669	LWE-1875-2500-1-1
1.875	2.563	0.315	0.669	LWE-1875-2563-1-1
1.875	2.625	0.315	0.669	LWE-1875-2625-1-1
1.875	2.688	0.315	0.669	LWE-1875-2688-1-1
1.875	2.750	0.315	0.669	LWE-1875-2750-1-1
1.875	2.813	0.315	0.669	LWE-1875-2813-1-1
1.875	2.875	0.315	0.669	LWE-1875-2875-1-1
1.875	2.938	0.315	0.669	LWE-1875-2938-1-1
1.875	3.000	0.315	0.669	LWE-1875-3000-1-1
1.875	3.063	0.315	0.669	LWE-1875-3063-1-1
1.875	3.125	0.315	0.669	LWE-1875-3125-1-1
1.875	3.188	0.315	0.669	LWE-1875-3188-1-1
1.875	3.250	0.315	0.669	LWE-1875-3250-1-1
1.875	3.313	0.315	0.669	LWE-1875-3313-1-1
1.875	3.375	0.315	0.669	LWE-1875-3375-1-1
1.938	2.438	0.315	0.669	LWE-1938-2438-1-1
1.938	2.500	0.315	0.669	LWE-1938-2500-1-1
1.938	2.563	0.315	0.669	LWE-1938-2563-1-1
1.938	2.625	0.315	0.669	LWE-1938-2625-1-1
1.938	2.688	0.315	0.669	LWE-1938-2688-1-1
1.938	2.750	0.315	0.669	LWE-1938-2750-1-1
1.938	2.813	0.315	0.669	LWE-1938-2813-1-1
1.938	2.875	0.315	0.669	LWE-1938-2875-1-1
1.938	2.938	0.315	0.669	LWE-1938-2938-1-1
1.938	3.000	0.315	0.669	LWE-1938-3000-1-1
1.938	3.063	0.315	0.669	LWE-1938-3063-1-1
1.938	3.125	0.315	0.669	LWE-1938-3125-1-1
1.938	3.188	0.315	0.669	LWE-1938-3188-1-1
1.938	3.250	0.315	0.669	LWE-1938-3250-1-1
1.938	3.313	0.315	0.669	LWE-1938-3313-1-1
1.938	3.375	0.315	0.669	LWE-1938-3375-1-1
1.938	3.438	0.315	0.669	LWE-1938-3438-1-1
2.000	2.500	0.315	0.669	LWE-2000-2500-1-1
2.000	2.563	0.315	0.669	LWE-2000-2563-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
2.000	2.625	0.315	0.669	LWE-2000-2625-1-1
2.000	2.688	0.315	0.669	LWE-2000-2688-1-1
2.000	2.750	0.315	0.669	LWE-2000-2750-1-1
2.000	2.813	0.315	0.669	LWE-2000-2813-1-1
2.000	2.875	0.315	0.669	LWE-2000-2875-1-1
2.000	2.938	0.315	0.669	LWE-2000-2938-1-1
2.000	3.000	0.315	0.669	LWE-2000-3000-1-1
2.000	3.063	0.315	0.669	LWE-2000-3063-1-1
2.000	3.125	0.315	0.669	LWE-2000-3125-1-1
2.000	3.188	0.315	0.669	LWE-2000-3188-1-1
2.000	3.250	0.315	0.669	LWE-2000-3250-1-1
2.000	3.313	0.315	0.669	LWE-2000-3313-1-1
2.000	3.375	0.315	0.669	LWE-2000-3375-1-1
2.000	3.438	0.315	0.669	LWE-2000-3438-1-1
2.000	3.500	0.315	0.669	LWE-2000-3500-1-1
2.063	2.563	0.315	0.669	LWE-2063-2563-1-1
2.063	2.625	0.315	0.669	LWE-2063-2625-1-1
2.063	2.688	0.315	0.669	LWE-2063-2688-1-1
2.063	2.750	0.315	0.669	LWE-2063-2750-1-1
2.063	2.813	0.315	0.669	LWE-2063-2813-1-1
2.063	2.875	0.315	0.669	LWE-2063-2875-1-1
2.063	2.938	0.315	0.669	LWE-2063-2938-1-1
2.063	3.000	0.315	0.669	LWE-2063-3000-1-1
2.063	3.063	0.315	0.669	LWE-2063-3063-1-1
2.063	3.125	0.315	0.669	LWE-2063-3125-1-1
2.063	3.188	0.315	0.669	LWE-2063-3188-1-1
2.063	3.250	0.315	0.669	LWE-2063-3250-1-1
2.063	3.313	0.315	0.669	LWE-2063-3313-1-1
2.063	3.375	0.315	0.669	LWE-2063-3375-1-1
2.063	3.438	0.315	0.669	LWE-2063-3438-1-1
2.063	3.500	0.315	0.669	LWE-2063-3500-1-1
2.063	3.563	0.315	0.669	LWE-2063-3563-1-1
2.125	2.625	0.315	0.669	LWE-2125-2625-1-1
2.125	2.688	0.315	0.669	LWE-2125-2688-1-1
2.125	2.750	0.315	0.669	LWE-2125-2750-1-1
2.125	2.813	0.315	0.669	LWE-2125-2813-1-1
2.125	2.875	0.315	0.669	LWE-2125-2875-1-1
2.125	2.938	0.315	0.669	LWE-2125-2938-1-1
2.125	3.000	0.315	0.669	LWE-2125-3000-1-1
2.125	3.063	0.315	0.669	LWE-2125-3063-1-1
2.125	3.125	0.315	0.669	LWE-2125-3125-1-1
2.125	3.188	0.315	0.669	LWE-2125-3188-1-1
2.125	3.250	0.315	0.669	LWE-2125-3250-1-1
2.125	3.313	0.315	0.669	LWE-2125-3313-1-1
2.125	3.375	0.315	0.669	LWE-2125-3375-1-1
2.125	3.438	0.315	0.669	LWE-2125-3438-1-1
2.125	3.500	0.315	0.669	LWE-2125-3500-1-1
2.125	3.563	0.315	0.669	LWE-2125-3563-1-1
2.125	3.625	0.315	0.669	LWE-2125-3625-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
2.188	2.688	0.315	0.669	LWE-2188-2688-1-1
2.188	2.750	0.315	0.669	LWE-2188-2750-1-1
2.188	2.813	0.315	0.669	LWE-2188-2813-1-1
2.188	2.875	0.315	0.669	LWE-2188-2875-1-1
2.188	2.938	0.315	0.669	LWE-2188-2938-1-1
2.188	3.000	0.315	0.669	LWE-2188-3000-1-1
2.188	3.063	0.315	0.669	LWE-2188-3063-1-1
2.188	3.125	0.315	0.669	LWE-2188-3125-1-1
2.188	3.188	0.315	0.669	LWE-2188-3188-1-1
2.188	3.250	0.315	0.669	LWE-2188-3250-1-1
2.188	3.313	0.315	0.669	LWE-2188-3313-1-1
2.188	3.375	0.315	0.669	LWE-2188-3375-1-1
2.188	3.438	0.315	0.669	LWE-2188-3438-1-1
2.188	3.500	0.315	0.669	LWE-2188-3500-1-1
2.188	3.563	0.315	0.669	LWE-2188-3563-1-1
2.188	3.625	0.315	0.669	LWE-2188-3625-1-1
2.188	3.688	0.315	0.669	LWE-2188-3688-1-1
2.250	2.750	0.315	0.669	LWE-2250-2750-1-1
2.250	2.813	0.315	0.669	LWE-2250-2813-1-1
2.250	2.875	0.315	0.669	LWE-2250-2875-1-1
2.250	2.938	0.315	0.669	LWE-2250-2938-1-1
2.250	3.000	0.315	0.669	LWE-2250-3000-1-1
2.250	3.063	0.315	0.669	LWE-2250-3063-1-1
2.250	3.125	0.315	0.669	LWE-2250-3125-1-1
2.250	3.188	0.315	0.669	LWE-2250-3188-1-1
2.250	3.250	0.315	0.669	LWE-2250-3250-1-1
2.250	3.313	0.315	0.669	LWE-2250-3313-1-1
2.250	3.375	0.315	0.669	LWE-2250-3375-1-1
2.250	3.438	0.315	0.669	LWE-2250-3438-1-1
2.250	3.500	0.315	0.669	LWE-2250-3500-1-1
2.250	3.563	0.315	0.669	LWE-2250-3563-1-1
2.250	3.625	0.315	0.669	LWE-2250-3625-1-1
2.250	3.688	0.315	0.669	LWE-2250-3688-1-1
2.250	3.750	0.315	0.669	LWE-2250-3750-1-1
2.313	2.813	0.315	0.669	LWE-2313-2813-1-1
2.313	2.875	0.315	0.669	LWE-2313-2875-1-1
2.313	2.938	0.315	0.669	LWE-2313-2938-1-1
2.313	3.000	0.315	0.669	LWE-2313-3000-1-1
2.313	3.063	0.315	0.669	LWE-2313-3063-1-1
2.313	3.125	0.315	0.669	LWE-2313-3125-1-1
2.313	3.188	0.315	0.669	LWE-2313-3188-1-1
2.313	3.250	0.315	0.669	LWE-2313-3250-1-1
2.313	3.313	0.315	0.669	LWE-2313-3313-1-1
2.313	3.375	0.315	0.669	LWE-2313-3375-1-1
2.313	3.438	0.315	0.669	LWE-2313-3438-1-1
2.313	3.500	0.315	0.669	LWE-2313-3500-1-1
2.313	3.563	0.315	0.669	LWE-2313-3563-1-1
2.313	3.625	0.315	0.669	LWE-2313-3625-1-1
2.313	3.688	0.315	0.669	LWE-2313-3688-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
2.313	3.750	0.315	0.669	LWE-2313-3750-1-1
2.313	3.813	0.315	0.669	LWE-2313-3813-1-1
2.375	3.063	0.354	0.709	LWE-2375-3063-1-1
2.375	3.125	0.354	0.709	LWE-2375-3125-1-1
2.375	3.188	0.354	0.709	LWE-2375-3188-1-1
2.375	3.250	0.354	0.709	LWE-2375-3250-1-1
2.375	3.313	0.354	0.709	LWE-2375-3313-1-1
2.375	3.375	0.354	0.709	LWE-2375-3375-1-1
2.375	3.438	0.354	0.709	LWE-2375-3438-1-1
2.375	3.500	0.354	0.709	LWE-2375-3500-1-1
2.375	3.563	0.354	0.709	LWE-2375-3563-1-1
2.375	3.625	0.354	0.709	LWE-2375-3625-1-1
2.375	3.688	0.354	0.709	LWE-2375-3688-1-1
2.375	3.750	0.354	0.709	LWE-2375-3750-1-1
2.375	3.813	0.354	0.709	LWE-2375-3813-1-1
2.375	3.875	0.354	0.709	LWE-2375-3875-1-1
2.438	3.125	0.354	0.709	LWE-2438-3125-1-1
2.438	3.188	0.354	0.709	LWE-2438-3188-1-1
2.438	3.250	0.354	0.709	LWE-2438-3250-1-1
2.438	3.313	0.354	0.709	LWE-2438-3313-1-1
2.438	3.375	0.354	0.709	LWE-2438-3375-1-1
2.438	3.438	0.354	0.709	LWE-2438-3438-1-1
2.438	3.500	0.354	0.709	LWE-2438-3500-1-1
2.438	3.563	0.354	0.709	LWE-2438-3563-1-1
2.438	3.625	0.354	0.709	LWE-2438-3625-1-1
2.438	3.688	0.354	0.709	LWE-2438-3688-1-1
2.438	3.750	0.354	0.709	LWE-2438-3750-1-1
2.438	3.813	0.354	0.709	LWE-2438-3813-1-1
2.438	3.875	0.354	0.709	LWE-2438-3875-1-1
2.438	3.938	0.354	0.709	LWE-2438-3938-1-1
2.500	3.188	0.354	0.709	LWE-2500-3188-1-1
2.500	3.250	0.354	0.709	LWE-2500-3250-1-1
2.500	3.313	0.354	0.709	LWE-2500-3313-1-1
2.500	3.375	0.354	0.709	LWE-2500-3375-1-1
2.500	3.438	0.354	0.709	LWE-2500-3438-1-1
2.500	3.500	0.354	0.709	LWE-2500-3500-1-1
2.500	3.563	0.354	0.709	LWE-2500-3563-1-1
2.500	3.625	0.354	0.709	LWE-2500-3625-1-1
2.500	3.688	0.354	0.709	LWE-2500-3688-1-1
2.500	3.750	0.354	0.709	LWE-2500-3750-1-1
2.500	3.813	0.354	0.709	LWE-2500-3813-1-1
2.500	3.875	0.354	0.709	LWE-2500-3875-1-1
2.500	3.938	0.354	0.709	LWE-2500-3938-1-1
2.500	4.000	0.354	0.709	LWE-2500-4000-1-1
2.563	3.250	0.354	0.709	LWE-2563-3250-1-1
2.563	3.313	0.354	0.709	LWE-2563-3313-1-1
2.563	3.375	0.354	0.709	LWE-2563-3375-1-1
2.563	3.438	0.354	0.709	LWE-2563-3438-1-1
2.563	3.500	0.354	0.709	LWE-2563-3500-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
2.563	3.563	0.354	0.709	LWE-2563-3563-1-1
2.563	3.625	0.354	0.709	LWE-2563-3625-1-1
2.563	3.688	0.354	0.709	LWE-2563-3688-1-1
2.563	3.750	0.354	0.709	LWE-2563-3750-1-1
2.563	3.813	0.354	0.709	LWE-2563-3813-1-1
2.563	3.875	0.354	0.709	LWE-2563-3875-1-1
2.563	3.938	0.354	0.709	LWE-2563-3938-1-1
2.563	4.000	0.354	0.709	LWE-2563-4000-1-1
2.563	4.063	0.354	0.709	LWE-2563-4063-1-1
2.625	3.313	0.354	0.709	LWE-2625-3313-1-1
2.625	3.375	0.354	0.709	LWE-2625-3375-1-1
2.625	3.438	0.354	0.709	LWE-2625-3438-1-1
2.625	3.500	0.354	0.709	LWE-2625-3500-1-1
2.625	3.563	0.354	0.709	LWE-2625-3563-1-1
2.625	3.625	0.354	0.709	LWE-2625-3625-1-1
2.625	3.688	0.354	0.709	LWE-2625-3688-1-1
2.625	3.750	0.354	0.709	LWE-2625-3750-1-1
2.625	3.813	0.354	0.709	LWE-2625-3813-1-1
2.625	3.875	0.354	0.709	LWE-2625-3875-1-1
2.625	3.938	0.354	0.709	LWE-2625-3938-1-1
2.625	4.000	0.354	0.709	LWE-2625-4000-1-1
2.625	4.063	0.354	0.709	LWE-2625-4063-1-1
2.625	4.125	0.354	0.709	LWE-2625-4125-1-1
2.688	3.375	0.354	0.709	LWE-2688-3375-1-1
2.688	3.438	0.354	0.709	LWE-2688-3438-1-1
2.688	3.500	0.354	0.709	LWE-2688-3500-1-1
2.688	3.563	0.354	0.709	LWE-2688-3563-1-1
2.688	3.625	0.354	0.709	LWE-2688-3625-1-1
2.688	3.688	0.354	0.709	LWE-2688-3688-1-1
2.688	3.750	0.354	0.709	LWE-2688-3750-1-1
2.688	3.813	0.354	0.709	LWE-2688-3813-1-1
2.688	3.875	0.354	0.709	LWE-2688-3875-1-1
2.688	3.938	0.354	0.709	LWE-2688-3938-1-1
2.688	4.000	0.354	0.709	LWE-2688-4000-1-1
2.688	4.063	0.354	0.709	LWE-2688-4063-1-1
2.688	4.125	0.354	0.709	LWE-2688-4125-1-1
2.688	4.188	0.354	0.709	LWE-2688-4188-1-1
2.750	3.438	0.354	0.709	LWE-2750-3438-1-1
2.750	3.500	0.354	0.709	LWE-2750-3500-1-1
2.750	3.563	0.354	0.709	LWE-2750-3563-1-1
2.750	3.625	0.354	0.709	LWE-2750-3625-1-1
2.750	3.688	0.354	0.709	LWE-2750-3688-1-1
2.750	3.750	0.354	0.709	LWE-2750-3750-1-1
2.750	3.813	0.354	0.709	LWE-2750-3813-1-1
2.750	3.875	0.354	0.709	LWE-2750-3875-1-1
2.750	3.938	0.354	0.709	LWE-2750-3938-1-1
2.750	4.000	0.354	0.709	LWE-2750-4000-1-1
2.750	4.063	0.354	0.709	LWE-2750-4063-1-1
2.750	4.125	0.354	0.709	LWE-2750-4125-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
2.750	4.188	0.354	0.709	LWE-2750-4188-1-1
2.750	4.250	0.354	0.709	LWE-2750-4250-1-1
2.813	3.500	0.354	0.709	LWE-2813-3500-1-1
2.813	3.563	0.354	0.709	LWE-2813-3563-1-1
2.813	3.625	0.354	0.709	LWE-2813-3625-1-1
2.813	3.688	0.354	0.709	LWE-2813-3688-1-1
2.813	3.750	0.354	0.709	LWE-2813-3750-1-1
2.813	3.813	0.354	0.709	LWE-2813-3813-1-1
2.813	3.875	0.354	0.709	LWE-2813-3875-1-1
2.813	3.938	0.354	0.709	LWE-2813-3938-1-1
2.813	4.000	0.354	0.709	LWE-2813-4000-1-1
2.813	4.063	0.354	0.709	LWE-2813-4063-1-1
2.813	4.125	0.354	0.709	LWE-2813-4125-1-1
2.813	4.188	0.354	0.709	LWE-2813-4188-1-1
2.813	4.250	0.354	0.709	LWE-2813-4250-1-1
2.813	4.313	0.354	0.709	LWE-2813-4313-1-1
2.875	3.563	0.354	0.709	LWE-2875-3563-1-1
2.875	3.625	0.354	0.709	LWE-2875-3625-1-1
2.875	3.688	0.354	0.709	LWE-2875-3688-1-1
2.875	3.750	0.354	0.709	LWE-2875-3750-1-1
2.875	3.813	0.354	0.709	LWE-2875-3813-1-1
2.875	3.875	0.354	0.709	LWE-2875-3875-1-1
2.875	3.938	0.354	0.709	LWE-2875-3938-1-1
2.875	4.000	0.354	0.709	LWE-2875-4000-1-1
2.875	4.063	0.354	0.709	LWE-2875-4063-1-1
2.875	4.125	0.354	0.709	LWE-2875-4125-1-1
2.875	4.188	0.354	0.709	LWE-2875-4188-1-1
2.875	4.250	0.354	0.709	LWE-2875-4250-1-1
2.875	4.313	0.354	0.709	LWE-2875-4313-1-1
2.875	4.375	0.354	0.709	LWE-2875-4375-1-1
2.938	3.625	0.354	0.709	LWE-2938-3625-1-1
2.938	3.688	0.354	0.709	LWE-2938-3688-1-1
2.938	3.750	0.354	0.709	LWE-2938-3750-1-1
2.938	3.813	0.354	0.709	LWE-2938-3813-1-1
2.938	3.875	0.354	0.709	LWE-2938-3875-1-1
2.938	3.938	0.354	0.709	LWE-2938-3938-1-1
2.938	4.000	0.354	0.709	LWE-2938-4000-1-1
2.938	4.063	0.354	0.709	LWE-2938-4063-1-1
2.938	4.125	0.354	0.709	LWE-2938-4125-1-1
2.938	4.188	0.354	0.709	LWE-2938-4188-1-1
2.938	4.250	0.354	0.709	LWE-2938-4250-1-1
2.938	4.313	0.354	0.709	LWE-2938-4313-1-1
2.938	4.375	0.354	0.709	LWE-2938-4375-1-1
2.938	4.438	0.354	0.709	LWE-2938-4438-1-1
3.000	3.688	0.354	0.709	LWE-3000-3688-1-1
3.000	3.750	0.354	0.709	LWE-3000-3750-1-1
3.000	3.813	0.354	0.709	LWE-3000-3813-1-1
3.000	3.875	0.354	0.709	LWE-3000-3875-1-1
3.000	3.938	0.354	0.709	LWE-3000-3938-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
3.000	4.000	0.354	0.709	LWE-3000-4000-1-1
3.000	4.063	0.354	0.709	LWE-3000-4063-1-1
3.000	4.125	0.354	0.709	LWE-3000-4125-1-1
3.000	4.188	0.354	0.709	LWE-3000-4188-1-1
3.000	4.250	0.354	0.709	LWE-3000-4250-1-1
3.000	4.313	0.354	0.709	LWE-3000-4313-1-1
3.000	4.375	0.354	0.709	LWE-3000-4375-1-1
3.000	4.438	0.354	0.709	LWE-3000-4438-1-1
3.000	4.500	0.354	0.709	LWE-3000-4500-1-1
3.063	3.750	0.354	0.709	LWE-3063-3750-1-1
3.063	3.813	0.354	0.709	LWE-3063-3813-1-1
3.063	3.875	0.354	0.709	LWE-3063-3875-1-1
3.063	3.938	0.354	0.709	LWE-3063-3938-1-1
3.063	4.000	0.354	0.709	LWE-3063-4000-1-1
3.063	4.063	0.354	0.709	LWE-3063-4063-1-1
3.063	4.125	0.354	0.709	LWE-3063-4125-1-1
3.063	4.188	0.354	0.709	LWE-3063-4188-1-1
3.063	4.250	0.354	0.709	LWE-3063-4250-1-1
3.063	4.313	0.354	0.709	LWE-3063-4313-1-1
3.063	4.375	0.354	0.709	LWE-3063-4375-1-1
3.063	4.438	0.354	0.709	LWE-3063-4438-1-1
3.063	4.500	0.354	0.709	LWE-3063-4500-1-1
3.063	4.563	0.354	0.709	LWE-3063-4563-1-1
3.125	3.813	0.354	0.709	LWE-3125-3813-1-1
3.125	3.875	0.354	0.709	LWE-3125-3875-1-1
3.125	3.938	0.354	0.709	LWE-3125-3938-1-1
3.125	4.000	0.354	0.709	LWE-3125-4000-1-1
3.125	4.063	0.354	0.709	LWE-3125-4063-1-1
3.125	4.125	0.354	0.709	LWE-3125-4125-1-1
3.125	4.188	0.354	0.709	LWE-3125-4188-1-1
3.125	4.250	0.354	0.709	LWE-3125-4250-1-1
3.125	4.313	0.354	0.709	LWE-3125-4313-1-1
3.125	4.375	0.354	0.709	LWE-3125-4375-1-1
3.125	4.438	0.354	0.709	LWE-3125-4438-1-1
3.125	4.500	0.354	0.709	LWE-3125-4500-1-1
3.125	4.563	0.354	0.709	LWE-3125-4563-1-1
3.125	4.625	0.354	0.709	LWE-3125-4625-1-1
3.188	4.063	0.354	0.709	LWE-3188-4063-1-1
3.188	4.125	0.354	0.709	LWE-3188-4125-1-1
3.188	4.188	0.354	0.709	LWE-3188-4188-1-1
3.188	4.250	0.354	0.709	LWE-3188-4250-1-1
3.188	4.313	0.354	0.709	LWE-3188-4313-1-1
3.188	4.375	0.354	0.709	LWE-3188-4375-1-1
3.188	4.438	0.354	0.709	LWE-3188-4438-1-1
3.188	4.500	0.354	0.709	LWE-3188-4500-1-1
3.188	4.563	0.354	0.709	LWE-3188-4563-1-1
3.188	4.625	0.354	0.709	LWE-3188-4625-1-1
3.188	4.688	0.354	0.709	LWE-3188-4688-1-1
3.250	4.125	0.354	0.709	LWE-3250-4125-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
3.250	4.188	0.354	0.709	LWE-3250-4188-1-1
3.250	4.250	0.354	0.709	LWE-3250-4250-1-1
3.250	4.313	0.354	0.709	LWE-3250-4313-1-1
3.250	4.375	0.354	0.709	LWE-3250-4375-1-1
3.250	4.438	0.354	0.709	LWE-3250-4438-1-1
3.250	4.500	0.354	0.709	LWE-3250-4500-1-1
3.250	4.563	0.354	0.709	LWE-3250-4563-1-1
3.250	4.625	0.354	0.709	LWE-3250-4625-1-1
3.250	4.688	0.354	0.709	LWE-3250-4688-1-1
3.250	4.750	0.354	0.709	LWE-3250-4750-1-1
3.313	4.188	0.354	0.709	LWE-3313-4188-1-1
3.313	4.250	0.354	0.709	LWE-3313-4250-1-1
3.313	4.313	0.354	0.709	LWE-3313-4313-1-1
3.313	4.375	0.354	0.709	LWE-3313-4375-1-1
3.313	4.438	0.354	0.709	LWE-3313-4438-1-1
3.313	4.500	0.354	0.709	LWE-3313-4500-1-1
3.313	4.563	0.354	0.709	LWE-3313-4563-1-1
3.313	4.625	0.354	0.709	LWE-3313-4625-1-1
3.313	4.688	0.354	0.709	LWE-3313-4688-1-1
3.313	4.750	0.354	0.709	LWE-3313-4750-1-1
3.313	4.813	0.354	0.709	LWE-3313-4813-1-1
3.375	4.250	0.354	0.709	LWE-3375-4250-1-1
3.375	4.313	0.354	0.709	LWE-3375-4313-1-1
3.375	4.375	0.354	0.709	LWE-3375-4375-1-1
3.375	4.438	0.354	0.709	LWE-3375-4438-1-1
3.375	4.500	0.354	0.709	LWE-3375-4500-1-1
3.375	4.563	0.354	0.709	LWE-3375-4563-1-1
3.375	4.625	0.354	0.709	LWE-3375-4625-1-1
3.375	4.688	0.354	0.709	LWE-3375-4688-1-1
3.375	4.750	0.354	0.709	LWE-3375-4750-1-1
3.375	4.813	0.354	0.709	LWE-3375-4813-1-1
3.375	4.875	0.354	0.709	LWE-3375-4875-1-1
3.438	4.313	0.354	0.709	LWE-3438-4313-1-1
3.438	4.375	0.354	0.709	LWE-3438-4375-1-1
3.438	4.438	0.354	0.709	LWE-3438-4438-1-1
3.438	4.500	0.354	0.709	LWE-3438-4500-1-1
3.438	4.563	0.354	0.709	LWE-3438-4563-1-1
3.438	4.625	0.354	0.709	LWE-3438-4625-1-1
3.438	4.688	0.354	0.709	LWE-3438-4688-1-1
3.438	4.750	0.354	0.709	LWE-3438-4750-1-1
3.438	4.813	0.354	0.709	LWE-3438-4813-1-1
3.438	4.875	0.354	0.709	LWE-3438-4875-1-1
3.438	4.938	0.354	0.709	LWE-3438-4938-1-1
3.500	4.375	0.354	0.709	LWE-3500-4375-1-1
3.500	4.438	0.354	0.709	LWE-3500-4438-1-1
3.500	4.500	0.354	0.709	LWE-3500-4500-1-1
3.500	4.563	0.354	0.709	LWE-3500-4563-1-1
3.500	4.625	0.354	0.709	LWE-3500-4625-1-1
3.500	4.688	0.354	0.709	LWE-3500-4688-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
3.500	4.750	0.354	0.709	LWE-3500-4750-1-1
3.500	4.813	0.354	0.709	LWE-3500-4813-1-1
3.500	4.875	0.354	0.709	LWE-3500-4875-1-1
3.500	4.938	0.354	0.709	LWE-3500-4938-1-1
3.500	5.000	0.354	0.709	LWE-3500-5000-1-1
3.563	4.438	0.354	0.709	LWE-3563-4438-1-1
3.563	4.500	0.354	0.709	LWE-3563-4500-1-1
3.563	4.563	0.354	0.709	LWE-3563-4563-1-1
3.563	4.625	0.354	0.709	LWE-3563-4625-1-1
3.563	4.688	0.354	0.709	LWE-3563-4688-1-1
3.563	4.750	0.354	0.709	LWE-3563-4750-1-1
3.563	4.813	0.354	0.709	LWE-3563-4813-1-1
3.563	4.875	0.354	0.709	LWE-3563-4875-1-1
3.563	4.938	0.354	0.709	LWE-3563-4938-1-1
3.563	5.000	0.354	0.709	LWE-3563-5000-1-1
3.563	5.063	0.354	0.709	LWE-3563-5063-1-1
3.625	4.500	0.354	0.709	LWE-3625-4500-1-1
3.625	4.563	0.354	0.709	LWE-3625-4563-1-1
3.625	4.625	0.354	0.709	LWE-3625-4625-1-1
3.625	4.688	0.354	0.709	LWE-3625-4688-1-1
3.625	4.750	0.354	0.709	LWE-3625-4750-1-1
3.625	4.813	0.354	0.709	LWE-3625-4813-1-1
3.625	4.875	0.354	0.709	LWE-3625-4875-1-1
3.625	4.938	0.354	0.709	LWE-3625-4938-1-1
3.625	5.000	0.354	0.709	LWE-3625-5000-1-1
3.625	5.063	0.354	0.709	LWE-3625-5063-1-1
3.625	5.125	0.354	0.709	LWE-3625-5125-1-1
3.688	4.563	0.354	0.709	LWE-3688-4563-1-1
3.688	4.688	0.354	0.709	LWE-3688-4688-1-1
3.750	4.625	0.354	0.709	LWE-3750-4625-1-1
3.750	4.688	0.354	0.709	LWE-3750-4688-1-1
3.750	4.750	0.354	0.709	LWE-3750-4750-1-1
3.750	4.813	0.354	0.709	LWE-3750-4813-1-1
3.750	4.875	0.354	0.709	LWE-3750-4875-1-1
3.750	4.938	0.354	0.709	LWE-3750-4938-1-1
3.750	5.000	0.354	0.709	LWE-3750-5000-1-1
3.750	5.063	0.354	0.709	LWE-3750-5063-1-1
3.750	5.125	0.354	0.709	LWE-3750-5125-1-1
3.750	5.188	0.354	0.709	LWE-3750-5188-1-1
3.750	5.250	0.354	0.709	LWE-3750-5250-1-1
3.813	4.688	0.354	0.709	LWE-3813-4688-1-1
3.813	4.750	0.354	0.709	LWE-3813-4750-1-1
3.813	4.813	0.354	0.709	LWE-3813-4813-1-1
3.813	4.875	0.354	0.709	LWE-3813-4875-1-1
3.813	4.938	0.354	0.709	LWE-3813-4938-1-1
3.813	5.000	0.354	0.709	LWE-3813-5000-1-1
3.813	5.063	0.354	0.709	LWE-3813-5063-1-1
3.813	5.125	0.354	0.709	LWE-3813-5125-1-1
3.813	5.188	0.354	0.709	LWE-3813-5188-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
3.813	5.250	0.354	0.709	LWE-3813-5250-1-1
3.813	5.313	0.354	0.709	LWE-3813-5313-1-1
3.875	4.750	0.354	0.709	LWE-3875-4750-1-1
3.875	4.813	0.354	0.709	LWE-3875-4813-1-1
3.875	4.875	0.354	0.709	LWE-3875-4875-1-1
3.875	4.938	0.354	0.709	LWE-3875-4938-1-1
3.875	5.000	0.354	0.709	LWE-3875-5000-1-1
3.875	5.063	0.354	0.709	LWE-3875-5063-1-1
3.875	5.125	0.354	0.709	LWE-3875-5125-1-1
3.875	5.188	0.354	0.709	LWE-3875-5188-1-1
3.875	5.250	0.354	0.709	LWE-3875-5250-1-1
3.875	5.313	0.354	0.709	LWE-3875-5313-1-1
3.875	5.375	0.354	0.709	LWE-3875-5375-1-1
3.938	4.813	0.354	0.709	LWE-3938-4813-1-1
3.938	4.875	0.354	0.709	LWE-3938-4875-1-1
3.938	4.938	0.354	0.709	LWE-3938-4938-1-1
3.938	5.000	0.354	0.709	LWE-3938-5000-1-1
3.938	5.063	0.354	0.709	LWE-3938-5063-1-1
3.938	5.125	0.354	0.709	LWE-3938-5125-1-1
3.938	5.188	0.354	0.709	LWE-3938-5188-1-1
3.938	5.250	0.354	0.709	LWE-3938-5250-1-1
3.938	5.313	0.354	0.709	LWE-3938-5313-1-1
3.938	5.375	0.354	0.709	LWE-3938-5375-1-1
3.938	5.438	0.354	0.709	LWE-3938-5438-1-1
4.000	4.875	0.354	0.709	LWE-4000-4875-1-1
4.000	4.938	0.354	0.709	LWE-4000-4938-1-1
4.000	5.000	0.354	0.709	LWE-4000-5000-1-1
4.000	5.063	0.354	0.709	LWE-4000-5063-1-1
4.000	5.125	0.354	0.709	LWE-4000-5125-1-1
4.000	5.188	0.354	0.709	LWE-4000-5188-1-1
4.000	5.250	0.354	0.709	LWE-4000-5250-1-1
4.000	5.313	0.354	0.709	LWE-4000-5313-1-1
4.000	5.375	0.354	0.709	LWE-4000-5375-1-1
4.000	5.438	0.354	0.709	LWE-4000-5438-1-1
4.000	5.500	0.354	0.709	LWE-4000-5500-1-1
22.0	40.0	7.0	16.0	LWM-0220-0400-1-1
24.0	50.8	7.0	16.0	LWM-0240-0508-1-1
25.0	39.0	7.0	16.0	LWM-0250-0390-1-1
25.0	47.0	7.0	16.0	LWM-0250-0470-1-1
25.0	50.0	7.0	16.0	LWM-0250-0500-1-1
30.0	42.0	7.0	16.0	LWM-0300-0420-1-1
30.0	47.0	7.0	16.0	LWM-0300-0470-1-1
30.0	55.0	7.0	16.0	LWM-0300-0550-1-1
32.0	55.0	7.0	16.0	LWM-0320-0550-1-1
35.0	45.0	7.0	16.0	LWM-0350-0450-1-1
35.0	47.0	7.0	16.0	LWM-0350-0470-1-1
35.0	52.0	7.0	16.0	LWM-0350-0520-1-1
40.0	52.0	7.0	16.0	LWM-0400-0520-1-1
40.0	72.0	7.0	16.0	LWM-0400-0720-1-1



ProTech™ Bearing Isolators

ProTech LW Profile

LWE - English (inch)

LWM - Metric (mm)

Shaft Dia.	Bore Dia.	Total In Bore Depth	Total Seal Width	ProTech Part Number
41.0	66.0	8.0	17.0	LWM-0410-0660-1-1
42.0	62.0	8.0	17.0	LWM-0420-0620-1-1
44.0	58.0	8.0	17.0	LWM-0440-0580-5-3
45.0	65.0	8.0	17.0	LWM-0450-0650-1-1
50.0	72.0	8.0	17.0	LWM-0500-0720-1-1
54.0	78.0	8.0	17.0	LWM-0540-0780-1-1
55.0	70.0	8.0	17.0	LWM-0550-0700-1-1
57.1	73.0	8.0	17.0	LWM-0571-0730-5-1
58.0	80.0	8.0	17.0	LWM-0580-0800-1-1
60.0	80.0	8.0	17.0	LWM-0600-0800-1-1
65.0	91.0	9.0	18.0	LWM-0650-0910-5-3
66.7	82.6	9.0	18.0	LWM-0667-0826-5-1
70.0	90.0	9.0	18.0	LWM-0700-0900-1-1
70.0	95.0	9.0	18.0	LWM-0700-0950-1-1
75.0	90.0	9.0	18.0	LWM-0750-0900-1-1
75.0	95.0	9.0	18.0	LWM-0750-0950-1-1
75.0	100.0	9.0	18.0	LWM-0750-1000-1-1
80.0	106.0	9.0	18.0	LWM-0800-1060-5-3
80.0	110.0	9.0	18.0	LWM-0800-1100-1-1
84.0	109.0	9.0	18.0	LWM-0840-1090-1-1
85.0	110.0	9.0	18.0	LWM-0850-1100-1-1
85.0	112.0	9.0	18.0	LWM-0850-1120-5-1
90.0	110.0	9.0	18.0	LWM-0900-1100-1-1
90.0	115.0	9.0	18.0	LWM-0900-1150-1-1
110.0	130.0	9.0	18.0	LWM-1100-1300-5-1
125.0	150.0	9.0	18.0	LWM-1250-1500-5-1
130.0	160.0	9.0	18.0	LWM-1300-1600-5-1