



Online Buying Guide for Rotary Shaft Clipper® Oil Seals



ENGINEERING YOUR SUCCESS.

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	9651 H1L5	0.750	1.250	0.250	LUP
Gen. Purpose	9339 H1L5	0.750	1.625	0.312	LUP
Gen. Purpose	10751 H1L5	1.000	1.500	0.250	LUP
Gen. Purpose	9848 H1L5	1.125	1.625	0.312	LUP
Gen. Purpose	7054 H1L5	1.125	1.875	0.375	LUP
Gen. Purpose	8820 H1L5	1.250	1.750	0.250	LUP
Gen. Purpose	10058 H1L5	1.250	2.000	0.375	LUP
Gen. Purpose	9080 H1L5	1.375	1.875	0.250	LUP
High Pressure	15883 5066	1.375	2.000	0.313	HP
Gen. Purpose	10753 H1L5	1.375	2.062	0.375	LUP
Gen. Purpose	9394 H1L5	1.375	2.500	0.375	LUP
Gen. Purpose	11751 H1L5	1.378	2.205	0.394	LPD
Gen. Purpose	4850 H1L5	1.438	2.250	0.500	LUP
Gen. Purpose	11603 H1L5	1.497	2.835	0.500	LUP
Gen. Purpose	9831 H1L5	1.500	2.000	0.250	LUP
Gen. Purpose	11654 H1L5	1.500	2.000	0.313	LUP
Gen. Purpose	6679 H1L5	1.500	2.125	0.438	LUP
High Pressure	15409 5066	1.500	2.250	0.375	HP
Gen. Purpose	7033 H1L5	1.500	2.250	0.375	LUP
Gen. Purpose	9952 H1L5	1.500	2.500	0.375	LUP
Gen. Purpose	14618 H1L5	1.500	2.500	0.500	LDS
Gen. Purpose	9041 H1L5	1.500	2.500	0.500	LUP
High Pressure	15969 5066	1.625	2.375	0.375	HP
Gen. Purpose	12007 H1L5	1.625	2.438	0.375	LPD
Gen. Purpose	20428 H1L5	1.625	2.720	0.375	LUP
Gen. Purpose	8815 H1L5	1.688	2.375	0.313	LUP
Gen. Purpose	10054 H1L5	1.688	2.502	0.375	LUP
Wiper	12319 ALLL7	1.750	2.129	0.328	P

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
High Pressure	15898 5066	1.750	2.500	0.375	HP
Gen. Purpose	9854 H1L5	1.750	2.500	0.375	LUP
Gen. Purpose	9955 H1L5	1.750	2.750	0.500	LUP
Gen. Purpose	9393 H1L5	1.771	3.937	0.500	LUP
Gen. Purpose	5628 H1L5	1.812	2.500	0.375	LPD
Gen. Purpose	9550 H1L5	1.875	2.625	0.438	LUP
Wiper	19063 H1L5	1.875	2.627	0.375	H
Gen. Purpose	10189 H1L5	1.875	3.543	0.375	LPD
Gen. Purpose	12526 H1L5	1.963	3.544	0.500	LPD
Gen. Purpose	16972 H1L5	1.969	3.125	0.500	LPD
Gen. Purpose	11855 H1L5	2.000	2.625	0.313	LDS
Gen. Purpose	9736 H1L5	2.000	2.625	0.313	LPD
Gen. Purpose	10207 H1L5	2.000	2.686	0.375	LUP
Misalignment	13847 H1L5	2.000	2.750	0.375	LPDW
Gen. Purpose	11551 H1L5	2.000	2.750	0.500	LUP
Gen. Purpose	11018 H1L5	2.000	3.000	0.375	LUP
Gen. Purpose	9043 H1L5	2.000	3.000	0.500	LUP
Excluder	11983 H1L5	2.000	3.250	0.406	SSW
Gen. Purpose	4976 H1L5	2.188	3.000	0.500	LPD
Gen. Purpose	10251 H1L5	2.250	2.875	0.313	LUP
High Pressure	15455 5066	2.250	3.000	0.375	HP
Gen. Purpose	10289 H1L5	2.250	3.000	0.375	LUP
Gen. Purpose	10432 H1L5	2.250	3.000	0.500	LUP
Gen. Purpose	6336 H1L5	2.250	3.250	0.375	LUP
Wiper	16202 H1L5	2.250	3.250	0.500	H
Gen. Purpose	10418 H1L5	2.250	3.250	0.500	LUP
Gen. Purpose	8495 H1L5	2.250	4.000	0.500	LPD
Excluder	11992 H1L5	2.250	4.000	0.500	SSW

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	11143 H1L5	2.437	3.500	0.500	LUP
Gen. Purpose	9171 H1L5	2.438	3.125	0.375	LUP
Gen. Purpose	13498 H1L5	2.438	3.375	0.500	LPD
Excluder	11816 H1L5	2.498	4.500	0.500	SSW
Gen. Purpose	10208 H1L5	2.500	3.500	0.438	LUP
Wiper	16203 H1L5	2.500	3.500	0.500	H
Gen. Purpose	14620 H1L5	2.500	3.500	0.500	LDS
Gen. Purpose	10121 H1L5	2.500	3.500	0.500	LUP
Gen. Purpose	10050 H1L5	2.625	3.625	0.438	LUP
Gen. Purpose	9541 H1L5	2.688	3.750	0.500	LUP
Gen. Purpose	10526 H1L5	2.750	3.375	0.313	LUP
Gen. Purpose	14042 H1L5	2.750	3.500	0.375	LPD
Gen. Purpose	14781 H1L5	2.750	3.500	0.500	LDS
Gen. Purpose	11894 H1L5	2.750	3.500	0.500	LPD
High Pressure	15672 5066	2.750	3.625	0.438	HP
Gen. Purpose	9732 H1L5	2.750	3.750	0.500	LUP
Excluder	16616 H1L5	2.750	4.000	0.438	SSW
Gen. Purpose	11558 H1L5	2.813	3.751	0.500	LUP
Gen. Purpose	3631 H1L5	2.875	3.500	0.313	LPD
Gen. Purpose	10319 H1L5	2.901	3.601	0.232	LUP
Gen. Purpose	5961 H1L5	3.000	3.750	0.375	LUP
Gen. Purpose	9182 H1L5	3.000	4.000	0.375	LUP
Split	0300 9373	3.000	4.000	0.438	SPLIT
Gen. Purpose	9045 H1L5	3.000	4.000	0.500	LUP
Springless	9343 H1L7	3.000	4.000	0.500	SS
Gen. Purpose	13773 H1L5	3.000	4.000	0.562	LDS
Gen. Purpose	6423 H1L5	3.000	4.003	0.375	LUP
Gen. Purpose	5011 H1L5	3.125	4.125	0.500	LUP

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	4801 H1L5	3.156	4.250	0.469	LUP
Gen. Purpose	7190 H1L5	3.250	4.250	0.438	LUP
Wiper	11764 H1L5	3.250	4.250	0.500	H
Gen. Purpose	9547 H1L5	3.250	4.250	0.500	LUP
Gen. Purpose	13241 H1L5	3.250	4.250	0.625	LDS
Gen. Purpose	16431 H1L5	3.346	4.134	0.512	LUP
Gen. Purpose	10164 H1L5	3.375	4.375	0.500	LUP
Gen. Purpose	15471 H1L5	3.437	4.500	0.500	LPD
Gen. Purpose	10948 H1L5	3.438	4.625	0.500	LUP
Gen. Purpose	7325 H1L5	3.500	4.375	0.375	LUP
Gen. Purpose	9752 H1L5	3.500	4.500	0.438	LUP
High Pressure	16312 5066	3.500	4.500	0.500	HP
Gen. Purpose	12565 H1L5	3.500	4.500	0.500	LDS
Gen. Purpose	11197 H1L5	3.500	4.500	0.500	LUP
Split	0350 7341	3.500	4.500	0.500	SPLIT
Excluder	10915 H1L5	3.500	5.625	0.625	SSW
Gen. Purpose	11198 H1L5	3.625	4.625	0.500	LUP
Gen. Purpose	7146 H1L5	3.750	4.750	0.500	LUP
Gen. Purpose	10057 H1L5	3.750	5.000	0.469	LUP
Split	0393 10175	3.938	4.938	0.500	SPLIT
Gen. Purpose	9402 H1L5	3.938	5.000	0.468	LUP
Split	0393 9879	3.938	5.000	0.469	SPLIT
Gen. Purpose	9510 H1L5	3.938	5.000	0.500	LUP
Misalignment	11239 H1L5	3.938	5.000	0.500	LPDW
Excluder	14613 H1L5	3.938	5.750	0.625	SSW
Gen. Purpose	9866 H1L5	4.000	5.000	0.437	LUP
Gen. Purpose	9788 H1L5	4.000	5.000	0.438	RPD
Split	0400 10468	4.000	5.000	0.438	SPLIT

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	15141 H1L5	4.000	5.000	0.500	LDS
Gen. Purpose	7199 H1L5	4.000	5.000	0.500	LUP
Split	0400 10175	4.000	5.000	0.500	SPLIT
Springless	9342 H1L7	4.000	5.000	0.500	SS
High Pressure	15092 5066	4.000	5.250	0.625	HP
High Pressure	15373 5066	4.250	5.000	0.375	HP
Gen. Purpose	10490 H1L5	4.250	5.000	0.438	LUP
Gen. Purpose	7187 H1L5	4.250	5.250	0.438	LUP
Gen. Purpose	7040 H1L5	4.250	5.250	0.500	LUP
Excluder	15144 H1L5	4.330	6.102	0.591	SSW
Misalignment	11296 H1L5	4.438	5.500	0.563	LPDW
Gen. Purpose	10332 H1L5	4.438	5.500	0.600	LPD
Gen. Purpose	4168 H1L5	4.500	5.250	0.375	LUP
Gen. Purpose	13172 H1L5	4.500	5.500	0.500	LDS
Gen. Purpose	9170 H1L5	4.500	5.500	0.500	LUP
Gen. Purpose	11832 H1L5	4.500	5.625	0.563	LUP
Gen. Purpose	9549 H1L5	4.750	5.500	0.375	LUP
Gen. Purpose	9820 H1L5	4.750	5.750	0.500	LUP
Rotating Bore	17025 H1L5	4.750	6.000	0.500	OLLUP
Split	0487 9737	4.875	5.875	0.500	SPLIT
Split	0493 10788	4.938	5.938	0.500	SPLIT
Gen. Purpose	7144 H1L5	4.938	6.000	0.500	LPD
Split	0493 6260	4.938	6.250	0.563	SPLIT
Gen. Purpose	17164 H1L5	5.000	5.750	0.375	LUP
Gen. Purpose	9333 H1L5	5.000	5.750	0.438	LUP
Gen. Purpose	9629 H1L5	5.000	6.000	0.500	LUP
Gen. Purpose	9737 H1L5	5.000	6.000	0.500	RPD
Gen. Purpose	6325 H1L5	5.000	6.250	0.562	LUP

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	17959 H1L5	5.000	6.250	0.625	LDS
Excluder	10816 H1L5	5.248	7.375	0.625	SSW
Gen. Purpose	7042 H1L5	5.250	6.250	0.500	LUP
Gen. Purpose	7112 H1L5	5.250	6.500	0.625	LUP
Excluder	17473 H1L5	5.250	6.750	0.625	SSW
Gen. Purpose	10598 H1L5	5.375	6.375	0.500	LUP
Split	0543 12256	5.438	6.438	0.500	SPLIT
Gen. Purpose	9646 H1L5	5.438	6.625	0.500	LUP
Split	0543 11070	5.438	6.688	0.625	SPLIT
Gen. Purpose	4825 H1L5	5.500	6.250	0.438	LUP
Gen. Purpose	5926 H1L5	5.500	6.500	0.500	LUP
Split	0550 12256	5.500	6.500	0.500	SPLIT
Gen. Purpose	7186 H1L5	5.500	6.750	0.563	LUP
Gen. Purpose	1684 H1L5	5.500	6.750	0.625	LUP
Split	0550 11070	5.500	6.750	0.625	SPLIT
Gen. Purpose	13052 H1L5	5.500	7.000	0.750	LDS
Gen. Purpose	10152 H1L5	5.625	6.875	0.625	LUP
Gen. Purpose	9165 H1L5	5.750	7.000	0.625	LUP
Gen. Purpose	9514 H1L5	6.000	7.000	0.438	LUP
Split	0600 12737	6.000	7.000	0.500	SPLIT
Gen. Purpose	8947 H1L5	6.000	7.500	0.562	LUP
Gen. Purpose	4711 H1L5	6.000	7.500	0.625	RUP
Gen. Purpose	10439 H1L5	6.250	7.250	0.438	LUP
Gen. Purpose	8804 H1L5	6.250	7.500	0.500	LUP
Gen. Purpose	10267 H1L5	6.500	7.500	0.563	LUP
Gen. Purpose	8950 H1L5	6.500	8.000	0.750	LUP
Gen. Purpose	10041 H1L5	6.750	7.750	0.500	LPD
Misalignment	16215 H1L5	6.750	7.750	0.750	LUPW

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	3892 H1L5	7.000	8.000	0.437	LUP
Gen. Purpose	13240 H1L5	7.000	8.000	0.500	LDS
Gen. Purpose	6862 H1L5	7.000	8.000	0.625	LUP
Gen. Purpose	12094 H1L5	7.250	8.250	0.438	LUP
Gen. Purpose	10027 H1L5	7.250	8.500	0.625	LUP
Gen. Purpose	9973 H1L5	7.500	8.500	0.500	LUP
Gen. Purpose	9595 H1L5	7.750	8.750	0.438	LUP
Misalignment	15460 H1L5	7.750	9.375	0.625	LPDW
Excluder	15061 H1L5	8.000	10.250	0.750	SSW
Gen. Purpose	9191 H1L5	8.000	9.000	0.625	LUP
Gen. Purpose	9224 H1L5	8.250	9.500	0.625	LUP
Gen. Purpose	6718 H1L5	8.375	9.875	0.688	LUP
Gen. Purpose	16552 H1L5	8.500	9.500	0.625	LUP
Gen. Purpose	15959 H1L5	8.500	9.750	0.625	LUP
Gen. Purpose	10020 H1L5	8.625	9.625	0.500	LUP
Gen. Purpose	9557 H1L5	8.750	10.000	0.625	LUP
Gen. Purpose	5386 H1L5	9.000	10.000	0.469	LUP
Gen. Purpose	9891 H1L5	9.125	10.375	0.625	LUP
Gen. Purpose	8824 H1L5	9.500	11.500	1.000	LUP
Gen. Purpose	13809 H1L5	9.750	11.250	0.750	LUP
Gen. Purpose	9482 H1L5	10.000	11.250	0.625	LUP
Gen. Purpose	12529 H1L5	10.000	11.500	0.625	LUP
Gen. Purpose	8829 H1L5	10.500	11.750	0.625	LUP
Gen. Purpose	8471 H1L5	10.750	12.500	0.562	LUP
Gen. Purpose	11746 H1L5	11.000	12.000	0.625	LUP
Gen. Purpose	10697 H1L5	11.250	12.750	0.625	LUP
Gen. Purpose	8433 H1L5	12.000	13.500	0.750	RUP
Split	1300 6660	13.000	14.500	0.625	SPLIT

Type	Part Number	Shaft Dia.	Bore Dia	Width	Profile (Style)
Gen. Purpose	13811 H1L5	13.000	14.500	0.688	LUP
Split	1400 9447	14.000	16.000	1.000	SPLIT
Gen. Purpose	6334 H1L5	15.000	17.000	0.750	LUP
Split	1600 3919	16.000	18.000	0.875	SPLIT

Parker Hannifin Corporation
Engineered Polymer Systems Division

phone 800 233 3900
www.parker.com/eps



ENGINEERING YOUR SUCCESS.