

PVC PRESSURE HOSE CHEMICAL



SPW SPRAYCHEM

Parker Spraychem hose is specifically designed for use in pest control and agriculture chemical spray applications. It's red UV resistant cover offers remarkable performance in Australia's harsh environment. It's lightweight construction makes it suitable for most spraying applications, where flexibility and ease of handling is essential.



FEATURES:

- ◆ Good flexibility
- ◆ Smooth red cover
- ◆ Special blend of stabilisers provides superior UV resistance
- ◆ Suitable for most spraying applications
- ◆ Australian made

ID (mm)	OD (mm)	Working Pressure (psi)	Min Bend Radius (mm)	Weight (kg/mtr)	Coil Lengths (Mtrs)	Part No
10.0	17.0	300psi	80	0.16	20, 100	SPW-010-***
12.5	19.0	300psi	100	0.18	20, 100	SPW-012-***
20.0	27.5	250psi	190	0.35	20, 100	SPW-020-***

ID & OD dimensions are subject to the following tolerances:
6-20mm +/- 0.4mm

Temp Range:	Min -10°C to Max +60°C
Tube/Cover Compound:	Virgin PVC
Colour:	Black tube / Red cover
Ink Branding:	PARKER SPRAYCHEM (SIZE)MM PESTICIDE/WEEDICIDE (300) PSI WP MADE IN AUSTRALIA (DATE)

*** To complete part number, add coil length. Recommended safety factor 4:1. All W.P. ratings are at 20°C.