

R181SN

一层钢丝编织软管(包塑管)

EN853 1SN标准、煤安认证、MSHA认证



结构:内胶层、一层钢丝编织层、外胶层

应用范围:适于输送液压流体如醇、液压油、润滑油、乳化液、烃等

型号	软管内径					钢丝层外径 (mm)		软管外径 (mm)		最大工作压力		最小弯曲 半径	重量
	DN	inch	size	mm		min	max	min	max	MPa	PSI	mm	kg/m
R181SN-6	6	1/4	-4	6.2	7.0	10.6	11.6	12.2	13.7	22.5	3250	100	0.24
R181SN-8	8	5/16	-5	7.7	8.5	12.1	13.3	14.0	15.4	21.5	3100	115	0.28
R181SN-10	10	3/8	-6	9.3	10.1	14.5	15.7	16.7	18.1	18.0	2600	130	0.37
R181SN-13	13	1/2	-8	12.3	13.5	17.5	19.1	19.8	21.4	16.0	2300	180	0.41
R181SN-16	16	5/8	-10	15.5	16.7	20.6	22.2	22.9	24.5	13.0	1850	200	0.51
R181SN-19	19	3/4	-12	18.6	19.8	24.6	26.2	26.9	28.5	10.5	1500	240	0.66
R181SN-25	25	1	-16	25.0	26.4	32.5	34.1	34.6	36.6	8.8	1250	300	0.96

• 样本尺寸仅供参考, 请以实际产品尺寸为准