

R182SN

两层钢丝编织软管(包塑管)

EN853 2SN、煤安认证、MSHA认证



结构：内胶层、两层钢丝编织层、外胶层

应用范围：适于输送液压流体如醇、液压油、润滑油、乳化液、烃等

型号	软管内径					钢丝层外径 (mm)		软管外径 (mm)		最大工作压力		最小弯曲 半径	重量
	DN	inch	size	mm		min	max	min	max	MPa	PSI	mm	kg/m
R182SN-6	6	1/4	-4	6.2	7.0	12.1	13.3	14.3	15.7	40.0	5800	100	0.37
R182SN-8	8	5/16	-5	7.7	8.5	13.7	14.9	15.6	17.0	35.0	5050	115	0.45
R182SN-10	10	3/8	-6	9.3	10.1	16.1	17.3	17.6	19.3	33.0	4750	130	0.52
R182SN-13	13	1/2	-8	12.3	13.5	19.0	20.6	21.0	22.6	27.5	3950	180	0.65
R182SN-16	16	5/8	-10	15.5	16.7	22.2	23.8	24.2	25.8	25.0	3600	200	0.78
R182SN-19	19	3/4	-12	18.6	19.8	26.2	27.8	28.5	30.1	21.5	3100	240	1.02
R182SN-25	25	1	-16	25.0	26.4	34.1	35.7	37.3	38.9	16.5	2350	300	1.44

• 样本尺寸仅供参考，请以实际产品尺寸为准