



COMPOUND DATA SHEET

Parker O-Ring & Engineered Seals Division, North America

MATERIAL REPORT

Report Number 541330

Report Date 4/10/2025

Title: General Evaluation of Parker Compound NM507-90

Elastomer Type: NBR

Purpose: To document compliance to qualification requirements and basic material properties

Specification: AMS-P-5510

Color: Black

Recommended Temperature Range: -65°F to 180°F

Recommended For: Aliphatic hydrocarbons (propane, butane), petroleum oil, mineral oil, grease, diesel fuel, fuel oils, vegetable oils, HFA, HFB, & HFC hydraulic fluids, water (under 140°F), salt & alkali solutions, and dilute acids

Not Recommended For: Fuels of high aromatic content, aromatic hydrocarbons (benzene), chlorinated hydrocarbons (trichloroethylene), strong acids, glycols, ozone, weather, atmospheric aging, and polar solvents (ketone, acetone, acetic acid, ethylene-ester)

*"Purchaser use only. Reproduce only in full. Data pertains to items referenced only.
The recording of false, fictitious, or fraudulent statements or entries in the report may be punishable
as a felony under federal law."*

Original Physical Properties

Specific Gravity
Hardness, Shore A, pts
Tensile Strength, min, psi
Ultimate Elongation, min, %
Tensile stress at 50% elongation, psi min
Temperature retraction TR-10-10 max, °F

Test Method

ASTM D297
ASTM D2240
ASTM D1414
ASTM D1414
ASTM D1414
ASTM D1329

Spec Limits

1.25 to 1.45
85 to 95
1450
80
500
-45

Results

1.29
86
1774
107
677
-50

Corrosion and Adhesion

Section 3.2.11

No Corrosion
No Adhesion

AMS-QQ-A-250/4 2024 Aluminum Alloy
AMS-QQ-A-250/11 6061 Aluminum Alloy
AMS-QQ-A-250/12 7075 Aluminum Alloy
AMS-QQ-S-763 440C Stainless Steel
ASTM A484 303 Stainless Steel
AMS-6350 4130 Steel, Aircraft Quality

Pass
Pass
Pass
Pass
Pass
Pass

Dry Heat Resistance

ASTM D573

168 Hours ±0.5 @ 158°F ± 1.8 (70°C ± 1)

Hardness change, pts
Tensile Strength change, % max
Elongation change, % max

0 to 5
-10
-15

4
-2
-11

Compression Set

ASTM D395

168 Hours ±0.5 @ 158°F ± 1.8 (70°C ± 1)

Test Method B

Percent of Original Deflection, max

35

27

Oil Resistance in Mil-PRF-5606 (Royco 756)**168 Hours ±0.5 @ 158°F ± 1.8 (70°C ± 1)**

ASTM D471

Hardness change, Shore A, pts
Tensile Strength change, % max
Ultimate Elongation change, % max
Temperature retraction TR-10, max °F
Compression set, % of Original Deflection, max

Volume Change, %

-5 to 5
-15
-20
-39
25

1 to 8

-4
-8
-11
-50
13

3