## Turbine Series - 771000FH

## Specifications:


Height: 22.0" (55.88 cm)

Width: 21.25" (53.98 cm) with Bracket 12.3" (31.24 cm) with Bracket Depth:

39.0 lbs (17.7 kg) Weight: 1"-11 1/2 NPT Ports:


Service Clearance (Top): 10.0" (25.4 cm) Vacuum Installation Recommended Maximum Pressure: 15 psi (1.03 bar) Max Flow Rate: 540 gph (2044 lph)


FH Model Superseded to FV Model. See RSL0428 FH-FV Change Notification for available assemblies crosses.






## **PARTS**







	Part #	Description
1A		Mounting Bracket - Contact Technical Support
2A		Inlet/Outlet Manifold Tube - Contact Technical Support
ЗА		Turbine Fuel Filter - 1000FH Series See Cutsheet <b>RSL0292</b> for available Parts and Accessories

## Accessories and Parts Available (Not Shown)

4A	RK 11-1952	Complete Seal Service Kit - 900FH/1000FH Series Filters (Requires 2)
44	RK 11-1404	Complete Seal Service Kit - 900/1000 Series Filters For FG and Older Models (Requires 2)
	RK30880E	WIF Sensor and Light Kit - 1/2"-20 UNF
4B	RK33802	WIF Probe Kit - 1/2"-20 UNF - Two Wire Pigtail Water Detection Module Required - <i>Use 4C</i>
4C	RK 14329 RK 14321	Water Detection Module - 12 vdc Water Detection Module - 24 vdc

5A		Bowl Gasket - Included in 4A
5B	RK 11-1938	Bowl Kit - Includes 5A, 5C & 5D
5C	RK 20126	Bowl Plug (O-ring Included in 4A)
5D		Self-venting Drain (O-ring Included in 4A)

6A	2020V2	1000FH Replacement Element 2 micron
	2020V10	1000FH Replacement Element 10 micron
	2020V30	1000FH Replacement Element 30 micron



Online Link Turbine Series Selector



Online Link Turbine Series Replacement Parts Selector