

Together, we can
control the motion
of the world,
whichever direction
it's spinning.



3-Way Solenoid Valves

Parker FCD provides a wide range of 3-way solenoid valve solutions for directional flow control for instrumentation, valve actuation, cylinder control, dispensing equipment, and compressors. Available in stainless steel, brass, and aluminum with coil options to meet most industry requirements.



POWER GENERATION • CHEMICAL PROCESSING • OIL & GAS • PHARMACEUTICAL • PULP & PAPER •
FOOD & BEVERAGE • FACTORY AUTOMATION



ENGINEERING YOUR SUCCESS.

3-Way Solenoid Valves

	Range	
Port Sizes (NPT)	1/8"	3/4"
Orifice Sizes	1/32"	3/4"
Pressure Rating	Vacuum	1,100 psi
Flow Factors (Cv)	0.02	7.3
Media Temperature	-40°F	240°F
Ambient Temperature	-40°F	180°F
Function	3-Way, 2 Position, Normally Open, Normally Closed, Universal	
Body Material	Stainless Steel, Brass, Aluminum	
Application Specific	Quick Exhaust, High Pressure, Manifold Mount, Direct NAMUR Mount, Manual Reset, Manual Override	



Parker Hannifin Corporation
Fluid Control Division
 1 800 825 8305
www.parker.com/fcd