

Together, we can
meet demanding
applications from
the smallest lab to
the largest ocean.



4-Way Solenoid Valves

Parker FCD's 4-way solenoid valves come in pipe mount and direct NAMUR mount for double-acting valve actuators. Highly engineered and specification grade, they perform in temperatures as low as -40°F. Coupled with hazardous location coils, they're pure "high performance."



OIL & GAS • INSTRUMENTATION • LIFE SCIENCE • FOOD & BEVERAGE • TRANSPORTATION • ASSEMBLY CELLS •
CONTROL PANELS • DIAGNOSTICS • COMPRESSORS • FUEL DISPENSING • INDUSTRIAL & COMMERCIAL EQUIPMENT



ENGINEERING YOUR SUCCESS.

4-Way Solenoid Valves

	Range	
Port Sizes (NPT)	1/8"	1/2"
Orifice Sizes	3/64"	5/8"
Pressure Rating	Vacuum	150 psi
Flow Factors (Cv)	0.05	4.0
Media Temperature	-40°F	240°F
Ambient Temperature	-40°F	167°F
Function	4-Way, 2 and 3 Position, Normally Open, Normally Closed, Dual Position	
Body Material	Stainless Steel, Brass, Aluminum	
Application Specific	Direct NAMUR Mount, Manual Override	



Parker Hannifin Corporation
Fluid Control Division
 1 800 825 8305
www.parker.com/fcd