

ParFit Fuel Filters

PFF296 and PFF297



For on or off-highway vehicles and stationary equipment, ParFit fuel filters protect expensive system components from microscopic solid contaminants and damaging water. ParFit filters are engineered and manufactured to meet stringent quality requirements and OEM (Original Equipment Manufacturer) specifications for correct fit, long service life, and performance.

Every ParFit fuel filter contains one of three media grades developed for optimum performance and versatility. Each media grade was laboratory tested to SAE standards to guarantee the best cost/performance value. ParFit fuel filters are Racor quality in an effective, all-in-one, spin-on package.



Contact Information:

Parker Hannifin Corporation
Racor Division
P.O. Box 3208
3400 Finch Road
Modesto, CA 95353

phone 800 344 3286
209 521 7860

fax 209 529 3278
racor@parker.com

www.parker.com/racor
www.parker.com/racorproducts

Product Features:

- ISO 9002 certified manufacturing practices ensures superior quality.
- Filter media specified by Racor filtration experts.
- Better engine protection compared to other brands.
- High contaminant capacity.
- 5 micron media.
- Suitable for high pressure injection systems.
- Water stripping filter media is rated at 98% efficient.
- Performance meets or exceeds OEM specifications.



ENGINEERING YOUR SUCCESS.

PFF296 Cross Reference Information

If you have any of these filters, use the premium Racor PFF296 filter instead.

| Ford Motor Co. | | Massey Ferguson | | International Harvester | |
|----------------|---------------|-----------------|-------------|-------------------------|-------------|
| 134827 | C5NE-9176-A | 57766 | 1076810M1 | 306975 | 765051-C91 |
| 500625 | C5NE-9176-C | 151890 | 114924188 | 765051 | 765051-R91 |
| 1423477 | C7NN-9176-A | 504239 | 151890-M1 | 765951 | 765951-C91 |
| 1582261 | C7TF-9365-C | 835944 | 1049939M91 | 796051 | 765951-R91 |
| 1583371 | C7TZ-9365-A | 835994 | 1049939T91 | 2656621 | 796051-R91 |
| 1635103 | C7TZ-9365-C | 851890 | 1077260M91 | 3044506 | 7960521R91 |
| 1700328 | C9TZ-9365-A | 870971 | 1712202-M1 | 3062788 | 796460-R91 |
| 2914074 | D0NN-9176-B | 890971 | 1802271-M1 | 3069205 | 796951-R91 |
| 3914074 | D2NN-9176-A | 960689 | 1841890-M1 | 3602788 | 3043645-R91 |
| 5010518 | D9FL-9150-B | 1021350 | 1851890-M1 | 76951R91 | 3044106-R91 |
| 5020289 | D0NN-9176-B | 1021351 | 1896096-M1 | 1133280R1 | 3044506-R91 |
| 5029459 | 2701E-9150-A | 1640997 | 1896247M91 | 218577-A1 | 3044506-R92 |
| 5038883 | 2701E-9150-B | 1712202 | 1951890-M1 | 306975-R1 | 3044506-R93 |
| 6130357 | 2701E-9176-B | 1802271 | 2871492-M1 | 304405-R91 | 3044506-R94 |
| 6130358 | 775F-9150-AA | 1841890 | 3405418-M1 | 3062788R91 | 3069205-R91 |
| 6149716 | C5NE-9176-AC | 1896096 | 835994-M91 | 3069205-R1 | 3134477-R91 |
| 6149717 | D0NN-9N074-B | 2650017 | 835994-M92 | 306975-R91 | 3144477-R91 |
| 6161789 | D8NN-9N074-A | 2656613 | 836218-M91 | 757836-R91 | 3144477-R92 |
| C5N9176A | D0NN-9N074-B | 2656621 | 851890-M91 | | |
| C5N9176C | E7NN-9176-AA | 26540017 | 883786-M91 | | |
| C5NE-9176 | 825F-9150-A2A | 26560017 | 1640997-M91 | | |
| 2704E-9150 | D8NN-9N074-AA | 26560110 | 1841890-M91 | | |
| C5NE-9167-A | EDPN-9N074-AA | 26561117 | 1896074-M91 | | |
| | | 1013891M1 | 1896096-M91 | | |
| | | 1024386M1 | 3438731-M91 | | |
| | | 1049939M1 | | | |

| Volvo | | Motorcraft | | Alfa Romeo | Allis Chalmers | | BOSCH | | |
|---------|----------|------------|---------|-------------------|----------------|------------|---------------|---------------|-------------------|
| 233628 | 7236628 | EFG3 | FL157 | 105-64-040601 | 78981 | 251397-5 | 74014 | 1-457-434-087 | 1-457-434-909 |
| 236628 | 236628-4 | EFG5 | AFD157 | 105-64-060001 | 251397 | 251397-6 | N4201 | 1-457-434-201 | 1-457-434-910 |
| 858201 | 62115852 | FG25 | EFG296 | 105-64-060002 | 252050 | 70251397 | BDF4201 | 1-457-434-900 | 9-451-733-000 |
| 6211585 | 66136656 | FG38 | EFG315 | 105-64-040601 | 2099490 | 71206239 | 1-457-429-215 | 1-457-434-901 | 9-455-160-246 |
| 6613665 | 66488453 | EFG88 | SFG103 | 105-64-0406001 | 4060050 | 1005069-8 | 1-457-429-219 | 1-457-434-902 | 9-879-993-036 |
| 6648845 | 79055273 | FD157 | FD157FP | 105-64-0406002 | 4490296 | 1005078-8 | 1-457-434-011 | 1-457-434-903 | 1-457-434-900-850 |
| | | | | 105-64-0406001-02 | 4621740 | 1005078-9 | 1-457-434-016 | 1-457-434-904 | 1-457-434-900-867 |
| | | | | | 9924318 | 4060050-4 | 1-457-434-017 | 1-457-434-905 | 1-457-434-905-850 |
| | | | | | | 70251397-9 | | | |

| Lucas | John Deere | Fram | AC Delco | General Motors | | Iveco | | Kubota | Koehring | Manitou |
|--------|------------|---------|----------|----------------|----------|---------|---------|-------------|----------|---------|
| L296F | AT13387 | C4155 | ACD51 | 813561 | 7965190 | 1901629 | 4651986 | 15451-43560 | 3041R91 | 26513 |
| L296FE | AT17387 | C1191-A | ACD59 | 813562 | 7973058 | 1901687 | 4669550 | 70000-14632 | 8030104 | 49660 |
| | AT17387T | C1191PL | ACD159 | 983883 | 7984288 | 4261739 | 4680444 | 70000-37500 | 8320243 | 105615 |
| | | | ACD173 | 983884 | 9974348 | 4561986 | 9918114 | Z14FF-10044 | 8825183 | 138196 |
| | | | TP1228 | 6371716 | 9975348 | 4612227 | 9918144 | | 8825380 | 171547 |
| | | | | 7371716 | 25166009 | 4621540 | 9918184 | | | 473037 |
| | | | | | | 4621740 | 9924318 | | | |

| Mopar | Nissan | Owatonna | New Holland | Napa Gold | Purflux | Purolator | | CASE | |
|---------|------------|-----------|-------------|-----------|---------|-----------|---------|---------|-------------|
| L311 | 11492-4188 | 425-32331 | 500625 | 3142 | CS155 | KX23 | MFF629 | 915319 | K915319 |
| 2236295 | | 425-32607 | 505776 | 3166 | CS157 | T149 | PED116 | 951319 | K960911 |
| | | | 730755 | 3166MP | CS159 | F50149 | PM4020 | 960911 | 1502155-C91 |
| | | | 83937061 | | CS157A | F50155 | MFF516A | E36623 | 3044506-R91 |
| | | | | | | F57629 | MFF629A | K62594 | 3044506-R93 |
| | | | | | | MF629A | MFF629F | K906708 | |

| Fleetguard | Agco | Baldwin | Bedford | Chamberlain | Champion | Chrysler | Coopers | Cummins | Daewoo |
|------------|------------|---------|---------|-------------|------------|----------|---------|---------|-----------|
| FF167 | 70251397 | BF825 | 6371716 | 26259 | L131 | L311 | G629 | 3937061 | 2474-6017 |
| LF4052 | 70251397-9 | | 7371716 | 65507 | L137 | 601980 | AZF015 | | |
| FF167-A | | | 7988149 | 2650017 | LABS 296F | 2236295 | AZF100 | | |
| LF4052A | | | | | LABS L296F | 5038883 | AZF101 | | |

And Many More...

PFF297 Cross Reference Information

If you have any of these filters, use the premium Racor PFF297 filter instead.

| Volvo | Ford Motor Co. | Massey Ferguson | Wix | Purolator | Perkins | Renault | FIAT | BOSCH |
|-----------|----------------|-----------------|----------|-----------|----------|------------|---------|-------------------|
| 3210209 | 3917626 | 26560602 | 2027P | KX24 | 265088 | 3052535 | 1930255 | N4200 |
| 4785391 | 5011306 | 26566602 | 2030P | F53135 | 2650097 | 3082657 | 1930277 | 1-457-429-678 |
| 32102097 | 78GB-9150-AA | 189287-M91 | 33142 | PF3131 | 26560602 | 6005000895 | 5984018 | 1-457-434-200 |
| 119933786 | D8NN-9176-AA | 3405419-M1 | 33166 | PF3135 | 26560607 | 6005007410 | 5984019 | 9-455-160-328 |
| 119990661 | A830X-9150-JA | 3621009-M1 | 33166MP | MFF783A | 26566602 | 7701028181 | 9939229 | 1-457-429-678-650 |
| | | 1896287-M91 | CW1172MP | | | | | |
| | | 1896432-M91 | | | | | | |
| | | 3405419-M91 | | | | | | |

| Luber Finer | Motorcraft | General Motors | Fleetguard | Fram | PURFLUX | Sakura | White | Greyfriars | AC Delco |
|-------------|------------|----------------|------------|-------|---------|---------|-----------|------------|----------|
| L3569F | FD83 | 7984781 | FF4052 | C1114 | CS178 | FC2101 | 266526 | 458F | TP942 |
| LFP637 | EFG24 | 25011197 | FF5002 | C4161 | CA178A | FC5105 | 266536 | 658P | ACD519 |
| LFF3501 | EFG77 | 25011198 | FF4052-A | C4163 | CS178A | FC-5101 | 266536-AS | | 89028792 |
| LFP637F | FD810 | | | | | | | | |
| | MFD-810 | | | | | | | | |

| Hercules | Coopers | Citroen | C.A.V. | Big A | AP-Lockheed | American Parts | Mann & Hummel | Kralinator |
|----------|---------|----------|----------|-------|-------------|----------------|---------------|------------|
| 266526 | G912 | 594734 | 699 | 576 | LK783 | 574 | P945 | F963 |
| 266536 | AZF029 | 95503693 | 796 | 95163 | LK3764 | 576 | P9451 | F964 |
| 266536AS | AZF086 | 95583693 | 7176902 | 95196 | APF783A | | P945X | |
| | | | 7111-699 | | | | | |
| | | | 7111-796 | | | | | |

| Donaldson | Baldwin | John Deere | Napa Gold | Vapomatic | Knecht | Caterpillar | RYCO | Hastings Premium | Quaker State |
|-----------|---------|------------|-----------|-----------|--------|-------------|--------|------------------|--------------|
| P556287 | BF874 | AP29320 | 3163 | VPD6004 | DF21 | 2W3236 | R2388P | FF836 | QSC1114 |
| P779330 | BF884 | | 3196 | VPD6022 | KX24 | | | FF856 | |

| M Filter | Mahle | Manitou | Lister | LTH | Lamborghini | Harmo | Guiot |
|----------|-------|---------|---------|----------|-------------|-------|--------|
| MP432 | KX24 | 138196 | 397-512 | LTH297BD | 243191301 | P289 | GC1032 |

| Giesse | G.U.D. | Fispa | Fiaam | Dorman | General Electric | Crosland | Continental (Mexico) |
|--------|--------|--------|--------|---------|------------------|----------|----------------------|
| NH118 | G912 | FNC052 | FP4779 | JV429-4 | JV4294 | 620 | PC-4163 |

| Sullair | Talbot | Unipart | Vm Engines | Motaquip | Hanomag-Henschel | Hengst | Champion |
|---------|----------|---------|------------|----------|------------------|--------|----------|
| 40990 | 941392 | GFE5006 | 4531059 | VFF104 | 26560602 | E761K | L132 |
| 40992 | 75066000 | GFE5298 | 45310059A | VFF114 | | | |

| AGCO | ACT | Agrifur | ALCO | Allis Chalmers | Arctic Traveler | ATSA | Carrier-Transcold |
|----------|---------|----------|-------|----------------|-----------------|----------|-------------------|
| 72257868 | FPF-010 | 73029050 | MD195 | 4490295 | 4490295 | ATC-4163 | 941392 |

| Coles | Clean | Clark | Hymac | IVECO | PBR | Pegaso | Colt Industries |
|---------|-------|--------|---------|---------|--------|--------|-----------------|
| 8772571 | DN222 | 961048 | 2700216 | 1930277 | AG3207 | 197785 | 21367 |

And Many More...

Parker Hannifin Corporation
Filtration Group
Global Headquarters
 6035 Parkland Boulevard
 Cleveland, OH 44124-4141
 T 216 896 3000, F 216 896 4021
www.parker.com

North America

**Compressed Air Treatment
 Filtration & Separation/Balston**
 242 Neck Road
 Haverhill, MA 018350723
 T 978 858 0505, F 978 858 0625
www.parker.com/balston

Filtration & Separation/Finite
 500 Glaspie Street, PO. Box 599
 Oxford, MI 483715132
 T 248 628 6400, F 248 6281850
www.parker.com/finitefilter

Airtek
 4087 Walden Avenue
 Lancaster, NY 14086
 T 716 685 4040, F 716 685 1010
www.airtek.com

domnick hunter NA Sales Co.
 5900-B Northwoods Parkway
 Charlotte, NC 28269
 T 704 9219303, F 704 921-1960
www.domnickhunter.com

Engine Filtration & Water Purification

Racor
 3400 Finch Road, PO Box 3208
 Modesto, CA 95353
 T 209 521 7860, F 209 529 3278
www.parker.com/racor

Racor
 850 North West St., PO Box 6030
 Holly Springs, MS 38635
 T 662 252 2656, F 662 274 2118
www.parker.com/racor

Racor
 302 Parker Drive
 Beaufort, SC 29906
 T 843 846 3200, F 843 846 3230
www.parker.com/racor

Racor -- Village Marine Tec.
 2000 West 135th Street
 Gardena, CA 90249
 T 310 516 9911, F 310 538 3048
www.villagemarine.com

Hydraulic Filtration

Hydraulic Filter
 16810 Fulton County Road #2
 Metamora, OH 435409714
 T 419 644 4311, F 419 644 6205
www.parker.com/hydraulicfilter

Process Filtration

Process Advanced Filtration
 2340 Eastman Avenue
 Oxnard, CA 93030
 T 805 604 3400, F 805 604 3401
www.parker.com/processfiltration

© 2009 Parker Hannifin Corporation
 7800 Rev - (May 2009)

Europe

**Compressed Air Treatment
 domnick hunter Industrial**
 Dukesway, Team Valley Trading Estate
 Gateshead, Tyne & Wear
 England NE11 OPZ
 T +44 (0) 191 402 9000,
 F +44 (0) 191 482 6296
www.domnickhunter.com

**Hiross Zander
 Padova Business Unit**
 Strada Zona Industriale 4
 35020 S. Angelo di Piove Padova, Italy
 T +39 049 9712 111, F +39 049 9701 911
www.dh-hiross.com

**Hiross Zander
 Essen Business Unit**
 Zander Aufbereitungstechnik GmbH
 Im Teelbruch 118
 D-45219 Essen, Germany
 T +49 2054 9340, F +49 2054 934164
www.zander.de

Parker Gas Separations
 Oude Kerkstraat 4
 P O Box 258
 4870 AG Etten- Leur, Netherlands
 T +31 76 508 5300, F +31 76 508 5333

Engine Filtration & Water Purification

Racor
 Shaw Cross Business Park
 Churwell Vale Dewsbury,
 WF12 7RD England
 T +44 (0) 1924 487000,
 F +44 (0) 1924 487038
www.parker.com/rfde

Racor Research & Development
 Parker Hannifin GmbH & Co KG
 Inselstrasse 3 – 5
 70327 Stuttgart Germany
 T +49 (0)711 7071 290-0,
 F +49 (0)711 7071 290 -70
www.parker.com/racor

Hydraulic Filtration

Hydraulic Filter
 Stieltjesweg 8, 6827 BV
 P.O. Box 5008 6802 EA
 Arnhem, Holland
 T +31 26 3760376, F +31 26 3643620
www.parker.com/eurofilt

Urjala Operation, Finn Filter
 Salmentie 260
 31700 Urjala as Finland
 T +358 20 753 2500, F +358 20 753 2501
www.parker.com/fi

Condition Monitoring Center
 Brunel Way Thetford,
 Norfolk IP 24 1HP England
 T +44 1842 763299, F +44 1842 756300
www.parker.com/cmcc

**Process Filtration
 domnick hunter Process**
 Durham Road, Birtley Co. Durham,
 DH3 2SF England
 T +44 (0) 191 410 5121,
 F +44 (0) 191 410 5312
www.domnickhunter.com

Asia Pacific

India
 Plot EL 26, MIDC, TTC Industrial Area
 Mahape, Navi Mumbai 400 709 India
 T +91 22 5613 7081, 82, 83, 84, 85
 F +91 22 2768 6618 6841
www.parker.com/india

Japan
 626, Totsuka-cho, Totsuka-ku
 Yokohama-shi, 244-0003 Japan
 T +81 45 870 1522, F +81 45 864 5305
www.parker.com/japan

Korea
 1-C Block, Industrial Complex of Jangan,
 615-1, Geumui-Ri Jangan-Myeon,
 Hwaseong-City Gyeonggi-Do, Korea
 T +82 31 359 0771, F +82 31 359 0770
www.parker.com/korea

**Malaysia
 domnick hunter**
 Lot 558A, Jalan Subang 3
 Off Persiaran Subang
 Sungai Penaga Industrial Park
 47610 Subang Jaya
 Selangor Darul Ehsan, Malaysia
 T +60 3 5638 1476, F +60 3 5638 1527
www.parker.com/malaysia

Shanghai
 280 YunQiao Road
 JinQiao Export Processing Zone
 Shanghai 101206 China
 T +86 21 5031 2525, F +86 21 5834 3714
www.parker.com/china

Singapore
 No. 11 4th Chin Bee Road
 Jurong Town, Singapore 619702
 T +65 6887 6330, F +65 6261 4929
www.parker.com/singapore

Thailand
 1023 3rd Floor, TPS Building
 Pattanakam Road, Suanluang,
 Bangkok 10250 Thailand
 T +66 2717 8140, F +66 2717 8148
www.parker.com/thailand

Latin America

**Parker Comercio Ltda.
 Filtration Division**
 Estrada Municipal Joel de Paula
 900 Eugenio de Melo,
 Sao Jose dos Campos
 CEP 12225390 SP Brazil
 T +55 12 4009 3500, F +55 12 4009 3529
www.parker.com/br

Africa

Parker Hannifin Africa Pty Ltd
 Parker Place, 10 Berne Avenue,
 Aeroport Kempton Park,
 1620 South Africa
 T +27 11 9610700, F +27 11 3927213
www.parker.com/eu

