



# Premium Elastic Sealant Cords and Slugs



Virginia Premium Elastic Sealant is a non-hardening, water-resistant compound specifically formulated to exclude moisture, dust, and dirt from joints, seams and openings in a wide range of applications. Virginia Premium Elastic Sealant is pliable and can be easily manipulated to take on virtually any form. This product adheres to most clean surfaces allowing for use with a wide variety of materials. Virginia Premium Elastic Sealant is excellent for use in sealing refrigerated cases and around window air conditioners. Constant exposure to extreme conditions encountered by over the road trailers and motor homes is another difficult problem solved with Virginia Premium Elastic Sealant. This product has an operating temperature range from -30°F to 158°F (-34°C to 70°C) and is off-white in color, allowing it to virtually disappear in most applications.



## Characteristics:

- Seals out moisture, dust and dirt.
- Resistant to water, water vapor, temperature, alcohol, and mild acids or caustics.
- Service temperature range from -30°F to 158°F (-34°C to 70°C).
- Excellent adhesion to wood, metal, plastics, glass, as well as many other surfaces.
- Off-white color.
- Non-staining, non-drying.

## Uses:

Any application which requires moisture, dust and dirt to be sealed out and where ease of application is an important consideration.



ENGINEERING YOUR SUCCESS.



# Premium Elastic Sealant Cords and Slugs

## Suggested Application

### Instructions:

1. Adhering surfaces should be clean and dry.
2. Place Virginia Premium Elastic Sealant over opening to be sealed and gently press into place with thumbs.

## Specifications:

Base	Non-drying synthetic polymers
Filler	Inert materials (contains no asbestos)
Color	Off-white
Odor	Non contaminating to sweet butter
Shrinkage	Nil
High resistance to	Water, water vapor, physical shock, alcohol, mild acids and caustics

## Cautionary Notes:

Refer to MSD sheet for further information. MSD sheets are available at your local wholesaler.

## Package Sizes Available:

Virginia Premium Elastic Sealant is available in cords or slugs. Cords are available in 100 foot rolls of 3/16" diameter gum or in 25 foot rolls of 3/8" diameter gum. Slugs are available in 2 lb. boxes.

**NON-WARRANTY** – All data, statements and recommendations contained herein are based upon the best information available and are believed to be reliable. However, no warranty, either expressed or implied, is made concerning the application of this product since the customer's use cannot be controlled. Statements concerning the use of this product should not be construed as suggestions, recommendations or inducements that it be used in violation of patent rights or in violation of any applicable laws or regulations. Product improvement is a continuous process at Virginia, therefore, product specifications may change without notice.

