










Service Kits

	Description	P31	P32	P33
Air Preparation Products	Panel mount (plastic)	P31KA00MP	P32KA00MP	P33KA00MP
	Panel mount nut (aluminum)	P31KA00MM	P32KA00MM	P33KA00MM
Global	5µ element kit	P31KA00ESE	P32KA00ESE	P33KA00ESE
	1µ element kit	P31KA00ES9	P32KA00ES9	P33KA00ES9
Prep-Air II	0.01µ element kit	P31KA00ESC	P32KA00ESC	P33KA00ESC
	Adsorber element kit	P31KA00ESA	P32KA00ESA	P33KA00ESA
Miniature	Auto drain kit		P32KA00DA	P32KA00DA
	Differential pressure indicator kit	P31KA00RQ	P32KA00RQ	P32KA00RQ
P3N	Fill plug kit	P31KA00PL	P32KA00PL	P32KA00PL
	Drip control assembly kit	P32KA00PG	P32KA00PG	P32KA00PG
General Industrial	Plastic bowl w/ bowl guard & manual drain	P31KA00BGM	P32KA00BGM	P33KA00BGM
		P31KA00BGB		
Stainless Steel	Plastic bowl w/ bowl guard & pulse drain		P32KA00BGA	P33KA00BGA
		P31KA00BGN	P32KA00BGN	P33KA00BGN
Precision / Proportional	Metal bowl w/o sight gauge & manual drain	P31KA00BMM	P32KA00BMM	P33KA00BMM
		P31KA00BMB		
Bulk Liquid Separators	Metal bowl w/o sight gauge & pulse drain		P32KA00BMA	P33KA00BMA
		P31KA00BMN		
Bulk Liquid Separators	Metal bowl w/ sight gauge & manual drain		P32KA00BSM	P33KA00BSM
			P32KA00BSA	P33KA00BSA
Bulk Liquid Separators	Metal bowl w/ sight gauge & auto drain		P32KA00BSN	P33KA00BSN
		P31KA00BSN		

Most popular.



Service Kits

Port size	Description	P31	P32	P33
	Regulator - relieving repair kit	P31KA00RB	P32KA00RB	P33KA00RB
	Regulator - non relieving repair kit	P31KA00RC	P32KA00RC	P33KA00RC
	Regulator - main adjusting spring 0-2 bar (0-30 PSIG) kit	P31KA00PR	P32KA00PR	P33KA00PR
	Regulator - main adjusting spring 0-4.1 bar (0-60 PSIG) kit	P31KA00PS	P32KA00PS	P33KA00PS
	Regulator - main adjusting spring 0-8.6 bar (0-125 PSIG) kit	P31KA00PT	P32KA00PT	P33KA00PT
	Regulator - main adjusting spring 0-17 bar (0-250 PSIG) kit		P32KA00PV	P33KA00PV
	Square flush mount gauge kit	0-4 bar	K4511SCR04B	
		0-11 bar	K4511SCR11B	
		0-60 PSIG	K4511SCR060	
		0-160 PSIG	K4511SCR160	
	1.00" round gauge	0-60 PSIG / 0-4.1 bar	K4510N18060	
		0-160 PSIG / 0-10 bar	K4510N18160	
	40mm round gauge (Not for use with common port regulators)	0-30 PSIG / 0-2 bar	K4515N18030	
		0-60 PSIG / 0-4.1 bar	K4515N18060	
		0-160 PSIG / 0-10 bar	K4515N18160	
	50mm round gauge	0-30 PSIG / 0-2 bar	K4520N14030	K4520N14030
		0-60 PSIG / 0-4.1 bar	K4520N14060	K4520N14060
		0-160 PSIG / 0-10 bar	K4520N14160	K4520N14160
		0-300 PSIG / 0-20 bar	K4520N14300	K4520N14300
	44mm (1-3/4") digital round	0-160 PSIG / 0-11 bar / 0-1.1 MPa	K4517N14160D	K4517N14160D
	Body connector o-ring (spares kit) (pack of 10)	P31KA00CY	P32KA00CY	P33KA00CY
	Tamperproof knob kit	P31KB00AT	P32KB00AT	



Air Preparation Products

Global

Prep-Air II

Miniature

P3N

General Industrial

Stainless Steel

Precision / Proportional

Bulk Liquid Separators

 Most popular.

