

# Parflex® Spiral Guard™

Prevent premature hose wear.



When it comes to protecting hoses, Parflex Spiral Guard™ delivers the ultimate in abrasion resistance, crush resistance, flexibility and strength. In addition, the exceptionally smooth facing and rounded edges prevent the guard from getting caught on rough surfaces.

Although Parflex Spiral Guard™ was designed for protection, it is also used for bundling and organizing. It easily slips over the end of your hose or can be quickly wound around the hose if fittings are present. Ultimately, Parflex Spiral Guard™ delivers more advantages than cut pipe or sleeving protection at a competitive price and often, lower price.

Parflex Spiral Guard™ is available in 2 styles:

- a standard version (with yellow stripe) for above ground applications not requiring fire-resistant, anti-static properties
- an MSHA/FRAS approved version for underground mining, aircraft refueling, and similar restricted applications

Sizes range from 12mm to over 150 mm O.D.

## Contact Information: Product Features:

Parker Hannifin Corporation  
**Parflex Division**  
1300 North Freedom St.  
Ravenna, OH 44266  
**phone 330 296 2871**  
**fax 330 286 8433**  
[www.parker.com/parflex](http://www.parker.com/parflex)

- High abrasion protection
- Exceptional anti-crush performance
- Does not get caught on surfaces
- Lightweight
- Easy installation and routing - can be installed/replaced without removing hose from equipment
- Self-lubricating interior minimizes wear on hose

- Does not require clamping and it does not bunch up
- Excellent bend radius
- Low profile
- Allows easy monitoring for leaks
- MSHA/FRAS approved version available



ENGINEERING YOUR SUCCESS.

# Parflex® Spiral Guard™

Multi-advantage line protection in standard and MSHA/FRAS.

Save on replacing expensive, high-maintenance lines with the most advantages in line protection. For complete details on Parflex Spiral Guard, call 330.296.2871 or visit [www.parker.com/parflex](http://www.parker.com/parflex) today.

## Ordering Information

PSG - Spiral Guard is available in these sizes



Product Code	Hose O.D. Range	Carton Quantity	1-Wire Braid Size	2-Wire Braid Size	Multispiral Size
Part Number	MM	M	Inch	Inch	Inch
PSG 12	10-13	20	-	-	-
PSG 16 or PSG FRAS 16	12-17	20	1/4"	1/4"	-
PSG 20 or PSG FRAS 20	16-22	20	3/8"	1/4", 3/8"	3/8"
PSG 25 or PSG FRAS 25	22-28	20	1/2", 5/8"	1/2", 5/8"	1/2", 5/8"
PSG 32 or PSG FRAS 32	27-33	20	3/4"	5/8", 3/4"	3/4"
PSG 40 or PSG FRAS 40	33-42	20	1"	1"	1"
PSG 50 or PSG FRAS 50	42-55	20	1-1/4", 1-1/2"	1-1/4"	1-1/4"
PSG 63 or PSG FRAS 63	52-65	20	2"	1-1/2"	1-1/2"
PSG 75 or PSG FRAS 75	65-80	10	-	2"	2"
PSG 90 or PSG FRAS 90	80-150	10	-	-	-
PSG 110 or PSG FRAS 110	150-above	10	-	-	-

