



9200 Series Replacement Parts

Body Size	Part Number	Description	Weight (lbs.)
1/2	50001-211-0260	Interface O-Ring	.01
1/2	92-805-L4	Replacement Lever (Left hand)	.23
1/2	92-805-R4	Replacement Lever (Right hand)	.23
1/2	92-806-4	Replacement Yellow Grip (Left hand)	.01
1/2	92-807-4	Replacement Red Grip (Right hand)	.01
1/2	92-813-4	Replacement Black Grip (Right hand)	.01
1/2	92-814-L4	Replacement Cam Stop (Left hand)	.01
1/2	92-814-R4	Replacement Cam Stop (Right hand)	.01
1/2	92-906-4A	Wave Washer	.01

9200 Series Accessories

Body Size	Part Number	Clamp Type
1/2	9006-4	Breakaway - double
1/2	9507-4-1H	Automatic Dust Cover

NOTE: 9507-4-1H automatic dust cover cannot be used without the 9006-4 clamp.

9200 Series Dust Caps and Plugs

Body Size	Dust Cover	Color/Material	Nipple Dust Cap	Weight (lbs.)
1/2	9507-4-1	Black Rubber	5209-4M	.04

NOTE: 9507-4-1 rubber dust cover can be used with or without the 9006-4 clamp.





9500 Series Kits combines two color coded 9250 couplers with a 9006-4 clamp and dust protection. The dust covers automatically close when the male tip is removed and are color coordinated with the coupler lever handles to easily identify raise and lower lines. The 9502 Series Kits are preassembled and ready for use. 9250 couplers accept 8010 (ISO 5675) tips and are not included with the kit.

Kit contents:

- (1) 9250 Coupler (right hand orientation)
- (1) 9250 Coupler (left hand orientation)
- (1) 9006-4 Clamp Assembly
- (1) 9507-4-1H Automatic Dust Cover Assembly



Quick Couplings

Open Position



9250 Series

By turning the rugged, color-coded lever to "Open" you lock open the valves in both the female body and the male tip, so they are unaffected by rapid variations in fluid flow.

Turning the lever to Open without a male tip in place will not result in oil flow. The 9250 Series design prevents this from happening.

Valves will close automatically in the case of a breakaway.

Closed Position



9250 Series

In the Closed position the 9250 shuts off oil flow at the remote outlet. This allows for easy, sprayless, zero-pressure connecting or disconnecting and for additional safety when working on an implement.

Levers are color-coded to identify Raise and Lower lines.

Body Size	Part Number	Port End	Description	Rated Pressure (psi)	Sleeve Diameter	Flats	Clamp	Dust Cover
1/2	9500-4	1/2-14 NPTF	Kit	3000	1.50	1.13	9006-4	9507-4-1H
1/2	9500-16	7/8-14 ORB	Kit	3000	1.50	1.13	9006-4	9507-4-1H
1/2	9502-4	1/2-14 NPTF	Kit (assembled)	3000	1.50	1.13	9006-4	9507-4-1H



Catalog 3900 - Agricultural Coupling Clamps

5001-4 Single breakaway clamp	
	Designed for use with all Pioneer couplers having a 1-1/2" diameter sleeve (1/2" body size). Yokes and braces are heavy duty metal stampings.
5006-4 Double breakaway clamp	
	Designed for use with all Pioneer couplers having a 1-1/2" diameter sleeve (1/2" body size). Yokes and braces are heavy duty metal stampings.
9006-4 Double breakaway clamp	
	Designed for use with 9250 lever couplers. Steel material bar with heavy duty diecast yoke.

