

PRO-SHIELD® 7058

Two Component Easy To Use Conductive Epoxy Adhesive

Parker Chomerics PRO-SHIELD 7058 is a two-component, silver filled conductive epoxy adhesive system designed for applications where a strong, highly conductive electrical bond must be achieved.

PRO-SHIELD 7058 is recommended for relatively small bond lines but can be used for larger bond lines in applications where vibration or potential for cracking is not an issue. It is a good choice for precise application in and around tight spaces and electrical components.

Curing can be achieved in as little as 15 minutes. Typical applications include bonding and grounding of electrical components, cold soldering, and bonding and sealing machined enclosures.




Product Features

- Two component silver filled epoxy
- Thin paste
- Low VOCs
- Minimal shrinkage
- Excellent conductivity 0.005 ohm-cm
- 30 minute working life, works well over wide temp. ranges
- Good chemical resistance >1000 psi lap shear
- Good for permanently bonding surfaces

Typical Applications

- Electrical grounding of surfaces between metallic surfaces
- Cold soldering
- Bonding and sealing of machined electrical enclosures



PRO-SHIELD® 7058 Product Information

Typical Properties	Typical Values	Test Method
Packaging	50cc dual mix syringe	N/A
Primer Included	N/A	N/A
Polymer Family	Epoxy	N/A
Filler Material	Silver	N/A
Color	Silver	N/A
Volume Resistivity (OHM/cm)	0.005	N/A
Nominal Hardness (Shore D)	80	N/A
Lap Shear Strength, KPA (PSI)	6895 (1000)	CHO-TM-TP11
Calculated VOC (g/L)	1	Calculated
Theoretical coverage at 1 mil (ft ² /gal)	1603	N/A
Specific Gravity	2.7	ASTM D792
Shelf life, date of manufacture (months)	9	N/A

PRO-SHIELD® 7058 Ordering Information

Product	Weight (grams)	Packaging	Part Number	Primer
PRO-SHIELD 7058	100	50cc dual syringe with mixer	90-05-7058-0000	Not Required



WARNING: This product contains chemicals known by the State of California to cause cancer, birth defects, or other reproductive harm. For more information go to www.P65Warnings.ca.gov



We're Here to Help

Scan QR code or visit parker.com/chomerics to:

- [Request a Free Sample](#)
- [Talk to an Expert](#)
- [Get a Quote](#)
- [Find Where to Buy](#)

Parker Hannifin Corporation
Chomerics Division
77 Dragon Court
Woburn, MA 01801
Phone 781 935 4850
Fax 781 933 4318
chomailbox@parker.com
parker.com/chomerics

CHODS1251 March 2026

©2026 Parker Hannifin Corporation

