


P Series Servo Drive

Pulse Drive Specifications

Motor Output Power		PD-04P	PD-10P	PD-35P
Shaft Power @ Continuous Current		400 Watts	1000 Watts	3500 Watts
Shaft Power @ Peak Current		1200 Watts	3000 Watts	10500 Watts
Drive Output Power				
Continuous Current (RMS)		3.0 Amps	6.75 Amps	16.7 Amps
Peak Current (RMS)		9.0 Amps	20.25 Amps	50.1 Amps
Bus Voltage		340VDC		
Drive Input Voltage		100-120VAC 50/60Hz 230 VAC, 1/3Ø, 50/60Hz	230 VAC, 1/3Ø, 50/60Hz	
Drive Control Voltage		100-120VAC 50/60Hz 230 VAC, 1Ø, 50/60Hz	230 VAC, 1Ø, 50/60Hz	230 VAC, 1Ø, 50/60Hz
Performance				
Servo update		62.5µ seconds		
Accuracy		± 1 encoder count ; encoder dependent		
Commutation		Sinusoidal		
Control				
Indexer Function		64 user defined profiles, relative/absolute moves, registration, sequences and I/O selection		
Position Control		Step and direction, CW and CCW		
Speed Control		+/- 10V, 1:5000		
Torque Control		+/- 10V		
Feedback				
Encoder Input		Quadrature Incremental encoder, BiSS-C (absolute) encoder, EnDAT 2.2		
Encoder Output		RS-422 compatible differential driver		
I/O				
Digital input		16-channel, +24V common, user selectable functions		
Digital output		8-channel, Differential (Isolated), user selectable functions		
Analog input		2-channel, ±10V (max.), 12bits		
Analog output		2-channel, ±10V (max.), selectable, 12bits		
Communications				
USB		USB 2.0 for firmware upload and drive configuration		
Serial		RS422 for PC or HMI interface, MODBUS-RTU		
Standard		ANSI/ TIA/ EIA-422 standard		
Baud Rate		9,600/ 19,200/ 38,400/ 57,600/ 115,200 bps		
Configuration Software		Drive Support Tool		
Standards		CE (EMC, LVD) UL/cUL recognized	CE (EMC, LVD) UL/cUL listed	CE (EMC, LVD) UL/cUL listed
Built-in Functions				
Display		7 Segment LED, 5 digits for Status and Alarms		
Node Selection		3 dip switches, 1 rotary for address 0-31		
Dynamic Braking		Built-in, user selectable reaction		
Internal Regeneration		100 ohm, 50W	40 ohm, 100W	12.6 ohm, 150W
External Regeneration		50 ohm, 140W	30 ohm, 300W	30 ohm, 600W
Environmental				
Temperature		0 - 50 °C (32 - 122 °F)		
Humidity		0 - 90% non-condensing		
Shock / Vibration		15g, 11msec half sign / 10-2,000Hz @ 2g		

Pulse Drive Dimensions



(Unit: mm)

		PD-04P	PD-10P	PD-35P
H	Height	158	158	158
OH	Overall Height	169	169	169
OW	Overall Width	38	58	88
W1	Width 1	6	10	44
W2	Width 2	26	48	44
W3	Width 3	32	42	78
W4	Width 4	6	6	5
D	Depth	107.7	127.7	112.5
OD	Overall Depth	173	197	198

Solid Models Available for Download parkermotion.com/pseries