



aerospace  
climate control  
electromechanical  
filtration  
fluid & gas handling  
hydraulics  
pneumatics  
process control  
sealing & shielding



## Food Transfer Hoses

Sanitary Transfer Solutions from Parker/PAGE



ENGINEERING YOUR SUCCESS.

# Food Transfer Hoses

Sanitary Transfer Solutions from  
Parker/PAGE

## Customer Value Proposition:

Parker/PAGE International's Butyl and Nitrile tube hoses offer reliable solutions for the sanitary transfer of your food and beverage products. Both the FTHB (Butyl) and the FTHN (Nitrile) hose feature a white, seamless, mirror finish tube that resists the collection of bacteria and is very easy to clean. For added strength and durability each hose has a synthetic reinforcement that withstands internal pressures, a helical wire for full vacuum capabilities and a high grade weather and abrasion resistant cover for longevity.

These hoses are excellent choices for applications where preservation of taste, aroma and color are crucial. Typical uses include milk, beer, wine, pharmaceuticals, cosmetics and fruit juice. For applications with edible oils such as peanut, canola or vegetable, the FTHN Nitrile hose is an ideal solution.

Parker/PAGE FTHN products are designed for use with a multitude of high quality crimp fittings.

## Contact Information:

Parker Hannifin Corporation  
**Parker/PAGE International Hose**  
801 Airway Drive, Suite B  
Fort Worth, TX 76106

phone (817) 625-0076 or 800-847-7280  
fax (817) 625-1901 or 888-293-2667  
email [page@parker.com](mailto:page@parker.com)

[www.pageintl.com](http://www.pageintl.com)

## Our Products Meet or Exceed the following Standards:

- PMO (Grade A Pasteurized Milk Ordinance)
- CFIA (Canadian Food Inspection Agency)
- USDA's Dairy Division
- 3A Class II
- NSF



FTHN - White Nitrile Tube with Gray Nitrile Cover and White Stripe

FTHB -White Butyl Tube with Gray EPDM Cover and Blue Stripe

## Hose Specifications

Hose ID	Hose OD	Work Pressure	Min. Burst	Vacuum Rating	Min. Bend Rad.	Weight	Page No.
Inches	Inches	PSI @72°F	PSI @72°F	In. HG @72°F	Inches	Lbs./Ft.	Nitrile Tube
(MM)	(MM)	(Bars @22°C)	(Bars @22°C)	(Kg/Sq.Cm @22°C)	(MM)	(Kgs/M)	(Butyl Tube)
0.50	0.95	350	1400	29.9	2.00	0.37	08-FTHN
(12.7)	(24.1)	(24.1)	(96.5)	(1.0)	(50.8)	(0.55)	(08-FTHB)
0.75	1.25	350	1400	29.9	3.00	0.55	12-FTHN
(19.0)	(31.7)	(24.1)	(96.5)	(1.0)	(76.2)	(0.81)	(12-FTHB)
1.00	1.53	300	1200	29.9	4.00	0.68	16-FTHN
(25.4)	(38.8)	(20.6)	(82.7)	(1.0)	(101.6)	(1.01)	(16-FTHB)
1.25	1.74	250	1000	29.9	5.00	0.95	20-FTHN
(31.7)	(41.2)	(17.2)	(68.9)	(1.0)	(127.0)	(1.41)	(20-FTHB)
1.50	2.13	250	1000	29.9	6.00	1.22	24-FTHN
(38.1)	(54.1)	(17.2)	(68.9)	(1.0)	(152.4)	(1.81)	(24-FTHB)
2.00	2.68	250	1000	29.9	7.00	1.68	32-FTHN
(50.8)	(68.0)	(17.2)	(68.9)	(1.0)	(177.8)	(2.50)	(32-FTHB)
2.50	3.30	150	600	29.9	8.00	2.42	40-FTHN
(63.5)	(83.8)	(10.3)	(41.4)	(1.0)	(203.2)	(3.60)	(40-FTHB)
3.00	3.88	150	600	29.9	9.00	3.15	48-FTHN
(76.2)	(98.6)	(10.3)	(41.4)	(1.0)	(228.6)	(4.68)	(48-FTHB)
4.00	4.98	150	600	29.9	12.00	4.67	64-FTHN
(101.6)	(126.5)	(10.3)	(41.4)	(41.4)	(1.0)	(6.95)	(64-FTHB)
6.00	6.90	100	400	400	29.9	5.15	96-FTHN
(152.4)	(175.3)	(6.9)	(27.6)	(1.0)	(914.4)	(7.66)	(96-FTHB)

Temperature Range: FTHB -40°F to +250°F (-18°C to +121°C) \* FTHN -40°F to +225°F (-18°C to +107°C)

11/07 quantity Printer Bulletin# PAGE-013D



ENGINEERING YOUR SUCCESS.