



# PROSTEEL A Filter Cartridges

- liquid filters
- 316L stainless steel

PROSTEEL A filters provide the ideal solution in applications where traditional polymer based filters are limited by compatibility, exposure time or a combination of high temperature and viscosity.

They are ideally suited to filtration of the solvents used in a wide range of process industries from pharmaceuticals, food & beverage and electronics through to paints and inks. The Parker domnick hunter range of stainless steel filters provides a solution to compatibility issues while maintaining absolute retention ratings down to 3.0 micron. 316L stainless steel fibres are sintered together into a graded pore structure.



The efficiency of the media increases through the filtration bed resulting in excellent dirt holding capacity while maintaining high relative flow rates compared to alternative technology such as sintered powder tubes and metal membranes. The filters are available in two formats both using the same filtration media but one manufactured in a pleated construction and one in a cylindrical wrap. This allows a cost-effective selection depending on flow rate and dirt holding requirements.

## Features and Benefits

- Absolute rated stainless steel liquid filters
- Ideal for aggressive solvents, viscous and hot solutions
- Removal rating 3, 5 and 10 microns
- Compatible with most solvents
- Graded density metal fibre technology provides exceptional dirt holding capacity while retaining excellent flow rates
- Available in two formats; pleated and wrapped, for complete system optimization



## Performance Characteristics



Pleated cartridge flow rates  
10" Size (250 mm) Cartridge

Cylindrically wrapped cartridge flow rates  
10" Size (250 mm) Cartridge

## Specifications

### Materials of Construction

- Filtration Media: 316L Stainless Steel
- Inner Support Core: 316L Stainless Steel
- Outer Protection Cage: 316L Stainless Steel
- End Caps: 316L Stainless Steel
- Standard o-rings/gaskets\*: EPDM
- Assembly Method: TIG Welded

\*All o-rings are manufactured from FDA approved compounds.

### Recommended Operating Conditions

Operating Temperature		Maximum Forward DP		Maximum Reverse DP	
°C	°F	(bar)	(psi)	(bar)	(psi)
200	392	25	364	3	44


Note: The maximum operating temperature is dependant on o-ring selection and properties of the liquid being filtered.

### Effective Filtration Area (EFA)

- ZCCF Cylindrical Wrap  
10" (250 mm) 0.05 m<sup>2</sup> (0.53 ft<sup>2</sup>)
- ZCMF Pleated  
10" (250 mm) 0.13 m<sup>2</sup> (1.39 ft<sup>2</sup>)

### Retention Characteristics

The retention characteristics of the stainless steel filters are determined using ACFTD in accordance with the single pass test ASTM 795-88.



### Dirt Holding Capacity

The table below gives an indication of dirt holding capacity in grams when tested in accordance with the Multipass method ISO 168892.

Type	Micron Rating		
	3.0	5.0	10.0
ZCCF	3.0	3.5	4.0
ZCMF	7.0	7.6	8.4

### Integrity Test Data

The general condition of the cartridge can be tested via the bubble point method. Typical values are detailed in the table below.

Micron Rating	3.0	5.0	10.0
Bubble Point (mbarg)	125.0	76.0	37.0
in Water (psig)	1.78	1.1	0.54

## Ordering Information

ZC


-


-

Code   Type	Code   Length (Nominal)	Code   Micron	Code   Endcap (10")	Code   O-rings				
CF MF	B 2.5" (65 mm) A 5" (125 mm) 1 10" (250 mm) 2 20" (500 mm) 3 30" (750 mm)	003 3.0 µm 005 5.0 µm 010 10.0 µm	B dh DOE C 226 Bayonet	E* EPDM P PTFE Encapsulated Silicone S Silicone V Viton				
All cartridges are supplied as single items.		<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Code   Endcap (Demi)</th> </tr> </thead> <tbody> <tr> <td>T TRUESEAL</td> </tr> <tr> <td>Z Demi A &amp; B Std</td> </tr> </tbody> </table>		Code   Endcap (Demi)	T TRUESEAL	Z Demi A & B Std	*EPDM o-ring supplied as standard without having to specify the 'E' code.	
Code   Endcap (Demi)								
T TRUESEAL								
Z Demi A & B Std								