

HTFL High Temperature Diesel Fuel Line Tubing

Parflex FL Tubing:

Nylon tubing designed for use in tractor, trailer and other mobile fuel systems.

- Heat and light stabilized.
- 100% quality controlled - 100% pressure tested.
- Reduces weight and labor in comparison with hose and hardline tubing.
- For use in D.O.T. diesel fuel applications.
- For use with Parker Prestomatic diesel fuel fittings.
- **Do not exceed temperature and pressure ranges.**

Diesel Fuel Tubing:

Heat and light stabilized seamless extruded nylon core reinforced with fibrous reinforcement and a bonded protective blue nylon cover sheath.

Part No.	Reel Length ft.	Nom. Tube O.D. in.	Nom. Tube I.D. in.	Min. Bend Radius in.	Weight lbs. Per 100 ft.
#					
PFT-4A-XXX-1000-FL	1000	1/4	.170	1.00	1.21
PFT-6B-XXX-500-FL	500	3/8	.251	1-1/2	2.71
PFT-8B-XXX-500-FL	500	1/2	.376	2	3.89
PFT-10B-XXX-250-FL	250	5/8	.441	2-1/2	7.04
PFT-12B-XXX-250-FL	250	3/4	.566	3	8.57

Temperature Range:
-40°F to +200°F (-40°C to +93°C).
Maximum Working Pressure:
150PSI Contact Parflex
Division for application review

xxx represents color code.
Standard color: blue (BLU).
Consult Division for additional colors.

HTFL Diesel Fuel Line Tubing (High Temperature)

Part No.	Nom. Tube O.D. in.	Nom. Tube O.D. in.	Nom. Wall Thickness	Max. Working Pressure at 73° F	Min. Burst Pressure at 73° F PSI	Min. Bend Radius in.	Weight Lbs. Per ft.	Reel Length ft.
#								
HTFL-6B-BRN-500	3/8	.251	.062	175	1,400	1-1/2	.028	500
HTFL-8B-BRN-500	1/2	.376	.062	155	950	2	.039	500
HTFL-10B-BRN-250	5/8	.441	.092	140	900	2-7/8	.071	250
HTFL-12B-BRN-250	3/4	.566	.092	150	800	3	.086	250

Tube: High temperature and chemical resistant special polyamide
Reinforcement: High strength yarn fiber
Cover: High temperature and UV resistant special polyamide

Cover Color: Brown (other colors, contact Parflex)
Temperature Range: -50°F to + 266°F (-46°C + 130°C) 28 inches Hg
Vacuum Rating: 28 inches Hg
Fittings: *Parker NTA series brass compression fittings

Parker Fluid Connectors Group North American Divisions & Distribution Service Centers

Your complete source for quality tube fittings, hose & hose fittings, brass & composite fittings, quick-disconnect couplings, valves and assembly tools, locally available from a worldwide network of authorized distributors.

Fittings:
Available in inch and metric sizes covering SAE, BSP, DIN, GAZ, JIS and ISO thread configurations, manufactured from steel, stainless steel, brass, aluminum, nylon and thermoplastic.

Hose, Tubing and Bundles:
Available in a wide variety of sizes and materials including rubber, wire-reinforced, thermoplastic, hybrid and custom compounds.

Worldwide Availability:
Parker operates Fluid Connectors manufacturing locations and sales offices throughout North America, South America, Europe and Asia-Pacific.

For information, call toll free...

1-800-C-PARKER
(1-800-272-7537)

North American Divisions

Energy Products Division
Stafford, TX
phone 281 566 4500
fax 281 530 5353

Fluid System Connectors Division
Otsego, MI
phone 269 694 9411
fax 269 694 4614

Hose Products Division
Wickliffe, OH
phone 440 943 5700
fax 440 943 3129

Industrial Hose Division
Strongsville, OH
phone 440 268 2120
fax 440 268 2230

Parflex Division
Ravenna, OH
phone 330 296 2871
fax 330 296 8433

Tube Fittings Division
Columbus, OH
phone 614 279 7070
fax 614 279 7685

Distribution Service Centers

Buena Park, CA
phone 714 522 8840
fax 714 994 1183

Conyers, GA
phone 770 929 0330
fax 770 929 0230

Lakeville, MN
phone 952 469 5000
fax 952 469 5729

Louisville, KY
phone 502 937 1322
fax 502 937 4180

Portland, OR
phone 503 283 1020
fax 503 283 2201

Toledo, OH
phone 419 878 7000
fax 419 878 7001
419 878 7420
(FCG Kit Operations)

Canada
Grimsby, ONT
phone 905 945 2274
fax 905 945 3945
(Contact Grimsby for other Service Center locations.)



aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding



Diesel Fuel Solutions



© 2012 Parker Hannifin Corporation

Parker Hannifin Corporation
Fluid System Connectors Division
300 Parker Dr.
Otsego, MI 49078
Phone: 269-692-6555
Fax: 269-694-4614
www.parker.com/fcg

Print Reorder Number
BUL.DF-01

Date of Issue



ENGINEERING YOUR SUCCESS.

Diesel Fuel Fittings Solutions

DF:

- Push-to-Connect Solution
- Elastomeric Seal
- Targeted for tank to firewall and chassis routings
- Not for engine temperatures
- For use with PFTFL tubing
- -40°F to 200°F (-40C to 93C)
- Maximum working pressure 150psi
- Electroless Nickel plated for >20% biodiesel applications



Safe Lock:

- Meets SAE J2044
- Push-to-Connect with locking mechanism
- Operating Pressure up to 72 psi (5 bar)
- Operating Vacuum down to -7.2 psi (-.5 bar)
- 40°F to 239°F
- Fluorocarbon & Fluorosilicone seal
- Composite body
- For use with 389 Super Flex FL-7 fuel line hose
Please contact Industrial Hose Products Division for clamp specifications



NTA:

- Compression solution
- <B20% biodiesel applications
- Electroless Nickel plated for >B20% biodiesel
- For use with HTFL tubing
- -50°F to 266°F (-46C to 130C)



Diesel Fuel Fittings Solutions

Vibra-Lok:

- Commonly used in engine applications
- Elastomeric seal
- Excellent vibration resistance
- Fluorocarbon sleeve available for high temperature
- Wide range of tubing
- -15 to +450F with fluorocarbon sleeve
- -30 to +275F with Buna N Sleeve



45° Flare:

- Resists mechanical pullout
- Meets functional requirements of SAE J512 and J513
- UL Listing
- Resists vibration – Long nut
- Wide range of tubing
- Copper, Aluminum, Welded steel hydraulic tubing that can be flared
- 550 to 2800 psi - depending on tubing and wall thickness
- -65° to +250°F



Inverted Flare:

- Resists mechanical pullout
- Meets functional requirements of SAE J512
- UL Listing
- Zinc Chromate steel nut available
- Wide range of tubing
- Copper, Aluminum, Welded steel hydraulic tubing that can be flared
- 550 to 2800 psi - depending on tubing and wall thickness
- -65° to +250°F



Series 389 SUPER-FLEX FL-7 Barrier Fuel Line Hose

Diesel Fuel Hose:

Tube: Nitrile with translucent THV barrier

Reinforcement: Multiple aramid plies

Cover: Black CPE, smooth finish

Temp Range: -40°F to +257°F (-40°C to +125°C)

Brand Method: White ink

Brand Example: PARKER SERIES 389 SUPER-FLEX® FL-7 (ID) SAE J30R7/R14T2 FUEL LINE (YEAR CODE) PKHPLINE389 EPA COMPLIANT 15 g/m²/day CARB Q-08-013 MAX WP 50 PSI USA (DATE CODE)

Design Factor: 5:1

Industry Standards: SAE J30R7, SAE J30R14T2, CARB 2006 SORE

Applications:

- Low pressure fuel lines on blowers, grinders, mowers, off-road engines, pressure washers, saws
- Agricultural equipment, autos, busses, construction equipment, off-road equipment

Vacuum: 24" Hg (3/16" through 3/8" ID); 10" Hg (1/2" through 3/4" ID)

Compare To: Avon Greenbar 700, Gates 4219B

Part No.	ID (in)	ID (mm)	Reinf Plies	OD (in)	OD (mm)	Approx Wt. (lbs/ft)	Approx Wt. (kgs/ft)	Min Bend Rad (in)	Min Bend Rad (mm)	Max Rec WP (psi)	Max Rec WP (bar)	Max Rec WP (bar)
38904	1/4	6.4	2	0.500	12.7	0.09	0.04	1.5	38.1	50	3.4	250
38905	5/16	7.9	2	0.562	14.3	0.11	0.05	2.0	50.8	50	3.4	250
38906	3/8	9.8	2	0.625	15.8	0.12	0.05	2.5	63.5	50	3.4	250
38908	1/2	12.7	2	0.781	19.8	0.18	0.08	4.0	101.6	50	3.4	250
38910	5/8	15.9	2	0.938	23.9	0.24	0.11	5.0	127.0	35	3.4	250

Warnings: Refer to CrimpSource at www.safehose.com for coupling recommendations and crimp specifications.



Couplings attached with bands or clamps may reduce the working pressure of the hose assembly to less than the maximum rated working ressure of the hose.

Diesel Fuel Fitting-Hose/Tube Capability

Product	Fitting Temperature	Fitting Max Pressure	Type	Size	389 Super Flex Fuel Hose -40°F to 257°F	HTFL Tubing -50°F to 266°F	PFT-FL Tubing -40°F to 200°F	Copper, Steel, Stainless Tubing
DF	-40°F to 200°F	140psi	Push to Connect	1/2" and 5/8"				
Hose Barb	-40°F to 257°F	50psi	Barb	3/16" to 1 1/2"				
NTA	-50°F to 266°F	140psi	Compression	1/4" to 3/4"				
Safe Lock (SAE J2044)	-40°F to 239°F	72psi	Push to Connect	1/4" to 5/8"				
Vibra Lok	-30°F to 275°F	100psi	Compression	1/8" to 3/4"				

Approved Application