



aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding



icountBS - Bottle Sampler

The portable solution to fluid contamination
bottle sampling



ENGINEERING YOUR SUCCESS.

The complete solution - industrial design combined with state of the art technology

The icountBS - Bottle Sampler from Parker with its innovative industrial design has been developed for customers looking for state of the art technology, attention to detail and the compactness of a permanent laboratory particle analysis model.

Combine this with on-board, laser based, leading edge technology to bring to all industries a truly revolutionary Particle Counter. The icountBS is a product from the next generation of Parker's fluid particle analysis and monitoring innovations.

The IBS features an easy to use interactive touch screen, environmentally controlled pressurized bottle chamber for air bubble suppression via an internal compressor pump, with automated door locking mechanism, sample tube cleaning sleeve minimizing contamination cross over, and an internal printer.

The icountBS benefits from Parkers knowledge and experience of providing bottle analysis equipment to the market over the last 15 years.

This experience comes from selling market leading innovative solutions and by having front line condition monitoring products for all sectors of fluid analysis opportunities. The unit was at every stage developed with the customers voice in mind.





icountBS - Bottle Sampler Features & Benefits

- Quick sample bottle analysis with variable test time options from 15 second and volume capacities from 10ml.
- Repeatable and re-producible result performance to ISO4406:1999 and NAS1638 particle count distributions. For other calibration standards consult Parker CMC.
- On-board compressor and 'shop' air capability.
- Design concept allowing for portability. DC and rechargeable battery pack power options built in.
- Cost-effective and economical alternative solution to external laboratory services.
- 6 fixed channel size analysis.
- Fluid resistant touch type screen panel.
- Sample tube self cleaning sleeve minimizing contamination cross over.
- Internal thermal printer.

Analysing the test results

Once the automatic oil sample test has been completed, what next?

Solid contaminants in fluid power systems vary in size, shape, form and quantity. The most harmful contaminants are normally between 6 microns and 14 microns. The ISO code is the preferred method of reporting quantity of contaminants. The ISO code number corresponds to contamination levels relating to three sizes.

The first scale number represents the number of particles larger than 4µm(c) per 100 milliliters of fluid,

the second number for particles larger than 6 µm(c) per 100 milliliters of fluid and the third number for particles larger than 14 µm(c) per 100 milliliters of fluid.

For example: An ISO code 20/18/14 indicates that there are between 500,000 and 1,000,000 particles larger than 4µm(c), and between 130,000 and 250,000 particles larger than 6 µm(c), and between 4,000 and 8,000 particles larger than 14µm(c).

icountBS reporting and data

In addition to the 'raw data' printout of ISO compliant data from the icountBS's on-board printer, icount Mini-lab described on page 7 offers the user the advantage of a 2-page report template providing hard copy data on ISO and NAS individual counts and average contamination results.



Component Cleanliness Guide

Suggested acceptable contamination levels for various hydraulic systems

Target contamination class to ISO 4406: 1999			Suggested maximum particle level			Sensitivity	Type of system	Typical components
4 µm(c)	6 µm(c)	14 µm(c)	4 µm(c)	6 µm(c)	14 µm(c)			
15	13	9	16,000	4,000	250	Super critical	Silt-sensitive control systems with very high reliability. Laboratory or aerospace	High performance servo valves
17	15	11	64,000	16,000	1,000	Critical	High performance servo and high pressure long life systems, e.g. aircraft, machine tools etc.	Industrial servo valves
18	16	13	130,000	32,000	4,000	Very important	High quality reliable systems. General machine requirements	Piston pumps, proportional valves, compensated flow controls
20	18	14	500,000	130,000	8,000	Important	General machinery and mobile systems. Medium pressure, medium capacity	Vane pumps, spool valves
21	19	15	1,000,000	250,000	16,000	Average	Low pressure heavy industrial systems, or applications where long life is not critical	Gear pumps, manual and poppet valves, cylinders
23	21	17	4,000,000	1,000,000	64,000	Main protection	Low pressure systems with large clearances	Ram pumps

Notes:

Tables have been generated by organisations in various industries.

Some of the tables are defined in cumulative counts, e.g. '>6µm' and others are represented as differential counts e.g. '6-14µm'.

All µm(c) refer to MTD distributions. All µm references will refer to ACFTD distributions.

All standards are in counts per 100ml and provide easy methods for converting particle counts into limits that are simple to interpret. By noting the requirements of the standard, particle counts can be accurately converted to contamination levels.

icount BS Product Specification

Principle of Operation	Laser based light obscuration
Calibration Dust	MTD or ACFTD
Dimensions	H=530 x W=190 (210 Door) x D=410 (mm)
Weight	18Kg
Mechanical Composition	Stainless steel 316, plated mild steel and aluminium
Plastics Composition	Precision polyurethane RIM mouldings and ABS plastic
Environmental Operating Temperature (Tested)	+5°C to + 60°C
Operating RH range	20 – 85% (Tested at 30°C, no condensation)
Storage Temperature	-40°C to + 90°C
Storage RH range	10 – 90% (Tested at 30°C, no condensation)
Channel Sizes	MTD - >4µ(c),>6µ(c),>14µ(c),>21µ(c),>38µ(c), >70µ(c) ACFTD - >2µ,>5µ,>15µ,>25µ,>50µ,>100µ
Analysis Range	ISO 7 to 21, NAS 0 to 12
Contamination Standards	MTD - ISO 4406:1999 & NAS 1638 ACFTD - ISO 4406:1987, ISO 4406:1991 & NAS 1638 For further contamination standards consult Parker CMC
Calibration Standard	ISO MTD and ACFTD calibration to traceable ISO Standards. (Contact Parker CMC for further details).
Fluid Management	Maximum single sample = 100ml Minimum single sample = 10ml
Possible Test Configurations	User selectable from single test up to 5 tests per run (eg.1x100ml up to 5 x50ml per run)
Pre-Test Flush Volume	Minimum = 10ml, Maximum = 100ml
Viscosity Range	5 to 400 cSt
Fluid Compatibility	Mineral oils, petroleum and hydrocarbon based fluids (consult manufacturer) and some esters (consult manufacturer).
Sample Bottle Size	No specific bottle required. Maximum size = 75 (Dia) x 150 (H) mm. Maximum Volume = 250ml
Memory Storage	500 Tests (capacity warning after 450 tests)
Output Display	Backlight 256 Colour STN Transmissive
Output Display Resolution	320 x 3(R.G.B)(H) x 240(W) dots
Display Active Area	115(H) x 86(W) mm
Data Input	Via icon driven resistive touch screen
Printer	Thermal dot-line printing
Printer Paper	Ø50mm – (57mm x 25mm)
Test Certification	Calibration & Certificate of Conformity
Power Supply	DC Output – 12V@ 6.60Amps, 80 watts max. AC Input – 100 to 240V @ 1.2Amps (50 – 60 Hz)
Battery Power	2 Hours (recommended to be fully charged every 3 months)
Battery Stand-By Time	1 month (then 1 hour of operation)
Battery Fuse	6.3 Amps (anti-surge)
Air pressure Source	3.5 bar internal Mini-compressor OR 7 Bar shop air



Order your icountBS Now!

icountBS – Bottle Sampler Ordering Information

Key	Fluid Type		Calibration		Future Option		Future Option	Future Option	Future Option	Transportation Case		Power Supply Region		
	1	Mineral	1	ACFTD	0	Lab Unit				0	0	1	0	None
			2	MTD	1#	Mini-lab Package				1#	Case	1	USA	
	#	Contact Parker for further details											2	Europe

Key	Fluid Type	Calibration	Future Option	Future Option	Future Option	Future Option	Transportation Case	Power Supply Region
IBS	1	2	0	0	0	1	0	0
IBS	1	2	0	0	0	1	0	1
IBS	1	2	0	0	0	1	0	2

Accessories	Part Number
250ml Sample Bottle	ACC6NW001
Sample Bottle Pack (50)	ACC6NW002
Vapour/Waste Bottle	ACC6NW003
Waste Bottle Folder	ACC6NW004
Printer Paper Reel (x1)	ACC6NW005
UK Power Supply	ACC6NW006
USA Power Supply	ACC6NW007
European Power	ACC6NW008
Transit Case	Contact Parker
1m Waste Tube (Clear)	ACC6NW009
1m Vapour Hose (Blue)	ACC6NW010
USB Memory Stick	ACC6NW011
icountBS CD Manual	ACC6NW012



WARNING – USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

- This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.
- The user, through its own analysis and testing is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalogue and in any other materials provided by Parker or its subsidiaries or authorized distributors.
- To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

Offer of sale

Please contact your Parker representation for a detailed 'offer of sale'.



**NEW
PRODUCT**

Introducing the NEW icount 'Mini-lab' – The effective way of utilising your icountBS

How clean is your hydraulic system?

Contamination Control is only an oil sample away with our easy, 3-Step fluid analysis service.

Step 1

Obtain your sample of hydraulic oil.

Step 2

Take the 2 minute off-line oil sample test.

Step 3

View your results and run a report immediately.



Kit comprises: icountBS. Flat-pack trolley. 30 sample bottles. Optional Laptop/software/printer and cables

Parker Worldwide

AE – UAE, Dubai
Tel: +971 4 8127100
parker.me@parker.com

AR – Argentina, Buenos Aires
Tel: +54 3327 44 4129

AT – Austria, Wiener Neustadt
Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt
Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AU – Australia, Castle Hill
Tel: +61 (0)2-9634 7777

AZ – Azerbaijan, Baku
Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles
Tel: +32 (0)67 280 900
parker.belgium@parker.com

BR – Brazil, Cachoeirinha RS
Tel: +55 51 3470 9144

BY – Belarus, Minsk
Tel: +375 17 209 9399
parker.belarus@parker.com

CA – Canada, Milton, Ontario
Tel: +1 905 693 3000

CH – Switzerland, Etoy
Tel: +41 (0) 21 821 02 30
parker.switzerland@parker.com

CL – Chile, Santiago
Tel: +56 2 623 1216

CN – China, Shanghai
Tel: +86 21 5031 2525

CZ – Czech Republic, Klecany
Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst
Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup
Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid
Tel: +34 902 33 00 01
parker.spain@parker.com

FI – Finland, Vantaa
Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve
Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens
Tel: +30 210 933 6450
parker.greece@parker.com

HK – Hong Kong
Tel: +852 2428 8008

HU – Hungary, Budapest
Tel: +36 1 220 4155
parker.hungary@parker.com

IE – Ireland, Dublin
Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IN – India, Mumbai
Tel: +91 22 6513 7081-85

IT – Italy, Corsico (MI)
Tel: +39 02 45 19 21
parker.italy@parker.com

JP – Japan, Tokyo
Tel: +(81) 3 6408 3901

KR – South Korea, Seoul
Tel: +82 2 559 0400

KZ – Kazakhstan, Almaty
Tel: +7 7272 505 800
parker.easteurope@parker.com

LV – Latvia, Riga
Tel: +371 6 745 2601
parker.latvia@parker.com

MX – Mexico, Apodaca
Tel: +52 81 8156 6000

MY – Malaysia, Shah Alam
Tel: +60 3 7849 0800

NL – The Netherlands, Oldenzaal
Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Ski
Tel: +47 64 91 10 00
parker.norway@parker.com

NZ – New Zealand, Mt Wellington
Tel: +64 9 574 1744

PL – Poland, Warsaw
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal, Leca da Palmeira
Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest
Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow
Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga
Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SG – Singapore
Tel: +65 6887 6300

SK – Slovakia, Banská Bystrica
Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto
Tel: +386 7 337 6650
parker.slovenia@parker.com

TH – Thailand, Bangkok
Tel: +662 717 8140

TR – Turkey, Istanbul
Tel: +90 216 4997081
parker.turkey@parker.com

TW – Taiwan, Taipei
Tel: +886 2 2298 8987

UA – Ukraine, Kiev
Tel: +380 44 494 2731
parker.ukraine@parker.com

UK – United Kingdom, Warwick
Tel: +44 (0)1926 317 878
parker.uk@parker.com

US – USA, Cleveland
Tel: +1 216 896 3000

VE – Venezuela, Caracas
Tel: +58 212 238 5422

ZA – South Africa, Kempton Park
Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

European Product Information Centre
Free phone: 00 800 27 27 5374
(from AT, BE, CH, CZ, DE, DK, ES, FI, FR, IE, IT, NL, NO, PL, PT, RU, SE, UK, ZA)

