



aerospace  
climate control  
electromechanical  
filtration  
fluid & gas handling  
**hydraulics**  
pneumatics  
process control  
sealing & shielding



## Compact EHA

Electro-Hydraulic Actuators for  
high power density applications



ENGINEERING YOUR SUCCESS.

## Introducing Compact EHA ...

The new Compact EHA from Parker delivers powerful, reliable linear movement. Compact EHA is a fully self-contained electro-hydraulic actuator which combines high power density with light weight, low sound level and small envelope. Simple “plug 'n play” functionality makes Compact EHA the ideal solution for applications where other conventional linear movement technologies lack the power, speed and durability of compact hydraulics.

Available for 12V and 24V DC operation, Compact EHA is suitable for a wide range of mobile, light industrial and domestic applications.

## Where Can I Use Compact EHA?

### Turf Care/Lawn & Garden

- Deck lifts
- Mower blade lifts
- Golf course sprayer/sweeper

### Marine

- Jack plates
- Hatches
- Yacht transom actuators

### Material Handling

- Pallet lifts
- Lift tables
- Scissors tables
- Light aircraft tug

### Truck & All Terrain/Utility Vehicle

- Tailgate locks
- Utility vehicle attachments
- Cart/trailer bed lifts

### Military/Security

- Door opening
- Hatch lifting
- Cab lifts
- Armored vehicle attachments

### Construction

- Attachment locks
- Skid steer bucket level
- Plough/blade positioning

### Renewable Energy

- Solar panel positioning
- Wind turbine rotor locks

### Agriculture

- Chute positioners
- Sprayer arm lifts

### Medical/patient handling

- Stretchers & beds
- Ambulance cots
- Wheelchair access ramps
- Kneeling handicap vans



## Delivering Power with Control

### 1 Rugged DC Motor

A choice of 12V or 24V DC motors, each available in two power ratings, makes it easy to match your power supply and deliver the force your application demands. All versions are supplied with 1.5m (60 in) leads fitted with standard ring terminals, to simplify and speed up connection.

### 2 Reversible Gear Pump

Compact EHA's electric motor is mated to a robust gear pump, fully enclosed within the fluid reservoir. The fully sealed hydraulic system ensures that the pump operates under ideal conditions, guaranteeing a long, maintenance-free service life. Four different pump capacities allow Compact EHA to be tailored to the precise load and speed demands of your application.

### 3 Robust One-Piece Housing

All Parker Compact EHAs feature a tough, lightweight one-piece housing with integrated base mounting, manufactured from cast aluminium and anodized for durability. The absence of jointing faces minimizes potential leakage points, so Compact EHA is the ideal choice in environments where cleanliness is critical. Innovative design results in an exceptionally small footprint, so integrating Compact EHA into new products, or retro-fitting into existing designs, could not be easier.

### 4 Double-Acting Hydraulic Cylinder

Exceptional power density distinguishes the Parker Compact EHA from other linear actuation solutions. The powerful hydraulic cylinder, which can be powered in both directions, delivers up to 21.35kN (4800 lbf) of extend force, 15.57kN (3500 lbf) in retract – and can achieve speeds of up to 84mm (3.3 in) per second. The precision-machined stainless steel piston rod and micro-finished cylinder bore feature buna-nitrile and polyurethane sealing elements, keeping the hydraulic fluid in and external contaminants out – ensuring smooth control and long service life.

### 5 Simple Pivot Pin Mountings

Installing a Compact EHA could not be quicker – or easier. Both the base and the piston rod are machined to accept standard pivot pin sizes which, for ease of mounting, are commonly the same diameter at both ends. Installation involves securing both ends of the unit with pins, and then connecting the leads to your power supply. In minutes, your Compact EHA is ready for service.

Standard options include varied pin sizes, base end angle or orientation and spherical bearings. Custom mountings are available through special order.


### 6 Integrated Control Valves

To protect the Compact EHA against overload, and to allow loads to be held safely in position, all Parker Compact EHAs feature a built-in locking circuit, pressure relief, thermal and check valves. These features ensure the safety of the equipment – and of those operating it.

**Specifications**

**7 Internal Fluid Reservoir**

Long working life depends on clean hydraulic fluid. All Parker Compact EHAs are flushed, filled and sealed for life under controlled conditions during manufacture, to ensure that no contaminants enter the hydraulic system. The fluid is contained in an internal reservoir cast into the one-piece housing, so that it remains as clean as the day it was filled.



**Easy to Install and Connect**

Compact EHA is designed to make commissioning as simple as possible. The motor is connected to a suitable power supply and switching circuit, and the rod or base end is secured with a pivot pin. The unit is then actuated to align the opposite pivot pin connection, and the pin inserted to secure. And that's it – your Compact EHA is ready for use.

**Maintenance**

Because the Compact EHA is flushed, filled and sealed for life, there is virtually no maintenance required. This, in combination with the anodized housing, stainless steel rod and rugged seals and components, provides a longer service life with reduced warranty costs.

**Complete Compact EHA Solutions**

In addition to custom actuators, our engineers are experienced in the design of complete actuation systems. Where your requirement includes cable harnesses, switchgear and power supplies, please contact us for the further information.

**Electro-Hydraulic Actuators  
Compact EHA**

**Specifications**

**Actuator**

Type	hydraulic, double-acting
Bore sizes	25.4mm (1.0 in), 31.8mm (1.25 in), 36.5mm (1.44 in)
Standard stroke lengths	102mm (4 in), 152mm (6 in), 203mm (8 in)
Piston rod diameters	14.2mm (.561 in), 15.9mm (.625 in), 19.1mm (.750 in)
Standard mounting pin diameters	6.4mm (.250 in), 9.5mm (.375 in), 12.7mm (.500 in)

**Motor**

Motor types	12V DC, 245W (motor A) 12V DC, 560W (motor B) 24V DC, 245W (motor C) 24V DC, 560W (motor D)
Leads – length	1.5m (60 in)
Leads – wire size	14 gauge (motors A & C) 12 gauge (motors B & D)
Connector type	ring terminals, 6.6mm (.26 in) I/D

**Pump**

Pump type	gear, reversible
Pump capacities	.100 gear = .16cc/rev (.010 in <sup>3</sup> /rev) .190 gear = .31cc/rev (.019 in <sup>3</sup> /rev) .250 gear = .41cc/rev (.025 in <sup>3</sup> /rev) .327 gear = .53cc/rev (.032 in <sup>3</sup> /rev)
Fluid medium	automatic transmission fluid (ATF)

**Circuit**

Sealed locking hydraulic circuit with integrated pump, motor, actuator and reservoir, relief, thermal, check and back pressure valves.

**Certification and Testing**

Vibration	(minimum integrity test) MIL-STD-810F
Sealing	IP65 and IP67
Salt spray	1000 hours per ASTM B117
CE marked	in conformity with Machinery Directive 98/37/EC and 2007/42/EC
For other application-specific approvals, please consult factory.	







**Performance**

Maximum force – extend	21.35kN (4800 lbf)
Maximum force – retract	15.57kN (3500 lbf)
Maximum speed	84mm/sec(3.3 in/sec)
Duty cycle	see page 6

**General**

Construction – body	anodized cast aluminium, one-piece
– piston rod	stainless steel
Orientation	universal
Manual release option	retained, for emergency use only
Operating temperature range	-34°C (-30°F) to +65°C (150°F)
Sound Level	< 70dBA
Weight	see page 5

The maximum force available and Amperage draw on rod extend for different combinations of motor, pump and cylinder bore can be determined from the tables below:




Current draw for Motor C (24VDC, 245 W) and Motor D (24VDC, 560 W) will be approximately ½ of Amp draw shown above.


**Retract Forces:** The maximum force available on **rod retract** is lower than on extend due to the presence of the piston rod which reduces the effective surface area of the piston. When the force required to retract the piston rod approaches that required for extend, please contact the factory.

Note: Performance data is based on **rod extend**, not retract, and is for reference only.

**Hydraulic Schematic**





**Suggested Diagram for Wiring**





Function	Positive	Ground
Extend	Blue	Green
Retract	Green	Blue

**STANDARD MOTOR DUTY CYCLE CHARACTERISTICS**



**S2**  
 Time at constant load followed by "off" time to allow the motor to cool to ambient temperature

**S3**  
 Percentage of "on" time in a repetitive 10 minute cycle




**Weights**

To calculate the weight of a standard Compact EHA, identify the weight of the basic unit from the left hand columns, then add the corresponding weight for the motor required.

EHA - basic unit without motor		Weight	Add for	
Stroke Length	with Rod Ø		Motor A or C	Motor B or D
102mm (4 in)	14.2mm (.561 in)	2.1kg (4.7 lb)		
152mm (6 in)	15.9mm (.625 in)	2.8kg (6.5 lb)	1.5kg (3.3 lb)	2.0kg (4.3 lb)
203mm (8 in)	19.1mm (.750 in)	3.5kg (7.6 lb)		

**Dimensions**



Pin to Pin Dimensions for Units with Spherical Bearings	Spherical on Rod End		Spherical on Base End	
	In Extend	In Retract	In Extend	In Retract
Stroke Length				
102mm (4 in)	250.57mm (9.865 in)	351.79mm (13.85 in)	253.90mm (9.996 in)	354.99mm (13.976 in)
152mm (6 in)	301.37mm (11.865 in)	402.59mm (15.85 in)	304.70mm (11.996 in)	405.79mm (15.976 in)
203mm (8 in)	352.17mm (13.865 in)	453.39mm (17.85 in)	355.50mm (13.996 in)	453.59mm (17.976 in)

For further detail, tolerances or information on these drawings, contact the division.

**Warning**

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

**Offer of Sale**

Please contact your local Parker representative for a detailed offer of sale.

**About Us**

Parker Hannifin is the world's leading diversified manufacturer of motion and control technologies and systems, providing precision-engineered solutions for a wide variety of mobile, industrial and aerospace markets.

The company employs approximately 52,000 people in 48 countries around the world.

Visit us at [www.parker.com/oildyne](http://www.parker.com/oildyne)

**COMPACT EHA (Electro-Hydraulic Actuator) APPLICATION/DATA SHEET**

Company: \_\_\_\_\_ Date: \_\_\_\_\_  
 Contact: \_\_\_\_\_ Phone: \_\_\_\_\_  
 Email: \_\_\_\_\_ Fax: \_\_\_\_\_  
 End Customer & Location: \_\_\_\_\_ Government Customer?  Yes  No

Application: \_\_\_\_\_

What is the specific task to be performed by the Compact EHA? \_\_\_\_\_

In EXTEND: Operating Force: \_\_\_\_\_ N or lbs (circle one) Operating Rate: \_\_\_\_\_ mm/sec or in/sec (circle one)

In RETRACT: Operating Force: \_\_\_\_\_ N or lbs (circle one) Operating Rate: \_\_\_\_\_ mm/sec or in/sec (circle one)

Is the load pushing or pulling the rod?  **PUSHING**  **PULLING**  **BOTH** Is the direction of motion the same as the load?  **YES**  **No**

DUTY CYCLE: Cycles per Day: \_\_\_\_\_ Time Between Cycles: \_\_\_\_\_ Product Life Requirement: \_\_\_\_\_

Maximum allowable amperage: \_\_\_\_\_ Operating Temperature Range: \_\_\_\_\_ TO \_\_\_\_\_ °C or °F (circle one)

Potential for Side-Loading:  **YES \*\***  **No** Exposure to Vibration?  **YES \*\***  **No** Shock Loading?  **YES \*\***  **No**

\*\* If YES, explain: \_\_\_\_\_

Unit Code: \_\_\_\_\_ If you can't code out what you need with options below, contact your sales representative.

**EHA - - - 0 - - - B - - - B - - - N**

**BORE**

A	25.4 mm (1.00 in)
B	31.8 mm (1.25 in)
C	36.5 mm (1.44 in)

**STROKE**

400	102 mm (4.00 in)
600	152 mm (6.00 in)
800	203 mm (8.00 in)

**CIRCUIT**

B	STANDARD
---	----------

If possibility of runaway condition exists, call Division for proper choice of L or M

**MANUAL RELEASE**

N	NO	A	YES
---	----	---	-----

**PUMP**

1	.100 GEAR
2	.190 GEAR
3	.250 GEAR
4	.327 GEAR

**MOTOR**

A	12 VDC MOTOR, 245 WATTS
B	12 VDC MOTOR, 560 WATTS
C	24 VDC MOTOR, 245 WATTS
D	24 VDC MOTOR, 560 WATTS

ROD END	Pivot Hole Diameter			
	6.4mm (.25 in)	9.5mm (.375 in)	12.7mm (.50 in)	Spherical Bearing
A Bore 25.4mm (1.00 in)	ACA 14.2mm (.561 in) diameter rod			
B Bore 31.8mm (1.25 in)	ACA 14.2mm (.561 in) diameter rod	BCC 15.9mm (.625 in) diameter rod		
C Bore 36.5mm (1.44 in)	ACA 14.2mm (.561 in) diameter rod	BCC 15.9mm (.625 in) diameter rod	CCE 19.1mm (.750 in) diameter rod	CBX 19.1mm (.750 in) diameter rod

For other rod diameter/pivot hole size combinations, contact Oildyne.

BASE END	With A Bore 25.4mm (1.00 in)		With B Bore 31.8mm (1.25 in)		With C Bore 36.5mm (1.44 in)	
		90° from Std*		90° from Std*		90° from Std*
Pivot Hole Diameter						
6.4mm (.250 in)	BAA	BAJ	BAA	BAJ	BAA	BAJ
9.5mm (.375 in)			BCA	BCJ	BCA	BCJ
12.7mm (.500 in)					BEA	BEJ
Spherical Bearing	*See drawing on page 4 for standard orientation.				EOA	

	MAXIMUM EXTEND FORCE REQUIRED		CODE	MAXIMUM RETRACT FORCE REQUIRED		
	N	(lbs)		N	(lbs)	
A, B & C Bore	0-1780	(0-400)	04	0-1780	(0-400)	A, B & C Bore
	1781-3560	(401-800)	08	1781-3560	(401-800)	
	3561-5340	(801-1200)	12	3561-5340	(801-1200)	
	5341-7120	(1201-1600)	16	5341-7120	(1201-1600)	B & C Bore Only
	7121-8900	(1601-2000)	20	7121-8900	(1601-2000)	
B & C Bore Only	8901-10675	(2001-2400)	24	8901-10675	(2001-2400)	C Bore Only
	10676-12455	(2401-2800)	28	10676-12455	(2401-2800)	
	12456-14235	(2801-3200)	32	12456-14235	(2801-3200)	
C Bore Only	14236-16000	(3200-3600)	36   35	14236-15570	(3200-3500)	Only
	16001-17800	(3601-4000)	40			
	17801-19570	(4001-4400)	44			
	19571-21350	(4401-4800)	48			

**ADDITIONAL INFORMATION**

Annual Usage: \_\_\_\_\_ Prototype Date: \_\_\_\_\_ Production Start Date: \_\_\_\_\_ Target Price: \_\_\_\_\_  
 Components Being Replaced: \_\_\_\_\_  **NONE, New Design**  
 Comments: \_\_\_\_\_

**PLEASE PROVIDE DRAWINGS/DIAGRAMS OF THE APPLICATION and ANY OTHER HELPFUL INFORMATION**

Your Parker sales specialist will work with you to develop an accurate unit configuration which incorporates all the features required for your application. Please contact us for further information.



# Parker Hydraulics International Sales Offices

## North America

### Hydraulics Group Headquarters

6035 Parkland Boulevard  
Cleveland, OH 44124-4141 USA  
Tel: 216-896-3000  
Fax: 216-896-4031

### Parker Canada Division

160 Chisholm Drive  
Milton, Ontario, L9T 3G9 Canada  
Tel: 905-693-3000  
Fax: 905-876-1958

## Mexico

### Parker Hannifin de México

Industrial Hydraulic Sales  
Eje Uno Norte No. 100  
Parque Industrial Toluca 2000  
Toluca, Edo. de Mexico CP 50100  
Tel: 52 72 2275 4200  
Fax: 52 72 2279 9308

## Europe

### Hydraulics Group Headquarters

La Tuilière 6  
CH-1163 Etoy, Switzerland  
Tel: 41 21 821 8500  
Fax: 41 21 821 8580

## Latin America

### Parker Hannifin Ind. e Com. Ltda

#### Hydraulics Division

Av. Frederico Ritter, 1100  
94930-000 Cachoeirinha RS, Brazil  
Tel: 55 51 3470 9144  
Fax: 55 51 3470 9215

### Parker Hannifin Argentina S.A.I.C.

Stephenson 2711  
1667-Tortuguitas-Malvinas Argentinas  
Pcia. de Buenos Aires, Argentina  
Tel: 54 3327 44 4129  
Fax: 54 3327 44 4199

### Pan American Division

7400 NW 19th Street, Suite A  
Miami, FL 33126 USA  
Tel: 305-470-8800  
Fax: 305-470-8808

## Mobile Sales

### Mobile Sales Organization and Global Sales

850 Arthur Avenue  
Elk Grove Village, IL 60007 USA  
Tel: 847-258-6200  
Fax: 847-258-6299

## Industrial Sales

### Central Region

1042 Maple Avenue  
Unit 331  
Lisle, IL 60532 USA  
Tel: 630-964-0796

### Great Lakes Region

6035 Parkland Boulevard  
Cleveland, OH 44124-4141 USA  
Tel: 216-896-3000  
Fax: 216-896-4031

### Gulf Region

20002 Standing Cypress Drive  
Spring, TX 77379 USA  
Tel: 817-473-4431  
Fax: 888-227-9454

### Southwest Region

700 S. 4th Avenue  
Mansfield, TX 76063 USA  
Tel: 817-473-4431  
Fax: 888-227-9454

### Mid Atlantic & Southeast Regions

1225 Old Alpharetta Rd  
Suite 290  
Alpharetta, GA 30005 USA  
Tel: 770-619-9767  
Fax: 770-619-9806

### Midwest Region

8145 Lewis Road  
Minneapolis, MN 55427 USA  
Tel: 763-513-3535  
Fax: 763-544-3418

### Northeast Region

P.O. Box 396  
Pine Brook, NJ 07058 USA  
Tel: 973-227-2565  
Fax: 973-227-2467

### Northwest Region

6458 North Basin Avenue  
Portland, OR 97217 USA  
Tel: 503-283-1020  
Fax: 866-611-7308

### Pacific and Plains Region

8460 Kass Drive  
Buena Park, CA 90621 USA  
Tel: 714-228-2509  
Fax: 714-228-2511

## Asia Pacific

### Parker Hannifin Shanghai Ltd.

280 Yunqiao Road,  
Jin Qiao Export Processing Zone  
Shanghai 201206, China  
Tel: 86 21 2899 5000  
Fax: 86 21 5834 8975

### Parker Hannifin Hong Kong Ltd.

Suites 01-04, 20/F,  
Tower 2, The Gateway,  
Harbour City, Tsimshatsui,  
Hong Kong  
Tel: 852 2428 8008  
Fax: 852 2480 4256

### Parker Hannifin Japan Ltd.

Shirokandedai Building 2nd Floor  
3 2 10 Shirokanedai  
Minato Ku  
Tokyo 108 0071  
Japan  
Tel: +(81) 3 6408 3900  
Fax: +(81) 3 5449 7202

### Parker Hannifin Korea Ltd.

18F KAMCO Yangjae Tower  
949-3 Dogok1-dong, Gangnam-gu  
Seoul, 135-860, Korea  
Tel: 82 2 559 0408  
Fax: 82 2 556 8187

### Parker Hannifin India Pvt Ltd.

Plot No. EL-26, MIDC,  
TTC Industrial Area  
Mahape, Navi Mumbai, 400 709, India  
Tel: 91 22 6513 7081  
Fax: 91 22 2768 6841

### Parker Hannifin Australia

Parker Hannifin Pty Ltd.  
9 Carrington Road  
Castle Hill, NSW 2154, Australia  
Tel: 612 9634 7777  
Fax: 612 9842 5111

## South Africa

### Parker Hannifin Africa Pty Ltd

10 Berne Avenue  
Aeroporto  
Kempton Park 1620,  
Republic of South Africa  
Tel: 19 610 700  
Fax: 13 927 213



## Parker Hannifin Corporation

Hydraulic Pump and Power Systems Division

Oildyne Business Unit

5520 Highway 169 North

New Hope, MN 55428-3502 USA

Ph: 937-644-3915

Fax: 937-642-3738

[www.parker.com/hps](http://www.parker.com/hps)