

# 2340N-24 *polyflex* Hose

High Pressure Hydraulic Hose  
for Oil & Gas Market



Parker **polyflex** 2340N-24 hose was specifically designed to serve the oil & gas market. Its state of the art construction makes it suitable for a wide range of land based, off shore and subsea applications. The seamless, extruded Polyamide core tube has a wide range of media compatibility. The high tensile steel reinforcement provides a full 5000 psi working pressure at 4:1 design factor. The Polyurethane cover provides durable protection. These features combine to offer a solution to withstand the rigors of the oil & gas industry. Polyflex 2340N-24 hose is a viable alternative to rigid piping and eliminates the need for special welding procedures and inspections, saving significant installation time while lowering installed costs.



## Contact Information:

Parker Hannifin Corporation  
**Parflex Division**  
11151 Cash Road  
Stafford, TX 77477  
phone (281) 566 4500  
fax (281) 582 5271  
[www.parker.com/parflex](http://www.parker.com/parflex)

## Product Features:

- API 17E and ABS approved
- 5000 psi working pressure at 4:1 design factor
- Seawater-resistant Polyurethane jacket



ENGINEERING YOUR SUCCESS.

# 2340N – High Pressure Hydraulic Hose



## Features

- Moisture ingress resistant
- Available in long continuous lengths
- Flexible, cost effective solution to welded pipe

## Applications/Markets



- Subsea Hydraulics
- BOP Stack
- Acidizing
- Well Stimulation
- Cementing
- Land Based Hydraulic Applications

Part Number	Nominal I.D.			Maximum O.D.		Maximum Working Pressure		Minimum Bend Radius		Weight		Permanent Fitting Series
	DN	inch	mm	inch	mm	psi	MPa	inch	mm	lbs./ft.	kg./mtr.	
#												
2340N-24V10	-24	1-1/2	38.0	2.18	55.5	5,000	34.5	17.72	450	2.35	3.50	8X

## Construction

Tube: Polyamide

Reinforcement: Two closed spiral layers and two open spiral layers of high tensile steel wire

Cover: Polyurethane

## Fittings

8X Series constructed of 316 Stainless Steel

## Colors

- Black

## Operating Parameters

Temperature Range:

-40°F to +212°F (-40°C to +100°C)

Vacuum Rating: 28 inch Hg

Change in working length @ Rated WPSI: +/-2%

Min. Burst Pressure is 4x Max. Working Pressure