



aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding



Wind Turbines

Dedicated Products and Solutions



ENGINEERING YOUR SUCCESS.

Dedicated products and solutions for

Parker – an experienced partner at your service

For many years, Parker Hannifin has been a major supplier of quality components and system solutions to the wind turbine industry, with manufacturing and engineering facilities around the world, including Europe's leading wind power nations, such as Denmark, Germany, Spain and the Netherlands as well as the United States and China, ensuring global aftermarket support.

Parker has dedicated teams of wind turbine specialists working globally to assist our clients in the

design of systems, sub-systems and solutions to meet the most demanding requirements, offering unbeatable global product availability and service.

There are several immediate value-adding benefits from utilising our expertise and our advanced technology.

For the manufacturer, time-to-market can be cut by several (very important) months, while production time and cost can be reduced by up to 15 percent,

thanks to integrated solutions, unique design features, globally synchronized logistics and services such as Kan-Ban, Kitting and Pre-assembly, which also cut inventories and simplify purchase routines significantly.

For the end-user, benefits such as greater efficiency, reduced downtime and less maintenance contribute to an improved profitability.

► Power units

The power unit is the heart of the turbine, supplying the power necessary to operate pitch, yaw and braking systems and providing backup in case of power failure, ensuring a safe stop with no risk of damage. Our hydraulic power units are designed with reliability, ease of maintenance and a wide operating temperature range in mind.



▲ Integrating real-time intelligence in the gearbox filtration system

Parker's engineered filtration solutions for wind turbines have proven to be effective in positively influencing the life of critical components such as gear boxes and bearings. Specially designed filter elements extend the life of the filters and reduce the number of filter changes thus improving the utilization of the turbine, increasing the uptime and reducing the service costs – especially when these are at a premium.

Magnetic pre-filtration ensures ferrous particles are minimized in the oil circuit and oil and filter life is further extended while progressive degradation in the bearings/gearbox is minimized. In-line condition monitoring system provides accurate and real-time data on the condition of the lubrication fluid going in and out of the drive train thus providing critical information on the state of the gearbox – allowing for pro-active changes and preventative maintenance, saving time and expensive repairs. The sensing and communication modules offer 'plug and play' functionality with the turbine control unit.

Parker advantages in short:

- Global presence with over 12000 service locations
- Outstanding wind turbine experience
- Dry Technology™
- Complete solutions for motion and control in turbines
- Complete Solutions for Power Conversion, transfer and storage
- Time-saving kitting and pre-assembly
- Product availability
- Extended warranty



wind turbines

▼ Pitch systems

Dynamic pitch systems with specially designed cylinders, with fully protected internal transducers on which integrated blocks containing all necessary valves are mounted, are placed inside the hubs. This necessitates reliable performance, maintenance accessibility and integrated safety functions. Parker can supply integrated systems with every component needed, including high performance electronic control valves compatible with any modern wind turbine control system. The pitch control can be combined with a technically advanced axis controller for pitch and maximum force control, bringing about high-accuracy blade control and permanent control of the mechanical load on the blades.



▼ Braking systems

Braking systems are used as a parking brake for servicing, for slowing down to a halt safely and to maintain a constant generator speed when the turbine is transmitting power. Parker offers a complete range of brake solutions for the wind turbine. Parker's high speed shaft brake solutions are modular and thus capable of hydraulic or electromechanical actuation, serviceable and adjustable without the need for disassembly from the turbine. They come complete with the actuation mechanism of your choice. The yaw brakes are self aligning, thus increasing the life of the brake and brake liners as well as the slew ring, saving thousands of euros over the turbine life. The rotor lock system is one-of-a-kind and requires no external power pack or oils – eliminating assembly time while also cutting service costs and weight. Just plug it in and press a switch to operate.



▼ Electromechanical Blade Pitch Control Systems

In addition to hydraulically controlled and actuated blade pitch control systems, Parker can also provide the components and systems to achieve highly dynamic performance with electromechanical technologies. Parker's electromechanical solutions include: DC drives with robust design and flexible connectivity; brushless servomotors in a full power range with flexible connection options; multi-axis motion controllers providing high speed coordinated multi-axis motion; servo drives with compact power and full programmability and electric cylinders offering compact power in a rugged package.






▲ Parker gear pumps and motors

A wide range of heavy duty gear pumps and motors for long, reliable service life in the hostile environment of a wind turbine's nacelle. Integrated functions for brake charging, unloading and other value-adding features.




▲ Precision hydraulic valves and electronics

Proportional valves for accurate and smooth control, high response valves for closed loop applications. From Parker's wide range of analogue and digital electronic controls, we can help you select the proper components and system solutions for superior performance at a competitive cost.



▼ Thermoplastic hoses – a problem solver for almost any hydraulic application

Available as single hoses, multiple hoses, hose bundles or preformed hoses, offering superb durability, ozone and UV resistance, non-conductivity, excellent chemical resistance, low volumetric expansion and low pressure drop. In combination with easy assembly, minimised downtime, and space saving compact design, these features guarantee brilliant performance and contribute to system profitability. Especially with customised solutions, the polyflex product range can perfectly meet the requirements of wind turbine applications. Guaranteed cleanliness level.





▲ Store energy

Our complete range of CE approved piston, bladder and diaphragm accumulators maintains high pressure for safe braking and dynamic control. Greater system efficiency and reduced pump sizes gives longer life, lower costs and reduced noise levels. Piston position sensors for monitoring our piston accumulators are also available.

▼ Steel and stainless steel quick couplings

A complete range of quick couplings for any tough environment application.



◀▶ Hydraulic fittings

These high-pressure fittings are used in all fields of hydraulic applications. A wide range of designs and materials makes them particularly suitable for wind turbine applications where safety, corrosion resistance, leak free connections and ease of assembly are important factors.



▶ Unique Parflange® F37 technology makes welding unnecessary

With the new Parflange® F37 system you are signalling the future: from now on, non-welded tube connections for the largest tube dimensions and pressures up to 420 bar (6,000 psi) can be prepared quickly, cleanly and with reduced costs. Traditional welding is a thing of the past.



◀ Parker Hoses

The best hose for your operation is the one that gets the job done right. At Parker, we offer the most comprehensive line of hoses and all the fittings and options you'll need, including UV resistance, maximum flexibility, a wide range of media compatibility, and hoses that are made to meet or exceed ISO and EN specifications. Additionally, we can provide guaranteed cleanliness levels for all your hose assemblies. These characteristics make Parker the hose supplier of choice for you.





◀▶ Added life

Parker Filtration technology extends the life and increases the reliability of wind turbines by specially designing on purpose solutions. Parker also ensures that the impact on the environment is minimized by utilizing environmentally friendly materials and manufacturing products that are recyclable/biodegradable to the extent possible. In addition to a wide range of hydraulic and lube oil filters, reservoirs and accessories, Parker offers a wide range of fluid condition monitoring solutions such as in-line and off-line particle measurement systems, moisture detection systems, pressure and temperature measurement systems and breather elements for both hydraulics and electrical systems. A comprehensive range of quality products to cover all your filtration needs.



▼ Specially designed cylinders

Parker's hydraulic cylinders for wind turbine applications deliver reliable performance under tough operating conditions. Typically, cylinders incorporate a manifold with control valves and feature a built-in position sensor. The system maintains selected rotor pitch during normal operation. In the event of e.g. grid loss, the rotor blades are quickly feathered.



▲ Integrated functionality

Customised system blocks simplify installation and servicing. These can include threaded cartridges, manifold mounted valves and, in addition, servo proportional valves. Pre-assembled and tested, they offer great value in reducing assembly and installation costs. Save on aftermarket purchasing and servicing!




◀ Quiet power

Parker offers a range of pumps, from variable piston pumps to fixed displacement vane pumps with high pressure and high speed capacities, low weight and exceptionally low levels of noise. A wide range of frame sizes and controls makes this range the obvious choice for modern wind turbine designs. All pumps are performance-matched to the other system components, for optimum performance and reliability.

▶ Measuring devices

A broad range of sensors and adaptors is available in our SensoControl® product offering, all designed to meet global standards. A wide variety of mounting styles, pressure ranges and monitoring systems accommodates all types of application demands. Combined pressure and temperature sensor units are available. Parker's diagnostic equipment can identify hard-to-detect variations in pressure, temperature and flow quickly and easily.






▼ Grid-Tie Inverter Systems

With more than 30 years of experience in inverter technology, Parker SSD Drives provides grid-tie inverter systems using innovative filtering and cooling methods to maximize energy recovery and ensure quality power to the grid. Parker SSD Drives inverter systems deliver efficient and reliable performance with compact mechanical designs, ensuring minimum footprint and easy handling. They include function-block programming, modular design scalable for solutions from 1 MW to hundreds of megawatts, application specific control logic, PWM switching technology and integral harmonic filtering. Pluggable power modules mean simple, on-site service and repair without the need for expensive shipping or handling.

► High Density Electronic Cooling

These best-in-class extreme cooling systems provide high performance and maximum power in a lightweight, compact system architecture. Advanced Parker Vaporizable Dielectric Fluid (VDF) cooling technology is 1000 times more effective than air at heat removal, with no condensation. Parker offers plug-in modularity with integrated bus system and minimal power wiring. These rugged sealed modules are easy to install and service.



▲▼ Subsea power cables

Parker Scanrope is a global supplier of subsea power cables and associated termination equipment to the offshore wind turbine and wave power industry. With our Engineering and Development staff, we have the experience and technical qualifications to supply customers with the necessary information for choosing the best design, customised to meet specific needs.



Parker Worldwide

AE – UAE, Dubai
Tel: +971 4 8127100
parker.me@parker.com

AR – Argentina, Buenos Aires
Tel: +54 3327 44 4129

AT – Austria, Wiener Neustadt
Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt
Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AU – Australia, Castle Hill
Tel: +61 (0)2-9634 7777

AZ – Azerbaijan, Baku
Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles
Tel: +32 (0)67 280 900
parker.belgium@parker.com

BR – Brazil, Cachoeirinha RS
Tel: +55 51 3470 9144

BY – Belarus, Minsk
Tel: +375 17 209 9399
parker.belarus@parker.com

CA – Canada, Milton, Ontario
Tel: +1 905 693 3000

CH – Switzerland, Etoy
Tel: +41 (0) 21 821 02 30
parker.switzerland@parker.com

CL – Chile, Santiago
Tel: +56 2 623 1216

CN – China, Shanghai
Tel: +86 21 2899 5000

CZ – Czech Republic, Klecany
Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst
Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup
Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid
Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa
Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve
Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens
Tel: +30 210 933 6450
parker.greece@parker.com

HK – Hong Kong
Tel: +852 2428 8008

HU – Hungary, Budapest
Tel: +36 1 220 4155
parker.hungary@parker.com

IE – Ireland, Dublin
Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IN – India, Mumbai
Tel: +91 22 6513 7081-85

IT – Italy, Corsico (MI)
Tel: +39 02 45 19 21
parker.italy@parker.com

JP – Japan, Fujisawa
Tel: +(81) 4 6635 3050

KR – South Korea, Seoul
Tel: +82 2 559 0400

KZ – Kazakhstan, Almaty
Tel: +7 7272 505 800
parker.easteurope@parker.com

LV – Latvia, Riga
Tel: +371 6 745 2601
parker.latvia@parker.com

MX – Mexico, Apodaca
Tel: +52 81 8156 6000

MY – Malaysia, Shah Alam
Tel: +60 3 7849 0800

NL – The Netherlands, Oldenzaal
Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Ski
Tel: +47 64 91 10 00
parker.norway@parker.com

NZ – New Zealand, Mt Wellington
Tel: +64 9 574 1744

PL – Poland, Warsaw
Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal, Leca da Palmeira
Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest
Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow
Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga
Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SG – Singapore
Tel: +65 6887 6300

SK – Slovakia, Banská Bystrica
Tel: +421 484 162 252
parker.slovakia@parker.com

SL – Slovenia, Novo Mesto
Tel: +386 7 337 6650
parker.slovenia@parker.com

TH – Thailand, Bangkok
Tel: +662 717 8140

TR – Turkey, Istanbul
Tel: +90 216 4997081
parker.turkey@parker.com

TW – Taiwan, Taipei
Tel: +886 2 2298 8987

UA – Ukraine, Kiev
Tel: +380 44 494 2731
parker.ukraine@parker.com

UK – United Kingdom, Warwick
Tel: +44 (0)1926 317 878
parker.uk@parker.com

US – USA, Cleveland (industrial)
Tel: +1 216 896 3000

US – USA, Lincolnshire (mobile)
Tel: +1 847 821 1500

VE – Venezuela, Caracas
Tel: +58 212 238 5422

ZA – South Africa, Kempton Park
Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

HYGE Ed. 2009-08-12

