



aerospace  
climate control  
electromechanical  
**filtration**  
fluid & gas handling  
hydraulics  
pneumatics  
process control  
sealing & shielding



## Why Buy Racor?

An objective look at unauthorised  
Racor fuel filter copies



# Racor takes pride in manufacturing a quality product that is fit for purpose and durable in all applications.

The manufacturing and design teams working at Racor are constantly striving to improve product performance to remain the leader in fuel filtration.



Some of the benefits a customer can expect to receive when buying a genuine Racor product are:

- OEM Quality and Validation
- Quality Certified Production Facilities to ISOTS16949
- Qualified Products and Materials
- Correct Performance and Durability
- Up to 70% Increased Service Life
- Extensive QA and Development Facilities
- \$10Bn Corporation: Continuity of Product/Service.

Extensive laboratory testing facilities at the Racor factory give assurance to all customers that the genuine Racor product will meet the demands of the engine system.

- ISO13353 Filter Efficiency/DHC
- ISO19438 Filter Efficiency/DHC
- SAE J 905 Filter Efficiency
- SAE J 1985 Filter Efficiency
- ISO 4020 6.1 Filter Cleanliness
- ISO 4020 6.2 /ISO 2942 Filter Integrity
- ISO 4020 6.3 Filter Differential Pressure
- ISO 4020 6.5 Water Separation
- ISO 4020 6.6 Filter Element Collapse
- ISO 4020 6.7 Hydrostatic Burst
- ISO 4020 6.8 Pressure Pulse Fatigue
- SAE J1839 Course Droplet Removal
- SAE J1488 Emulsified Water Removal
- ASTM B 117 Salt Fog Corrosion
- Numerous Internal Racor Test Standards and Customer Standards

Racor manufacturing locations are manufacturing to the highest possible standards. Some of the quality standards being maintained are listed below.

- QS9000
- ISO TS16949
- ISO14001
- Ford Q1
- UL listed
- Bureau Veritas Listed
- American Bureau of Shipping Listed
- API 5th Edition



# Racor Spin On Series

The Racor Spin on Series has standard primer pumps that tops the list of extensive options that allows bus fleets, truck fleets, RV owners and others to tailor a filter/separator system specifically to their operating requirements.

These options include a choice of three micron ratings for the Aquabloc filter element, 300 watt in head PTC (positive temperature coefficient heater) water sensor and flow rates up to 600 l/hr (160 US gph).



## Pump Diaphragm:

Racor use high quality support laminated high grade rubber fit for life diaphragms. Poor quality pump diaphragms will swell in the fuel, and leak in cold conditions, and eventually wear out under even mild Pressure pulsation/vibration

## Head casting:

Racor validate castings under extreme vibration and climatic conditions to meet chassis and engine specifications. Unlike unauthorised copies.

## Seal Materials:

Crucial in a modern fuel filter, Racor use high quality automotive grade materials in all seals and valves. Poor quality seals will swell excessively In the fuel, and leak in cold conditions

## Filter Can Components:

Racor validate canisters under extreme vibration and climatic conditions to meet chassis and engine specifications. Unlike unauthorised copies.

## Filter Media:

The true heart of the filter- Racor develop proprietary semi synthetic Aquabloc medias to meet the exacting specifications of injection system OEMs. These meet critical water removal and particle efficiency requirements. Copy cats regularly save cost on low quality medias which do not perform, and block up to 70% sooner.

## Coatings and plating:


Racor validate canisters under extreme salt spray and climatic conditions to meet OEM specifications and environmental requirements and are free from banned substances. Unlike unauthorised copies.

## Accessories:

Racor have a wide range of heater and sensor accessories all validated for integrity, EMC Compatibility and safety. Unlike unauthorised copies.

## Clear Bowl:

Racor use a unique and durable clear plastic bowl material with high clarity, excellent UV, Low temp/high temp resistance, impact resistant and impervious to all fuel types. Validated under extreme vibration and climatic conditions to meet strict OEM specifications. Copies often use more economical materials.







# Racor Turbine Series

Every engine runs better with a system that cleans fuel, removes water, heats fuel and senses when it's time for service. The system is the Racor Turbine Series and it's the most complete, most efficient, most reliable high-capacity engine protection you can install.

A system that protects your investment in engines and fuel is a system that contains genuine Racor Turbine Series.



# Common problems with copies that are not genuine Racor filters.

Issue	Concerns with Competitor Copies	Racor Commitment to Quality
<b>Blocked Filter</b>	Low quality media can block 70% sooner than Racor media.	Racor uses Aquabloc media that meets the exacting specifications of injection system OEM's meeting critical water removal and particle efficiency requirements.
<b>Bypassing</b>	Poorly constructed filter elements may bypass internally allowing dirty fuel to reach the engine	Racor use high quality materials and production processes to ISOTS16949 to avoid bypass problems.
<b>Split / Leaking Seal</b>	Poor quality seals will swell excessively, leak and may deteriorate within the service period.	Racor use high quality automotive grade materials. (For example; NBR, HNBR, Viton and bio-diesel compatible.)
<b>Dirty fuel reaching engine</b>	Incorrect efficiency filters will not protect the engine	Replacement to OEM grades will perform as designed for the application.
<b>Water in fuel reaching engine</b>	Few, if any of the copy filter elements work to original equipment levels	Racor use the same media and materials in original equipment and replacement filter elements.
<b>Cold Conditions</b>	Poor quality pump diaphragms and seals will harden and cause leaking. Incorrectly selected media will block in cold conditions.	Racor use high quality material rated for -40 deg C. Racor original applications are correctly selected for operating conditions.
<b>Cracked head casting</b>	Poor quality head castings cannot cope with extreme environmental conditions and vibrations.	Racor products are validated under extreme vibration and climatic conditions.
<b>Contains banned substances</b>	Some copy filters contain banned substances in the canister coating and plating.	Racor canisters contain no banned substances and are validated under extreme salt spray and climatic conditions.
<b>Cracked Clear Bowl</b>	Copy filter bowls are often made from poor quality material that will crack under extreme temperature or continuous vibrations.	Racor use a unique durable clear plastic bowl material with high clarity, excellent UV, low temperature / high temperature resistance, impact resistance and impervious to all fuel types.
<b>Can I buy accessories for my fuel filter?</b>	Unauthorized Racor copies do not always offer accessories. If they do they are likely not to be tested.	Racor have a wide range of heater and sensor accessories that are validated for integrity, EMC compatibility and safety.




# Water separation efficiency

The critical performance factor for any fuel filter is the water separation efficiency. The graph below shows the performance level of the Racor product versus some competitor copies. It is clear to see that the Racor water separators outperforms that of the competitor copies.


Be aware that some of these competitor products fail to remove particulates from the fuel and put the engine system in danger.

Some of the known manufacturers of low cost Racor copies are listed below.

- Griffin
- Separ
- Vetus
- Rauma
- YNY
- Sampiyon
- ASAS
- Chinese R90MER01
- Turbinas Chinas



## Water separation efficiency





**Together, we can** find new opportunities at the click of a mouse.



The Parker Racor Cross Reference and Applications Database is the new stand alone system that enables you to cross reference Racor parts against OEM part numbers, within seconds. With a range of powerful application tools including data sheets, standard reports and fleet finder, it gives you instant access to all the information you need to identify new sales opportunities. **To register now, and obtain your password, email [mday@parker.com](mailto:mday@parker.com)**



ENGINEERING YOUR SUCCESS.

[www.parker.com/rfde](http://www.parker.com/rfde)



**Together, we can** supply over 35,000 interchange elements

Offering immediate availability, competitive prices and quality to match or exceed any other product, Parfit is the one stop shop for all your replacement hydraulic filter elements. Developed with Parker engineering genius, Parfit Interchange elements will replace any filter element, whatever the original equipment specification, all from one single source.

**For more information, visit [www.parkerhfde.com/parfit](http://www.parkerhfde.com/parfit) or [www.parker.com/parfit](http://www.parker.com/parfit)**



ENGINEERING YOUR SUCCESS.

[www.parker.com/parfit](http://www.parker.com/parfit)



# Parker Worldwide

## Europe, Middle East, Africa

**AE – United Arab Emirates,**  
Dubai

Tel: +971 4 8127100  
parker.me@parker.com

**AT – Austria,** Wiener Neustadt

Tel: +43 (0)2622 23501-0  
parker.austria@parker.com

**AT – Eastern Europe,** Wiener  
Neustadt

Tel: +43 (0)2622 23501 900  
parker.easteurope@parker.com

**AZ – Azerbaijan,** Baku

Tel: +994 50 2233 458  
parker.azerbaijan@parker.com

**BE/LU – Belgium,** Nivelles

Tel: +32 (0)67 280 900  
parker.belgium@parker.com

**BY – Belarus,** Minsk

Tel: +375 17 209 9399  
parker.belarus@parker.com

**CH – Switzerland,** Etoy

Tel: +41 (0)21 821 87 00  
parker.switzerland@parker.com

**CZ – Czech Republic,** Klecany

Tel: +420 284 083 111  
parker.czechrepublic@parker.com

**DE – Germany,** Kaarst

Tel: +49 (0)2131 4016 0  
parker.germany@parker.com

**DK – Denmark,** Ballerup

Tel: +45 43 56 04 00  
parker.denmark@parker.com

**ES – Spain,** Madrid

Tel: +34 902 330 001  
parker.spain@parker.com

**FI – Finland,** Vantaa

Tel: +358 (0)20 753 2500  
parker.finland@parker.com

**FR – France,** Contamine s/Arve

Tel: +33 (0)4 50 25 80 25  
parker.france@parker.com

**GR – Greece,** Athens

Tel: +30 210 933 6450  
parker.greece@parker.com

**HU – Hungary,** Budapest

Tel: +36 1 220 4155  
parker.hungary@parker.com

**IE – Ireland,** Dublin

Tel: +353 (0)1 466 6370  
parker.ireland@parker.com

**IT – Italy,** Corsico (MI)

Tel: +39 02 45 19 21  
parker.italy@parker.com

**KZ – Kazakhstan,** Almaty

Tel: +7 7272 505 800  
parker.easteurope@parker.com

**NL – The Netherlands,** Oldenzaal

Tel: +31 (0)541 585 000  
parker.nl@parker.com

**NO – Norway,** Asker

Tel: +47 66 75 34 00  
parker.norway@parker.com

**PL – Poland,** Warsaw

Tel: +48 (0)22 573 24 00  
parker.poland@parker.com

**PT – Portugal,** Leca da Palmeira

Tel: +351 22 999 7360  
parker.portugal@parker.com

**RO – Romania,** Bucharest

Tel: +40 21 252 1382  
parker.romania@parker.com

**RU – Russia,** Moscow

Tel: +7 495 645-2156  
parker.russia@parker.com

**SE – Sweden,** Spånga

Tel: +46 (0)8 59 79 50 00  
parker.sweden@parker.com

**SK – Slovakia,** Banská Bystrica

Tel: +421 484 162 252  
parker.slovakia@parker.com

**SL – Slovenia,** Novo Mesto

Tel: +386 7 337 6650  
parker.slovenia@parker.com

**TR – Turkey,** Istanbul

Tel: +90 216 4997081  
parker.turkey@parker.com

**UA – Ukraine,** Kiev

Tel: +380 44 494 2731  
parker.ukraine@parker.com

**UK – United Kingdom,** Warwick

Tel: +44 (0)1926 317 878  
parker.uk@parker.com

**ZA – South Africa,** Kempton Park

Tel: +27 (0)11 961 0700  
parker.southafrica@parker.com

## North America

**CA – Canada,** Milton, Ontario

Tel: +1 905 693 3000

**US – USA,** Cleveland

Tel: +1 216 896 3000

## Asia Pacific

**AU – Australia,** Castle Hill

Tel: +61 (0)2-9634 7777

**CN – China,** Shanghai

Tel: +86 21 2899 5000

**HK – Hong Kong**

Tel: +852 2428 8008

**IN – India,** Mumbai

Tel: +91 22 6513 7081-85

**JP – Japan,** Tokyo

Tel: +81 (0)3 6408 3901

**KR – South Korea,** Seoul

Tel: +82 2 559 0400

**MY – Malaysia,** Shah Alam

Tel: +60 3 7849 0800

**NZ – New Zealand,** Mt Wellington

Tel: +64 9 574 1744

**SG – Singapore**

Tel: +65 6887 6300

**TH – Thailand,** Bangkok

Tel: +662 186 7000-99

**TW – Taiwan,** Taipei

Tel: +886 2 2298 8987

## South America

**AR – Argentina,** Buenos Aires

Tel: +54 3327 44 4129

**BR – Brazil,** Sao Jose dos Campos

Tel: +55 800 727 5374

**CL – Chile,** Santiago

Tel: +56 2 623 1216

**MX – Mexico,** Apodaca

Tel: +52 81 8156 6000

### EMEA Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL,  
IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

### US Product Information Centre

Toll-free number: 1-800-27 27 537

www.parker.com

