


CCCTX

Extra Long Male Elbow
37° Flare / NPTF

SAE 071602



Y* – Across wrench flats

| TUBE FITTING PART # | HOSE FITTING PART # | END SIZE | | T TUBE END UN/UNF-2A | D DRILL (in.) | D1 DRILL (in.) | M (in.) | N4 (in.) | XX AFTER ASSY (in.) | Y (in.) | Dynamic Pressure (x 1,000 PSI) | | |
|---------------------|---------------------|----------|----------------|----------------------|---------------|----------------|---------|----------|---------------------|---------|--------------------------------|-----|-----|
| | | 1 (in.) | 2 NPTF | | | | | | | | -S | -SS | -B |
| 4 CCCTX | 5703-2-4 | 1/4 | 1/8 - 27 | 7/16 - 20 | 0.172 | 0.188 | 0.89 | 1.56 | 1.36 | 7/16 | 6.0 | 6.0 | 3.3 |
| 4-4 CCCTX | 5703-4-4 | 1/4 | 1/4 - 18 | 7/16 - 20 | 0.172 | 0.281 | 1.05 | 2.07 | 1.69 | 9/16 | 6.0 | 6.0 | 3.3 |
| 5 CCCTX | 5703-2-5 | 5/16 | 1/8 - 27 | 1/2 - 20 | 0.234 | 0.188 | 0.97 | 1.63 | 1.40 | 9/16 | 6.0 | 6.0 | 3.3 |
| 6 CCCTX | 5703-4-6 | 3/8 | 1/4 - 18 | 9/16 - 18 | 0.297 | 0.281 | 1.06 | 2.07 | 1.69 | 9/16 | 6.0 | 6.0 | 3.3 |
| 6-6 CCCTX | 5703-6-6 | 3/8 | 3/8 - 18 | 9/16 - 18 | 0.297 | 0.406 | 1.14 | 2.34 | 1.99 | 3/4 | 6.0 | 6.0 | 3.3 |
| 8 CCCTX | 5703-6-8 | 1/2 | 3/8 - 18 | 3/4 - 16 | 0.391 | 0.406 | 1.25 | 2.34 | 1.99 | 3/4 | 6.0 | 6.0 | 3.3 |
| 8-8 CCCTX | 5703-8-8 | 1/2 | 1/2 - 14 | 3/4 - 16 | 0.391 | 0.531 | 1.33 | 2.87 | 2.38 | 7/8 | 6.0 | 6.0 | 3.3 |
| 10 CCCTX | 5703-8-10 | 5/8 | 1/2 - 14 | 7/8 - 14 | 0.484 | 0.531 | 1.45 | 2.87 | 2.38 | 7/8 | 5.0 | 5.0 | 3.3 |
| 12 CCCTX | 5703-12-12 | 3/4 | 3/4 - 14 | 1 1/16 - 12 | 0.610 | 0.719 | 1.66 | 3.28 | 2.74 | 1 1/16 | 4.0 | 4.0 | 2.3 |
| 16 CCCTX | 5703-16-16 | 1 | 1 - 11 1/2 | 1 5/16 - 12 | 0.844 | 0.938 | 1.81 | 4.05 | 3.40 | 1 5/16 | 3.0 | 3.0 | 2.0 |
| 20 CCCTX | 5703-20-20 | 1 1/4 | 1 1/4 - 11 1/2 | 1 5/8 - 12 | 1.078 | 1.250 | 2.06 | 5.00 | 4.46 | 1 5/8 | 2.5 | 2.5 | 1.6 |

Note: All steel "CCCTX" fittings have a 30° chamfer for sealing with NPCSM swivel type fittings.

Dimensions and pressures for reference only, subject to change.

