

955 Series

UHP Stainless Steel Diaphragm Valve
High Flow, Welded

aerospace
climate control
electromechanical
filtration
fluid & gas handling
hydraulics
pneumatics
process control
sealing & shielding

Value Proposition:

The 955 high purity diaphragm valves offer high flow in a compact device. The 955 valves offer a variety of manual operators to fit the customer's system requirements. Both the 955 manual and the Air Operated versions can be used in UHP systems up to 250 psig.

The 955AOP is ideal for low vapor pressure gas delivery systems.



Contact Information:

Parker Hannifin Corporation
Veriflo Division
250 Canal Blvd
Richmond, California 94804

phone 510 235 9590
fax 510 232 7396
veriflo.sales@parker.com

www.parker.com/veriflo
Mobile App: m.parker.com/veriflo

Product Features:


- Standard surface finish of 5 micro inch Ra
- Internally threadless and springless
- Fully functional from vacuum to 250 psig
- High cycle life (including corrosive service)
- 100% Helium leak tested
- Standard full internal electroplish
- Minimal particle generation and particle entrapment areas
- Vericlean™, Veriflo's low sulfur high purity 316L Stainless Steel enhances electropolishing, welding, and corrosion resistance



ENGINEERING YOUR SUCCESS.

955 Series

Dimensional Drawing



Actuator Style	Actuator Diameter (A)	Height (B)	Lever Radius (C)
AOPLPNC	1.55	3.44	-
AOPLPNO	1.29	3.05	-
G	-	*	-
I	1.70	2.65	-
L	-	2.63	1.75
M	-	2.63	.75
S	2.00	2.90	-

Port Style	End-To-End Length (D)
FS	2.96
FS (Optional)	2.30
FS (Optional)	2.78
FS8	4.20
TS	2.25
TS6	2.25
TS8	2.25

* See dimensional drawing.

955 Series

Ordering Information

Build a 955 Series valve by replacing the numbered symbols with an option from the corresponding tables below.

Contact factory for most up to date lead time information.

Blue = Configurations that have selections in blue will require a price quote from the factory.

Sample: **9** **55** **L** **S** **FS** **FM** **VESP**
Finished Order: **955LSFSFMVESP**

1 **Basic Series**
55 = 955

2 **Type**
AOPLPNC = Air Operated, Low Pressure, Normally Closed *Air Connection is 1/8" NPT*
AOPLPNO = Air Operated, Low Pressure, Normally Open *Air Connection is 1/8" NPT*
G = Toggle
I = Indicating Handwheel
L = Lever
M = Mini-Lever

3 **Body Material**
S = 316L Stainless Steel

4 **Port Style**
FS = 1/4" Face Seal *Standard only when configured as FSFS*
FS8 = 1/2" Face Seal *Standard only when configured as FS8FS8*
TS = 1/4" Tube Stub *Standard only when configured as TSTS*
TS6 = 3/8" Tube Stub *Standard only when configured as TS6TS6*
TS8 = 1/2" Tube Stub *Standard only when configured as TS8TS8*

Note: *Combinations of Port Style options may have an extended lead time.*

Note: *For Multiport: See 25000178 Valve Selection Guide. All Multiport configurations are Special Order.*

5 **Port Configuration**
M = Male Face Seal
F = Female Face Seal

6 **Optional Features**
This section can have multiple options
BL008 = Bleed Valve .008 Orifice
BL015 = Bleed Valve .015 Orifice
LK = LockOut-TagOut
LK includes LockOut-TagOut bracket for G-Type Valve; LOTO Clamp for M type Valve
PM = Panel Mount *Not available with Indicating Handwheel (I)*
PEEK = PEEK™ Seat
VESP = Vespel® Seat
Recommended for Nitrous Oxide (N2O) Service
2.3 = 2.3" End-To-End 1/4" FS Only
2.78 = 2.78" End-To-End 1/4" FS Only

955 Series

Specifications

Materials of Construction	
Wetted	
Body	VeriClean™ 316L Stainless Steel
Diaphragm	Elgiloy® or equivalent
Seat Options	PCTFE (std), PEEK™ or Vespel®
Non-wetted	
Cap	17-4 Stainless Steel
Nut	316L Stainless Steel
Actuator Housing	Anodized Aluminum
Operating Conditions	
<i>(Operating limits based upon pressure applied at inlet port.)</i>	
Maximum Pressure	
AOPLPNO, G	125 psig (8.62 barg)
AOPLPNC, I, L, M	250 psig (17.22 barg)
Minimum Pressure	Vacuum
Temperature	-40°F to 150°F (-40°C to 66°C)
AOP Actuation Pressure	75 psig (5 barg) nominal
AOP Air Inlet	1/8" NPT

Functional Performance	
Design	
Proof Pressure	375 psig (26 barg)
Burst Pressure	750 psig (52 barg)
Flow Capacity	C_v 0.55
Leak Rate	
Internal	Inboard Test Method
External	$\leq 4 \times 10^{-9}$ scc/sec He
	$\leq 2 \times 10^{-10}$ scc/sec He
Surface Finish	5 micro inch Ra
Internal Volume	3.29 cc (including Face Seal Fittings)
Approx. Weight	0.81 lbs. (0.36 kg)

Vespel® is a registered trademark of DuPont Performance Elastomers L.L.C.
Elgiloy® is a registered trademark of Elgiloy Company
VeriClean™ is a trademark of Parker Hannifin Corporation
PEEK™ is a trademark of Victrex plc.

For additional information on materials of construction, functional performance and operating conditions, please contact factory.

OFFER OF SALE:

The items described in this document are hereby offered for sale by Parker-Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the detailed "Offer of Sale" elsewhere in this document or available at www.parker.com/veriflo



FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE. THIS DOCUMENT IS FOR REFERENCE ONLY. PLEASE CONSULT FACTORY FOR LATEST PRODUCT DRAWINGS AND SPECIFICATIONS

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

The products described herein, including without limitation, product features, specifications, designs, availability and pricing are subject to change by Parker Hannifin Corp and its subsidiaries at any time without notice.

Proposition 65 Warning: This product contains chemicals known to the state of California to cause cancer or birth defects or other reproductive harm.

© 2009 Parker Hannifin Corporation



Use mobile device to scan this QR Code.

LitPN: 25000016 Rev: J Date of Issue 03/2017



ENGINEERING YOUR SUCCESS.