

CoolTherm™ SC-6726 Thermally Conductive Silicone Encapsulant

Description

LORD CoolTherm™ SC-6726 encapsulant is a two-component, addition-cure silicone system for use in applications where high temperature service is required. CoolTherm SC-6726 encapsulant adheres to most substrates without the use of a primer.

Features and Benefits

Broad Temperature Range – can be used on parts and devices that experience operating temperatures from -55°C to +200°C.

Reversion Resistant – provides excellent reversion resistance at high temperatures; will not cause corrosion.

Application

Mixing – Thoroughly mix each component prior to combining resin and hardener. Mix CoolTherm SC-6726 resin with CoolTherm SC-6726 hardener at a 1:1 ratio, by weight or volume.

Applying – Apply encapsulant using automatic meter/mix/dispense equipment.

Avoid applying CoolTherm SC-6726 encapsulant to surfaces that contain cure inhibiting ingredients, such as amines, sulfur, or tin salts. If bonding surface is in question, apply a test patch of encapsulant to the surface and allow it to set for the normal cure time.

Curing – Allow encapsulant to cure for 4 hours at 85°C. This time-at-temperature profile refers to the time the material should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay material actually reaching the target temperature. An overnight post cure at 85°C is recommended to obtain optimum properties, especially for large volumes.

Typical Properties*

	SC-6726 Resin	SC-6726 Hardener	Mixed
Appearance	Red Paste	Gray Paste	Red Paste
Viscosity, cps @ 25°C	56,000	56,000	56,000
Specific Gravity	2.26	2.12	2.20
Working Life, days @ 25°C	–	–	3-5

*Data is typical and not to be used for specification purposes.

LORD TECHNICAL DATA

Typical Cured Properties*

Volume Resistivity, ohm-cm @ 25°C ASTM D 257	1 x 10 ¹⁴
Thermal Conductivity, W/mK	0.8
Hardness Shore A	70
Tensile Strength, psi	600
Elongation at Break, %	60
Dielectric Strength, V/mil	350
Dielectric Constant @ 100 Hz	4.0
Dissipation Factor @ 100 Hz	0.02

*Data is typical and not to be used for specification purposes.

Shelf Life/Storage

Shelf life of each component is six months from date of manufacture when stored at 25°C in original, unopened container.

Cautionary Information

Before using this or any LORD product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Values stated in this technical data sheet represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as LORD Corporation has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, LORD Corporation does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

CoolTherm and "Ask Us How" are trademarks of LORD Corporation or one of its subsidiaries.

LORD provides valuable expertise in adhesives and coatings, vibration and motion control, and magnetically responsive technologies. Our people work in collaboration with our customers to help them increase the value of their products. Innovative and responsive in an ever-changing marketplace, we are focused on providing solutions for our customers worldwide ... Ask Us How.

LORD Corporation World Headquarters

111 Lord Drive
Cary, NC 27511-7923
USA

Customer Support Center (in United States & Canada)

+1 877 ASK LORD (275 5673)

www.lord.com

For a listing of our worldwide locations, visit LORD.com.

©2018 LORD Corporation OD DS3742 (Rev.2 1/18)

LORD
AskUsHow™