

Compound N8526

HNBR, black

Compound Data Sheet

Creator

JH / 11.06.2021

Print-Date

03.11.2023

Status

Release

Data created electronically. This document is not subject to change management.
Not signed.

Physical properties

Test	Norm	Specimen	Ref. Value	Typ. Value	Unit
Hardness	DIN ISO 48-4	> 6 mm	90±5	90	Shore A
Density	DIN EN ISO 1183-1		1.24±0.02	1.24	g/cm ³
Tensile strength	DIN 53 504	S2	≥ 15	23.1	N/mm ²
Ultimate elongation	DIN 53 504	S2	≥ 100	216	%
Tear strength	ISO 34-1 B	Methode B Verfahren (b)		29.9	N/mm
Compression set 24h / 150°C	DIN 53 517	Test body 1 deformation 25%		37.7	%
Low temperature properties Tonset TMA	VDA 675117	Ø 5x2 mm		-16	°C

Approvals

Aging Tests

Medium	Time (h)	Temp. (°C)	Norm	Properties		Typical value	
				Δ Hardness (ShA)	Δ Volume (%)	Δ RF (%)	Δ RD (%)
ASTM-1	168	100	DIN ISO 1817	+1	-1.1		
IRM-902	168	100	DIN ISO 1817	-4	+4.8		
IRM-903	168	100	DIN ISO 1817	-7	+13.4		
tap water	168	100	DIN ISO 1817	-3	+4.7		

The test results are mean values and represent typical material properties. They are not to be used as specification values.
These test results are gained under usual laboratory conditions and do not necessarily correspond to results measured on finished goods.
The compound information does not release the user from the necessity to conduct his own testing.
We reserve the right to make technical alterations.
© 2020, Parker-Hannifin Corporation. All Rights Reserved. Subject to change.



Parker Hannifin Manufacturing Germany GmbH & Co.KG
Engineered Materials Group Europe
Prädifa Technology Division
Arnold-Jäger-Str. 1
74321 Bietigheim-Bissingen • Germany
Tel. +49 (0) 7142 351-0 • Fax +49 (0) 7142 351-293