

LORD® 7545 URETHANE ADHESIVE

Technical Data Sheet

LORD® 7545 adhesive is an equal-mix, two-component urethane adhesive system used to bond FRP, SMC and other plastics with little surface preparation. This adhesive also bonds primed metals and various combinations of dissimilar substrates. LORD 7545 adhesive system is available in a range of working times to accommodate a wide variety of process requirements.

Features and Benefits

Durable: demonstrates high strength and excellent durability for structural applications.

Non-Flammable: exceeds U.S. DOT requirements for non-flammability and does not require explosion-proof equipment.

Suitable Appearance: off-white color of cured adhesive provides an acceptable appearance when non-painted or visible.

Environmentally Recommended: does not contain ozone depleting chemicals.

Environmentally Resistant: resists weathering, humidity and salt spray.

Chemically Resistant: solvent resistant when cured. Painting and most cleaning processes do not affect bond strength.

Non-Sag: remains in position when applied on vertical or overhead surfaces, allowing for greater process flexibility.

Application

Surface Preparation: Surfaces should be free of grease, dirt and other contaminants. For plastics, clean the surface with a dry rag wipe or a rag dampened with solvent. For metals, prime or grit blast the surface, then solvent wash for optimum bond performance.

Mixing: Mix LORD 7545-A resin with the appropriate curative at a 1:1 ratio, by volume. Handheld cartridges will automatically dispense the correct volumetric ratio of each component. Once mixed, the adhesive cures rapidly.

Applying: Apply adhesive using handheld cartridges or automatic meter/mix/dispense equipment.

- Handheld Cartridges
 1. Load the cartridge into the applicator gun and remove the end caps.
 2. Level the plungers by expelling a small amount of material to ensure both sides are level.
 3. Attach mixing tip and expel a mixer's length of adhesive.
 4. Apply adhesive to substrate and mate the parts within the working time of the adhesive. Clamp in position until adhesive reaches handling strength.
- Meter/Mix/Dispense Equipment
Contact your Parker Lord representative if assistance is needed using this equipment.

For optimum adhesion, bondline thickness of LORD 7545 adhesive should be 10-40 mil (254-1016 micron). However, large gaps may be filled where mating surfaces are irregular.

Typical Properties*

| | 7545-A Resin | 7545-G Curative | 7545-B Curative | 7545-C Curative | 7545-D Curative | 7545-E Curative | 7545-F Curative |
|--|----------------------------|----------------------------|-----------------------------|----------------------------|-----------------------------|----------------------------|----------------------------|
| Appearance | Brown Paste | Black Paste | Off-white or Black Paste | Off-white Paste | Off-white or Black Paste | Off-white Paste | Off-white Paste |
| Viscosity, cP @ 77°F (25°C) Brookfield | 25,000 - 70,000 | 230,000 - 650,000 | 230,000 - 650,000 | 230,000 - 650,000 | 230,000 - 650,000 | 230,000 - 650,000 | 230,000 - 650,000 |
| Density lb/gal (kg/m ³) | 12.5 -12.8 (1498 -1534) | 10.8 -11.2 (1294 -1342) | 10.8 -11.2 (1294 -1342) | 10.8 -11.2 (1294 -1342) | 10.6 -11.0 (1270 -1318) | 10.6 -11.0 (1270 -1318) | 10.5 -11.1 (1258 -1330) |
| Flash Point, °F (°C) Closed Cup | >200 (>93) | >200 (>93) | >200 (>93) | >200 (>93) | >200 (>93) | >200 (>93) | >200 (>93) |

*Data is typical and not to be used for specification purposes.

Curing: LORD 7545 adhesive will cure to full strength in 24 hours at 75°F (24°C), depending on the curative used. Cure rate can be accelerated by applying modest heat (temperatures up to 250°F [121°C]).

Cleanup: Clean equipment and tools prior to the adhesive cure with organic solvents such as acetone or methyl ethyl ketone (MEK). Do not use alcohol. Once adhesive is cured, heat the adhesive to 300°F (149°C) or above to soften the adhesive. This allows the parts to be separated and the adhesive to be more easily removed. Some success may be achieved with commercial adhesive strippers.

Shelf Life/Storage

Shelf life is six months from date of shipment when stored in a clean, dry environment at 65-85°F (18-30°C) in original, unopened container.

After opening, protect adhesive from excessive exposure to moisture by installing desiccant cartridges and/or using dry nitrogen as an inert cover.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Typical Properties* of Resin Mixed with Curative

| | 7545-A/G | 7545-A/B | 7545-A/C | 7545-A/D | 7545-A/E | 7545-A/F |
|---|------------|------------|------------|------------|-------------|-------------|
| Mix Ratio, Resin to Curative by Volume | 1:1 | 1:1 | 1:1 | 1:1 | 1:1 | 1:1 |
| by Weight | 1:0.87 | 1:0.87 | 1:0.87 | 1:0.85 | 1:0.85 | 1:0.85 |
| Solids Content by Weight, % | 100 | 100 | 100 | 100 | 100 | 100 |
| Working Time, minutes @ 75°F (24°C) | 1.5 | 3 - 5 | 6 - 8 | 11-18 | 22 - 38 | 45 - 65 |
| Time to Handling Strength @ 75°F (24°C) | 10 minutes | 30 minutes | 60 minutes | 90 minutes | 2 - 3 hours | 4 - 5 hours |

*Data is typical and not to be used for specification purposes.

Typical Cured Properties*

| | |
|---|--------------|
| Hardness Shore D | 67 |
| Tensile Strength at Break, psi (MPa) ASTM D882 | 3000 (20.7) |
| Elongation, % ASTM D882 | 72 |
| Young's Modulus, psi (MPa) ASTM D882 | 22,200 (153) |
| Glass Transition Temperature (T _g), °F (°C) ASTM D3418 | 116 (47) |
| Moisture Absorption, % ASTM D570 | <1 |

*Data is typical and not to be used for specification purposes.

Bond Performance*

| Substrates | CFRP | ABS | PC/ABS | E-coated Steel |
|---|-------------|-----------|-----------|----------------|
| Lap Shear @ 70°F (21°C), psi (MPa) | 2900 (20.0) | 550 (3.8) | 900 (6.2) | 2350 (16.2) |
| Failure Mode | SF | SF | SF | COH |
| Lap Shear @ -40°F (-40°C), psi (MPa) | 2600 (17.9) | 400 (2.8) | 550 (3.8) | 3300 (22.7) |
| Failure Mode | SF | SF | SF | ADH |
| Lap Shear @ 150°F (65°C), psi (MPa) | 1150 (7.9) | 350 (2.4) | 550 (3.8) | 1100 (7.6) |
| Failure Mode | COH | COH | COH | COH |
| Lap Shear after 500 hours @ 150°F (65°C), 85% RH, psi (MPa) | 2700 (18.6) | 550 (3.8) | 750 (5.2) | 2400 (16.5) |
| Failure Mode | SF | SF | COH | COH |
| Lap Shear after 168 hours Water Immersion @ 150°F (65°C), psi (MPa) | 2650 (18.3) | 550 (3.8) | 650 (4.5) | 2450 (16.9) |
| Failure Mode | COH/SF | SF | COH/SF | COH |
| Lap Shear after 500 hours Salt Spray Exposure, psi (MPa) | 2650 (18.3) | 550 (3.8) | 650 (4.5) | 2400 (16.5) |
| Failure Mode | SF | SF | SF | COH |
| Lap Shear after 500 hours @ 150°F (65°C), psi (MPa) | 2900 (20.0) | 550 (3.8) | 850 (5.8) | 1500 (10.3) |
| Failure Mode | SF | SF | SF | COH |
| T-Peel, pli (N/mm) | - | - | - | 33 (5.8) |
| Failure Mode | | | | COH |

Test Specimens

| | |
|---|---|
| Carbon Fiber Reinforce Plastic (CFRP) | 2x2 twill in epoxy resin matrix 3 mm thick |
| Acrylonitrile Butadiene Styrene Plastic (ABS) | 5 mm thick |
| Polycarbonate/ABS Blend (PC/ABS) | 5 mm thick |
| E-coated Steel | 1008 steel, 8 mm thick coated with PPG E6060C |

Failure Mode Definition

Abbreviation

| | |
|------------------|-----|
| Adhesive Failure | ADH |
| Cohesive Failure | COH |
| Stock Failure | SF |

*Data is typical and not to be used for specification purposes.

Parker Lord
Engineered Materials Group
 111 LORD Drive
 Cary, NC 27511-7923
 USA
www.parker.com/APS

DS3446E OD 03/25 Rev.5

Information and specifications subject to change without notice and without liability therefor.
 Trademarks used herein are the property of their respective owners.

© 2025 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.