

# LORD® 850S AND 852S TOUGHENED STRUCTURAL ACRYLIC ADHESIVES WITH LORD ACCELERATOR 25GB

## Technical Data Sheet

LORD® 850S and 852S acrylic adhesives in combination with LORD Accelerator 25GB can be used to replace welding, brazing, riveting and other mechanical fastening methods. These toughened structural adhesives perform particularly well in low-temperature environments and applications that are subject to high impact, high peel loads or high fatigue. LORD 850S and 852S adhesives provide a range of working times to accommodate a wide variety of process requirements.

LORD 850S and 852S adhesives, when mixed with LORD Accelerator 25GB, create adhesive systems that bond a wide variety of prepared or unprepared metals and some engineered plastics. These adhesive systems are specifically formulated to provide the highest impact and peel strengths available in a room temperature curing adhesive with exceptional cohesive failure mode.

LORD Accelerator 25GB allows precise control of the adhesive bondline thickness due to its content of glass beads. For further detailed information, refer to the LORD Accelerator 25GB data sheet.

### Features and Benefits

**Versatile:** bonds a wide range of unprepared metals with minimal substrate preparation, as well as polymer composite substrates such as FRP.

**Durable:** provides high strength for high-end structural bonding applications; 100% elongation improves impact strength and fatigue resistance.

**Temperature Resistant:** performs at temperatures from -40°F to +300°F (-40°C to +149°C); tolerates e-coat bake with cohesive failure at 338°F (170°C).

Note: Based on test results, LORD 850S/25GB adhesive system exhibits post bake/powder coating temperature resistance up to 400°F (204°C) for 90 minutes. Customer specific substrates should always be evaluated for specific application performance.

**Environmentally Resistant:** resists dilute acids, alkalis, solvents, greases, oils, moisture, salt spray and weathering; provides excellent resistance to indirect UV exposure.

**Non-Sag:** remains in position when applied on vertical or overhead surfaces, allowing for greater process flexibility.

### Application

**Surface Preparation:** Remove grease, loose contamination or poorly adhering oxides from metal surfaces. Normal amounts of mill oils and drawing compounds usually do not present a problem in adhesion. Most plastics require a simple cleaning before bonding. Some may require abrading for optimum performance.

**Mixing:** Mix LORD 850S or 852S adhesive with the proper amount of LORD Accelerator 25GB. Handheld cartridges will automatically dispense the correct volumetric ratio of each component. Even color distribution visually indicates a thorough mix. Once mixed, the adhesive cures rapidly.

### Typical Properties\*

	850S	852S
Appearance	Amber Paste	Amber Paste
Viscosity, cP @ 77°F (25°F) Brookfield	150,000 - 550,000	150,000 - 550,000
Density lb/gal (kg/m <sup>3</sup> )	8.00 - 8.30 (959 - 995)	8.00 - 8.30 (959 - 995)
Flash Point (Seta), °C (°F)	59 (15)	59 (15)

\*Data is typical and not to be used for specification purposes.

**Applying:** Apply adhesive using handheld cartridges or automatic meter/mix/dispense equipment.

- Handheld Cartridges
  1. Load the cartridge into the applicator gun and remove the end caps.
  2. Level the plungers by expelling a small amount of material to ensure both sides are level.
  3. Attach mixing tip and expel a mixer's length of adhesive.
  4. Apply adhesive to substrate and mate the parts within the working time of the adhesive. Clamp in position until adhesive reaches handling strength.

Do not re-expose adhesive to air once parts are mated. Mated parts should be repositioned by sliding to achieve proper alignment.

- Meter/Mix/Dispense Equipment  
Contact your Parker Lord representative if assistance is needed using this equipment.

**Curing:** Cure begins immediately once adhesive and accelerator are mixed. Time to handling strength is dependent on adhesive used. Complete cure requires 2-5 hours at room temperature. Mating surfaces must be held in contact during the entire curing process.

Cure rate can be accelerated by applying modest heat [ $<150^{\circ}\text{F}$  ( $<66^{\circ}\text{C}$ )]. Customer should evaluate adhesive strength and quality through a functional trial of their intended application process. Consult with Parker Lord application engineer for recommended maximum temperature dependent on chosen adhesive cure speed.

**Cleanup:** Clean equipment and tools prior to the adhesive cure with solvents such as isopropyl alcohol, acetone or methyl ethyl ketone (MEK). Once adhesive is cured, heat the adhesive to  $400^{\circ}\text{F}$  ( $204^{\circ}\text{C}$ ) or above to soften the adhesive. This allows the parts to be separated and the adhesive to be more easily removed.

## Shelf Life/Storage

Shelf life is six months when stored below  $77^{\circ}\text{F}$  ( $25^{\circ}\text{C}$ ) in original, unopened container. Storage temperatures of  $40-50^{\circ}\text{F}$  ( $4-10^{\circ}\text{C}$ ) are recommended. If stored cold, allow product to return to room temperature before using. Protect from exposure to direct sunlight.

LORD 850S and 852S adhesives are flammable. Do not store or use near heat, sparks or open flame.

## Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

*For industrial/commercial use only.* Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

## Typical Properties\* of Adhesive Mixed with Recommended Accelerator

	850S/25GB	852S/25GB
Mix Ratio by Volume, Adhesive to Accelerator	10:1	10:1
Solids Content, %	100	100
Working Time, minutes @ $75^{\circ}\text{F}$ ( $24^{\circ}\text{C}$ )	6-10	20-25
Time to Handling Strength, minutes @ $75^{\circ}\text{F}$ ( $24^{\circ}\text{C}$ ) 50 psi Shear	18-24	50-70
Full Cure Time, hours @ $75^{\circ}\text{F}$ ( $24^{\circ}\text{C}$ )	2**	5
Mixed Appearance	Red Paste	Red Paste

\*Data is typical and not to be used for specification purposes.

\*\*Reaches 90% of its full strength after 1 hour.

## Typical Cured Properties\* - LORD Adhesive/LORD Accelerator 25GB

	850S	852S
Hardness Shore D	66	67
Tensile Strength at Break, psi (MPa) ASTM D638, modified	2610 (18.0)	2683 (18.5)
Elongation, % ASTM D638, modified	100	100
Young's Modulus, psi (MPa) ASTM D638, modified	105,000 (724)	125,000 (862)
Glass Transition Temperature (Tg), $^{\circ}\text{F}$ ( $^{\circ}\text{C}$ ) ASTM E1640-99, by DMA	176 (80)	178 (81)

\*Data is typical and not to be used for specification purposes.

## Bond Performance\* – LORD 850S Adhesive/LORD Accelerator 25GB

Substrates	Aluminum to Aluminum	EZG to EZG	CRS to CRS
Lap Shear @ Room Temperature, psi (MPa)	2617 (18.1)	2081 (14.4)	2885 (19.9)
Failure Mode	C	C	C
Lap Shear @ 180°F (82°C), psi (MPa)	1044 (7.2)	1075 (7.4)	1157 (8.0)
Failure Mode	C	C	C
Lap Shear @ -30°F (-34°C), psi (MPa)	3183 (22.0)	2568 (17.7)	4017 (27.7)
Failure Mode	TLC	TLC	TLC
Lap Shear after 14 days @ 95°F (38°C), 95% RH, psi (MPa)	2584 (17.8)	2046 (14.1)	2790 (19.2)
Failure Mode	C	C	C
Lap Shear after 500 hours Salt Spray Exposure, psi (MPa) ASTM B117	2157 (14.9)	1482 (10.2)	1908 (13.2)
Failure Mode	C/A	C/A	C/A
T-Peel @ Room Temperature, pli (N/cm)	26 (46)	45 (79)	45 (79)
Failure Mode	C	C	C

Substrate	Surface Treatment
Aluminum, 0.032" thick 6061T6	IPA Wipe
Electrogalvanized Steel (EZG), 0.032" thick	IPA Wipe
Cold Rolled Steel (CRS), 0.032" thick	IPA Wipe

Bonded Parameters	Bond Area	Film Thickness	Cure	Mix Ratio
Metal Lap Shears (ASTM D1002)	1.0"x0.5"	0.010"	24 hr @ RT	10:1 by Volume
T-Peel (ASTM D1876 modified)	1.0"x3.0"	0.010"	24 hr @ RT	10:1 by Volume

Failure Mode Definition	Abbreviation
Adhesive Failure	A
Cohesive Failure	C
Thin Layer Cohesive Failure	TLC

\*Data is typical and not to be used for specification purposes.

## Bond Performance\* – LORD 852S Adhesive/LORD Accelerator 25GB

Substrates	Aluminum to Aluminum	EZG to EZG	CRS to CRS
Lap Shear @ Room Temperature, psi (MPa)	2880 (19.9)	2115 (14.6)	2975 (20.5)
Failure Mode	C	C	C
Lap Shear @ 180°F (82°C), psi (MPa)	1089 (7.5)	1090 (7.5)	1320 (9.1)
Failure Mode	C	C	C
Lap Shear @ -30°F (-34°C), psi (MPa)	3380 (23.3)	2627 (18.1)	4236 (29.2)
Failure Mode	TLC	TLC	TLC
Lap Shear after 14 days @ 95°F (38°C), 95% RH, psi (MPa)	2752 (19.0)	2016 (13.9)	2826 (19.5)
Failure Mode	C	C	C
Lap Shear after 500 hours Salt Spray Exposure, psi (MPa) ASTM B117	2022 (13.9)	1780 (12.3)	1807 (12.5)
Failure Mode	C/A	C/A	C/A
T-Peel @ Room Temperature, pli (N/cm)	26 (46)	47 (82)	49 (86)
Failure Mode	C	C	C

Substrate	Surface Treatment
Aluminum, 0.032" thick 6061T6	IPA Wipe
Electrogalvanized Steel (EZG), 0.032" thick	IPA Wipe
Cold Rolled Steel (CRS), 0.032" thick	IPA Wipe

Bonded Parameters	Bond Area	Film Thickness	Cure	Mix Ratio
Metal Lap Shears (ASTM D1002)	1.0"x0.5"	0.010"	24 hr @ RT	10:1 by Volume
T-Peel (ASTM D1876 modified)	1.0"x3.0"	0.010"	24 hr @ RT	10:1 by Volume

Failure Mode Definition	Abbreviation
Adhesive Failure	A
Cohesive Failure	C
Thin Layer Cohesive Failure	TLC

\*Data is typical and not to be used for specification purposes.

Parker Lord  
**Engineered Materials Group**  
 111 LORD Drive  
 Cary, NC 27511-7923  
 USA  
[www.parker.com/APS](http://www.parker.com/APS)

DS4596E OD 05/25 Rev.0

Information and specifications subject to change without notice and without liability therefor.  
 Trademarks used herein are the property of their respective owners.

© 2025 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.