

LORD® Signlok™ 403 Adhesive

Technical Data Sheet

LORD® Signlok™ 403 adhesive is a two-component adhesive system designed for bonding a wide variety of prepared or unprepared metals and engineered plastics.

LORD Signlok 403 adhesive can be used to replace welding, brazing, riveting and other mechanical fastening methods. This adhesive system is formulated to provide some of the highest impact and peel strengths available in a room temperature curing adhesive.

Features and Benefits:

Versatile – bonds a wide range of unprepared metals with minimal substrate preparation, as well as engineered thermoplastics including XENOY®, polycarbonate, ABS and acrylics.

Temperature Resistant – performs at temperatures from -40°F to +300°F (-40°C to +149°C).

Environmentally Resistant – resists dilute acids, alkalis, solvents, greases, oils, moisture, salt spray and weathering; provides excellent resistance to indirect UV exposure.

UL Recognized – UL 746C recognized.

Non-Sag – remains in position when applied on vertical or overhead surfaces, allowing for greater process flexibility.

Precise Bondline – allows precise control of the adhesive bondline thickness due to its content of glass beads.

Application:

Surface Preparation – Remove grease, loose contamination or poorly adhering oxides from metal surfaces. Normal amounts of mill oils and drawing compounds usually do not present a problem in adhesion. Most plastics require a simple cleaning before bonding. Some may require abrading for optimum performance.

Mixing – Mix adhesive with accelerator at a ratio of 2:1, adhesive to accelerator, by volume. Even color distribution visually indicates a thorough mix. Once mixed, the adhesive cures rapidly.

Handheld cartridges will automatically dispense the correct volumetric ratio of each component. Adhesive components should be leveled/purged prior to installation of mixing tip.

Applying – Apply mixed adhesive to bond surfaces using handheld cartridge or automatic meter/mix/dispense equipment. Contact your Parker Lord representative if assistance is needed using this equipment.

Curing – Cure begins immediately once adhesive and accelerator are mixed. Complete cure requires 24 hours at room temperature. Mating surfaces must be held in contact during the entire curing process. Cure rate can be accelerated by applying modest heat [$< 150^{\circ}\text{F}$ ($< 66^{\circ}\text{C}$)]. Cured adhesive is colored to visually indicate a full cure; cure color depends on the accelerator used.

Typical Properties*

	Adhesive (Part A)	Accelerator (Part B)
Appearance	Tan Paste	Off-white Paste
Density lb/gal (kg/m ³)	9.25 - 9.55 (1108 - 1144)	12.15 - 13.2 (1456 - 1581)
Flash Point, °F (°C)	59 (15)	≥200 (≥93)

*Data is typical and not to be used for specification purposes.

Cleanup – Clean equipment and tools prior to the adhesive cure with solvents such as isopropyl alcohol, acetone or methyl ethyl ketone (MEK). Once adhesive is cured, heat the adhesive to 400°F (204°C) or above to soften the adhesive. This allows the parts to be separated and the adhesive to be more easily removed.

Shelf Life/Storage:

Shelf life of each component is 18 months when stored in a well ventilated area below 80°F (27°C) in original, unopened container. Storage temperatures of 40-50°F (4-10°C) are recommended. If stored cold, allow product to return to room temperature before using. Protect from exposure to direct sunlight.

LORD Signlok 403 adhesive is flammable. Do not store or use near heat, sparks or open flame.

Cautionary Information:

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Typical Properties* of Adhesive Mixed with Accelerator	
Mix Ratio by Volume, Adhesive to Accelerator	2:1
Solids Content, %	100
Working Time, minutes @ 75°F (24°C)	2-4
Time to Handling Strength, minutes @ 75°F (24°C), 50 psi Shear	4-6
Full Cure Time, hours @ 75°F (24°C)	24**
Mixed Appearance	Tan Paste
Cured Appearance	Tan to Green

*Data is typical and not to be used for specification purposes.
**Reaches 90% of it full strength after 2 hours.

Typical Cured Properties*	
Lap Shear Strength, psi (MPa)	
Aluminum	2000 (13.79)
Steel	2300 (15.86)
Peel Strength, pli (N/mm)	20-23 (3.5-4.0)
Aluminum	

*Data is typical and not to be used for specification purposes.

Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.



Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275 5673
www.Parker.com/APS