

THERMOSET® HARDENER NO. 25

Technical Data Sheet

Thermoset® Hardener No. 25 is a curing agent designed for use with several LORD® and Thermoset epoxy resins to obtain a variety of handling and cured properties. Compositions using this hardener are moisture insensitive and cure to a high gloss.

Features and Benefits

Excellent Appearance: cures to a high gloss surface, free of "sweat-out"; exhibits good mar resistance.

Fast Cure: rapidly cures at room temperature (25°C).

Moisture Insensitive: cured properties obtained even when cured in high humidity conditions.

Application

Mixing: Refer to applicable epoxy resin data sheet for specific mixing instructions and mix ratios.

Applying: Refer to applicable epoxy resin data sheet for specific application instructions.

Curing: Refer to applicable epoxy resin data sheet for specific curing instructions. Cure rate is dependent on the mass and shape of the catalyzed resin, along with the ambient temperature and the presence of fillers.

Shelf Life/Storage

Shelf life is one year when stored in a well ventilated area at 25°C in original, unopened container.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Typical Properties*

Appearance	Amber Liquid
Viscosity, cP @ 25°C	5000
Specific Gravity	1.06

*Data is typical and not to be used for specification purposes.

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
phone +1 877 275-5673
www.parker.com/APS

DS3670 OD 10/24 Rev.1

Information and specifications subject to change without notice and without liability therefor.
Trademarks used herein are the property of their respective owners.

© 2024 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.