

THERM-A-GAP® CIP 35

Thermally Conductive Cure-in-Place Compound

Parker Chomerics THERM-A-GAP® CIP 35 is a thermally conductive silicone elastomer dispensable thermal interface material with a 2.5W/m-K thermal conductivity.

CIP 35 is designed to cool electronics without excessive compressive force in sensitive cooling applications.

This versatile liquid can be hand or robotically dispensed and then cured into complex geometries for cooling of multi-height components on a printed circuit board (PCB) without the expense of a molded sheet.

CIP 35 is available in ready-to-use cartridge systems, eliminating weighing, mixing, and degassing procedures.

This product has a thermal conductivity of 2.5 W/m-K and a hardness of 55 Shore A.



Product Features

- Dispensable cure-in-place gap filling, potting, sealing, and encapsulating
- Excellent blend of high thermal conductivity, flexibility, and ease of use
- Conformable to irregular shapes without excessive force on components
- Ready-to-use cartridge system eliminates weighing, mixing, and de-gassing steps
- Variety of kit sizes and configurations available to suit any application (handheld twin-barrel cartridges, SEMCO® tubes, and pneumatic applicators)
- Vibration damping
- Long shelf life, no settling or degradation of cure
- Sag resistance, maintains shape during cure



THERM-A-GAP® CIP 35 PRODUCT INFORMATION

	Typical Properties	CIP 35	Test Method
Physical	Color	Green	--
	Binder	Silicone	--
	Filler	Aluminum Oxide / Boron Nitride	---
	Number of Components	2 part	---
	Mix Ratio	1 : 1	---
	Specific Gravity	2.87	ASTM D792
	Hardness, Shore A	55	ASTM D2240
	Viscosity, poise	5000	Mod. ASTM D2196
	Pot Life, minutes	100	Time to 2X starting viscosity at 23°C
	Cure Cycles - for set up	30 min @ 150°C 180 min @ 100°C 48 hrs @ 23°C	Chomerics
Thermal	Thermal Conductivity, W/m-K	2.5	ASTM D5470
	Operating Temperature Range, °F (°C)	-67 to 392 (-55 to 200)	ASTM D5470
Electrical	Dielectric Strength, Kvac/mm (Vac/mil)	10 (250)	ASTM D149
	Volume Resistivity, ohm-cm	1.0 x 10 ¹⁴	ASTM D257
Regulatory	RoHS Compliant	Yes	Chomerics
	Outgassing, %TML [%CVM]	0.22 [0.06]	ASTM E595
	Flammability Rating (file E140244)	UL94-V0	UL 94
	Shelf Life	12 months	Chomerics

Mixpac® Dispensing Systems are available from multiple sources. When contacting Mixpac® equipment suppliers, reference cartridge volume (cc) and dual element cartridge A:B mix ratio. Refer to table for volume and mix ratio information.




Figure 1: Typical Applicator

THERM-A-GAP® CIP 35 ORDERING INFORMATION

Part Number	Typical Standard Fill Volume (cc)	Typical Standard Fill Mass (g)	Packaging Description
65-00-CIP35-0045	45 cc	128	1:1 dual component cartridge
65-00-CIP35-0200	200 cc	574	1:1 dual component cartridge
65-00-CIP35-0400	400 cc	1,148	1:1 dual component cartridge
65-00-CIP35-1200	1200cc	3,444	(2) 600cc SEMCO Cartridges
65-1P-CIP35-5000	5000cc	14,350	(2) 1 Gallon Pails, each pail has 8kg
65-5P-CIP35-10452	10,452cc	29,997	(2) 5 Gallon Pails, each pail has 25kg



We're Here to Help

Scan QR code or visit parker.com/chomerics to:

- [Request a Free Sample](#)
- [Talk to an Expert](#)
- [Get a Quote](#)
- [Find Where to Buy](#)

Parker Hannifin Corporation

Chomerics Division

77 Dragon Court

Woburn, MA 01801

Phone 781 935 4850

Fax 781 933 4318

chomailbox@parker.com

parker.com/chomerics

CHODS1120 August 2025

©2025 Parker Hannifin Corporation

