

Thermoset™ ME-588 BK Underfill Encapsulant

Description

LORD Thermoset™ ME-588 BK encapsulant is an anhydride-free, semiconductor grade epoxy underfill product developed for the encapsulation of densely populated area array flip chip devices. It is formulated with the necessary structural strength to handle over-molding processes.

Thermoset ME-588 BK encapsulant can be fast cured and is engineered to withstand 260°C peak reflow temperatures of lead-free solders.

Features and Benefits

Jettable – provides low viscosity for high speed jetting dispense.

Self-Filleting – provides surface tension and viscosity flow properties to achieve full coverage without producing bulky fillet on top of device.

Low Coefficient of Thermal Expansion – minimizes the possibility of cracking during temperature cycling (-40°C to +150°C); provides excellent thermal shock performance.

Rapid Flow – formulated to flow consistently without voids while maintaining a fast flow rate; can be used under small or large die with high-density interconnects and under devices with stand-off heights below 25 micron.

Good Adhesion – provides good adhesion to laminate, ceramic, solder mask and metal surfaces.

Device Reliability – provides high Tg and high fracture toughness, reducing the amount of thermally induced stress placed on the solder interconnects.

Typical Properties*

Uncured

Appearance	Black Liquid
Viscosity, cps @ 25°C	15,000
Specific Gravity	1.54
Gel Time, min @ 120°C	6
Working Life, hr @ 25°C	
20% viscosity increase	20
50% viscosity increase	50

Cured

Volume Resistivity, ohm-cm @ 25°C	$>1 \times 10^{13}$
Coefficient of Linear Thermal Expansion, ppm/°C	
alpha 1	44
alpha 2	100
Glass Transition Temperature (Tg), °C by TMA	148
Storage Modulus, MPa	5027
Dielectric Strength, V/mil	945

*Data is typical and not to be used for specification purposes.

LORD TECHNICAL DATA

Application

Applying – Before use with dispensing equipment, allow encapsulant to be warmed to room temperature (ideally 20-25°C). Thaw encapsulant by placing the syringe in a vertical (upright) position with dispense tip facing downward in an ambient environment. Consult handling instructions** for specific guidelines.

To decrease underfill time, preheat substrate to 100°C prior to encapsulant application.

Mount the syringe onto the dispensing equipment that has been thoroughly cleaned and purge encapsulant through the system until an unbroken flow of encapsulant is extruded. Dispense underfill encapsulant as a corner dot, line or L-shaped extrusion.

Curing – Allow material to cure for 7-20 minutes at 160-165°C. This time-at-temperature profile refers to the time the material should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay material actually reaching the target temperature.

Material can be cured at temperatures lower than 160°C with a longer duration.

Cleanup – Remove uncured encapsulant using common organic solvents such as acetone or isopropanol.

***Handling instructions are available on LORD.com.*

Values stated in this technical data sheet represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as LORD Corporation has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, LORD Corporation does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

Thermoset and "Ask Us How" are trademarks of LORD Corporation or one of its subsidiaries.

LORD provides valuable expertise in adhesives and coatings, vibration and motion control, and magnetically responsive technologies. Our people work in collaboration with our customers to help them increase the value of their products. Innovative and responsive in an ever-changing marketplace, we are focused on providing solutions for our customers worldwide ... Ask Us How.

LORD Corporation World Headquarters

111 Lord Drive
Cary, NC 27511-7923
USA

Customer Support Center (in United States & Canada)

+1 877 ASK LORD (275 5673)

www.lord.com

For a listing of our worldwide locations, visit LORD.com.

Shelf Life/Storage

Shelf life is six months from date of manufacture when stored at -40°C in original, unopened container. Syringe must be maintained at -40°C in a vertical (upright) position with the dispense tip facing down. Do not store syringe on its side (horizontally).

This material is shipped and stored frozen. Consult handling instructions** for thawing.

Cautionary Information

Before using this or any LORD product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.