

CoolTherm® SC-324 XLW Silicone Encapsulant

Handling/Application Notes – China only

CoolTherm® SC-324 XLW (eXtra Long Working life) silicone encapsulant is a two-component, thermally conductive system designed to provide excellent thermal conductivity for electrical encapsulating applications, while retaining desirable properties associated with silicones.

CoolTherm SC-324 XLW encapsulant offers a convenient 1:1, by weight or volume, mix ratio. It has a very low mixed viscosity for a filled encapsulating resin system. CoolTherm SC-324 XLW encapsulant retains excellent flexibility over a wide range of temperatures.

CoolTherm SC-324 XLW encapsulant is composed of an addition curing polydimethyl siloxane polymer that will not depolymerize when heated in confined spaces. As with all silicones, CoolTherm SC-324 XLW encapsulant generates no exotherm as it cures. It also exhibits low shrinkage and stress on components as it cures. CoolTherm SC-324 XLW encapsulant is designed to have long work life at high curing temperature. It can only be cured at elevated temperature.

Handling Recommendations:

The inherently low viscosity of CoolTherm SC-324 XLW encapsulant will lead to component stratification and filler settling during prolonged storage. It is important to thoroughly re-suspend the ingredients of each individual container prior to combination. This can be accomplished through manual or mechanical means.

Caution: Do not exceed 70°C during the mixing process.

Typical mechanical agitation would include:

- Single shaft dispersion utilizing a 4-inch dispersion blade. Scrape bottom of container with a clean, dry spatula until clumps of agglomerated filler are loosened. Blend thoroughly at 350-500 rpm until a homogeneous mixture is achieved.
- Turbulent agitation employing a common industrial paint shaker. Typically, six minutes on a standard 100 V industrial paint shaker with 3-axis mixing action is sufficient for thorough resuspension.

Deairing and Evacuation:

Unless a closed-chamber mechanical mixer is used, air may be introduced into the encapsulant system either during mixing or when catalyzing the mixture. Electrical properties of the silicone encapsulant are best when air bubbles and voids are minimized. Therefore, in extremely high voltage or other critical applications, vacuum may be appropriate.

Should vacuuming prove to be necessary for the application, the mixed silicone encapsulant should be deaired in a container large enough to allow for expansion from two to five times the original volume.

A vacuum of 2-20 mm Hg for five to ten minutes is generally adequate for small (one quart or less) batches. Larger batches may require longer vacuum time, lower pressures (<2 mm Hg), or introduction of the silicone encapsulant into the chamber in thin streams. Once the silicone encapsulant has been adequately deaired, the vacuum should be slowly released.

Cure Inhibition:

Avoid applying CoolTherm SC-324 XLW encapsulant to surfaces that contain cure inhibiting ingredients, such as amines, sulfur or tin salts. If bonding surface is in question, apply a test patch of CoolTherm SC-324 XLW encapsulant to the surface and allow it to set for the normal cure time.

Cleanup:

Disposable containers and utensils are recommended when working with silicones. However, when disposable materials are impractical, uncured silicone can be removed by cleaning equipment with solvent. Observe appropriate precautions when using flammable solvents. Solvent-cleaned utensils should be thoroughly dried before reuse; any remaining solvent can contaminate the next application.

Shelf Life/Storage:

Shelf life is six months for CoolTherm SC-324 resin and three months for CoolTherm SC-324 XLW hardener when stored at 5-30°C in original, unopened container. The material must be periodically rotated within its container to maintain maximum shelf life. Settling will occur if not mixed.

CoolTherm SC-324 XLW encapsulant evolves minute quantities of hydrogen gas. Do not repackage or store material in unvented containers. Adequately ventilate work area to prevent the accumulation of gas.

Cautionary Information:

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY: FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

©2023 Parker Hannifin - All Rights Reserved

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

OD TT3067E 12/23 Rev.0

Parker Lord
Engineered Materials Group
111 LORD Drive
Cary, NC 27511-7923
USA
www.Parker.com/APSChina

Parker Lord China
No.333, North Riyang Road,
China (Shanghai) Pilot Free Trade Zone, P.R.C.
Zipcode: 200131
Email: LORDChinaMarketing@parker.com
Phone: +86 21-3133 0800
Fax: +86 21-2042 2361

