

COOLTHERM® SC-6702 THERMALLY CONDUCTIVE SILICONE ENCAPSULANT

Technical Data Sheet

CoolTherm® SC-6702 thermally conductive silicone encapsulant is a two-component system designed to provide thermal conductivity for encapsulating sensitive electronic modules.

Features and Benefits

Convenient: easy to use 1:1 mix ratio, by weight or volume.

Primerless Adhesion: adheres without the use of a primer in most applications.

High Thermal Conductivity: provides thermal conductivity for applications where superior heat dissipation is required.

Broad Temperature Range: can be used on parts and devices that experience operating temperatures from -55°C to 260°C.

UL Rated: provides excellent flame retardancy; UL 94 V-0 certified.

Application

Mixing: Thoroughly mix each component prior to combining resin and hardener. Mix CoolTherm SC-6702 resin with CoolTherm SC-6702 hardener at a 1:1 ratio, by weight or volume. Automatic meter/mix/dispense equipment may be used for high volume production.

Unless a closed-chamber mechanical mixer is used, air may be introduced into the encapsulant system either during mixing or when catalyzing the mixture. Electrical properties of the silicone encapsulant are best when air bubbles and voids are minimized. Therefore, in extremely high voltage or other critical applications, vacuuming may be appropriate.

Applying: Apply silicone encapsulant using handheld cartridges or automatic meter/mix/dispense equipment.

Avoid applying CoolTherm SC-6702 encapsulant to surfaces that contain cure inhibiting ingredients, such as amines, sulfur, or butyl. If bonding surface is in question, apply a test patch of CoolTherm SC-6702 encapsulant to the surface and allow it to set for the normal cure time.

Curing: Allow encapsulant to cure for 16-24 hours at 85°C. This time-at-temperature profile refers to the time the material should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay material reaching the target temperature.

Shelf Life/Storage

Shelf life of each component is six months when stored at temperatures up to 40°C in original, unopened container.

Typical Properties*

	SC-6702 Resin	SC-6702 Hardener	Mixed
Appearance	Red Liquid	White Liquid	Red Liquid
Viscosity, cP @ 25°C	27,000	28,000	30,000
Specific Gravity	2.15	2.04	2.09
Gel Time, minutes @ 66°C	–	–	25
Working Life, hours @ 25°C	–	–	4

*Data is typical and not to be used for specification purposes.

Typical Cured Properties*

Thermal Conductivity, W/m·K Hot Disc Transient Method, ISO 22007-2	0.7
Coefficient of Linear Thermal Expansion, ppm/°C ASTM C 864	239
Hardness Shore A	65
Tensile Strength, MPa (psi) ASTM D 412	4.1 (600)
Elongation at Break, % ASTM D 412	80
Volume Resistivity, ohm-cm @ 25°C ASTM D 257	1.7 x 10 ¹⁵
Dielectric Strength, kV/mm (V/mil) ASTM D 149	17.1 (434)
Dielectric Constant @ 25°C 1 MHz, ASTM D 150	5.5
Dissipation Factor, % @ 25°C 1 MHz, ASTM D 150	0.014

**Data is typical and not to be used for specification purposes.

Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord
Engineered Materials Group
 111 LORD Drive
 Cary, NC 27511-7923
 USA
 phone +1 877 275-5673
www.parker.com/APS

DS3567 OD 08/25 Rev.4

Information and specifications subject to change without notice and without liability therefor.
 Trademarks used herein are the property of their respective owners.

© 2025 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.