

CHO-BOND® 1030

One Component Flexible Electrically Conductive Silicone Adhesive


CHO-BOND 1030 is a silver plated copper filled, one-component conductive silicone designed for applications where a flexible, strong, conductive electrical bond must be achieved. CHO-BOND 1030 greatly simplifies the problem of bonding conductive silicone EMI gaskets to metal substrates. It is formulated for relatively small bond lines, less than 0.010 inches (0.25mm), and should not be used as an EMI caulk where bond lines are greater than 0.010 inches (0.25 mm).

No volatile organic compounds (VOCs) and minimal shrinkage upon curing make CHO-BOND 1030 a good choice for a variety of commercial and military applications. CHO-BOND 1030's moisture cure silicone polymer system allows it to cure to the touch in 24hrs and provides a robust conductive bond over a wide range of application temperatures.

For best adhesion results, CHO-BOND 1030 should be used in conjunction with CHO-SHIELD 1086 primer. Typical applications include bonding, repair, and attachment of EMI gaskets, and sealing around EMI vents and windows.

Product Features

- One component
- Easy to use, no weighing or mixing required.
- Silver plated copper filler
- Good conductivity 0.050 ohm-cm.
- No VOCs
- Minimal shrinkage.
- Moisture cure silicone
- Flexible, 30 minute working life, rapid skin formation, > 200 psi lap shear strength, 24 hr handling time, wide range of application temperatures. 1 week for full cure.
- Non corrosive cure mechanism
- No corrosive by-products generated during curing to damage substrate.
- Medium paste
- Can be used on overhead or vertical surfaces.



CHO-BOND® 1030 Product Information

Typical Properties	CHO-BOND 1030	Test Method	
Polymer	Silicone	N/A	
Filler	Silver-Plated Copper	N/A	
Mix Ratio, A : B (by weight)	1-part	N/A	
Color	Light Gray	N/A	(Q)
Consistency	Medium Paste	N/A	(Q)
Maximum DC Volume Resistivity	0.050 ohm-cm	CHO-95-40-5555*	(Q/C)
Minimum Lap Shear Strength**	200 psi (1379 kPa)	CHO-95-40-5300*	(Q/C)
Minimum Peel Strength**	8.0 lb./inch (1401 N/m)	CHO-95-40-5302*	(Q/C)
Specific Gravity	3.8	ASTM D792	(Q/C)
Hardness	77 Shore A	ASTM-D2240	(Q/C)
Continuous Use Temperature	- 55°C to 200°C (-67 °F to 392 °F)	N/A	(Q)
Elevated Temperature Cure Cycle	None	N/A	
Room Temperature Cure	1 week***	N/A	(Q)
Working Life	0.5 hour	N/A	(Q)
Shelf Life, unopened	6 months @ 25°C (77°F)	N/A	(Q)
Minimum thickness recommended	N/A	N/A	
Maximum thickness recommended	0.010 in (0.25 mm)	N/A	
Volatile Organic Content (VOC)	0 g/l	Calculated	
Theoretical Coverage Area at 0.010" Thick per Pound (454 grams)	775 in² (5000 cm²)	N/A	
Theoretical Coverage - Length of an 1/8" Diameter Bead per Pound (454 grams)	50 feet (15.2 m)	N/A	

Notes: N/A – Not Applicable, (Q/C) - Qualification and Conformance Test, (Q) - Qualification Test

* This test Method is available from Parker Chomerics.

** Cure is sufficient for handling in 24 hours. Full specification properties are developed after 1 week (168 hours) at room temperature.

*** Chomerics' recommend minimum time to wait before applying paint over CHO-BOND 1019. Material will continue to cure after painting.

CHO-BOND® 1030 Ordering Information

Product	Weight (grams)	Packaging	Part Number	Primer Included
CHO-BOND 1030	113.4	1.5 fluid ounce aluminum foil tube	50-02-1030-0000	1086
CHO-BOND 1030	113.4	1.5 fluid ounce aluminum foil tube	50-02-1030-1000	No
CHO-BOND 1030	454	6 fluid ounce SEMCO cartridge	50-01-1030-0000	1086

Please refer to Parker Chomerics Surface Preparation and CHO-BOND Polythioether Application documents for information regarding the proper surface preparation, primer application (if required), and use of these compounds.



We're Here to Help

Scan QR code or visit parker.com/chomerics to:

- [Request a Free Sample](#)
- [Talk to an Expert](#)
- [Get a Quote](#)
- [Find Where to Buy](#)

Parker Hannifin Corporation

Chomerics Division

77 Dragon Court

Woburn, MA 01801

Phone 781 935 4850

Fax 781 933 4318

chomailbox@parker.com

parker.com/chomerics

CHODS1232 March 2026

©2026 Parker Hannifin Corporation

