

Turbine Series - 791000FV

FUEL




Specifications:

Height: 22.23" (56.47 cm)
Width: 21.44" (54.46 cm)
Depth: 7.96" (20.22 cm)
Weight: 32.8 lbs (14.9 kg)
Ports: 1 5/16"-12 UN-2B (SAE 1926-1)
 2X port Plugs Supplied
 2X 3/4" NPTF Adapters Supplied
Service Clearance (Top): 10.0" (25.4 cm)
Vacuum Installation Recommended
Maximum Head Pressure: 15 psi (1.03 bar)
Max Flow Rate: 540 gph (2044 lph)

Create a Part Number

Housing Type	Turbine Model - Triple 180/360/540 GPH Flow Rate		Accessory Options	12 VDC Heater (325 watt) 24 VDC Heater (325 watt)		Filtration Rating	10 micron
	791000FV			12	24		10

Dimensions:









MOUNTING HOLE PATTERN FOR 791000FV SCALE: NONE

ASSEMBLY	DESCRIPTION
791000FV10	791000 Triple Turbine Assy., 10 micron Filter
791000FV1210	791000 Triple Turbine Assy., 12VDC Heater, 10 micron Filter
791000FV2410	791000 Triple Turbine Assy., 24VDC Heater, 10 micron Filter



PARTS

Turbine - 791000FV Series



Part #	Description
1A	RK11-2076 T-handle/Lid Kit - Includes 1B, 1C & 1D
1B	T-handle O-ring - Included in 8A
1C	900FV/1000FV Lid
1D	Lid Gasket - Included in 8A

2A	2040V2	900FV Service Filter 2 micron - Includes 1B & 1D
	2040V2LL	900FV Service Filter 2 micron (Long Life) - Includes 1B & 1D
	2040V10	900FV Service Filter 10 micron - Includes 1B & 1D
	2040V30	900FV Service Filter 30 micron - Includes 1B & 1D
2B	2020V2	1000FV Service Filter 2 micron - Includes 1B & 1D
	2020V2LL	1000FV Service Filter 2 micron (Long Life) - Includes 1B & 1D
	2020V10	1000FV Service Filter 10 micron - Includes 1B & 1D
	2020V30	1000FV Service Filter 30 micron - Includes 1B & 1D

3	RK11-2092	Heater Kit - 12 vdc, 325 watt - Includes O-ring & Nut
	RK11-2093	Heater Kit - 24 vdc, 325 watt - Includes O-ring & Nut

4A	RK11-2077	Bracket Kit - Includes Bracket, Bolt, Washer, & Nut
4B	RK 11-1679	Feed-thru Plug - O-ring Included in 8A
4C	RK11-2078	Vacuum Gauge Port Plug
4D	RK11-2079	Valve Rebuild Kit

5A		Checkball and Gasket - Included in 5B & 8A
5B	RK11-2080	Centrifuge/Baffle/Checkball/Gasket Kit - Includes 6A Checkball and Gasket - Included in 8A

6A		Bowl Gasket - Included in 8A
6B	RK11-2081	Bowl Kit - Includes 6A, 6C, 6D, 6E & 6F
6C	RK 20126	Bowl Plug (O-ring Included in 8A)
6D		Self-venting Drain (Gasket Included in 8A)
6E		Bowl Ring
6F	RK 11542	Cap Screw Bowl Fasteners (set of 4)

7	RK11-2083	Mounting Bracket Kit - Includes Bracket & 4 bolts
---	-----------	--

Accessories and Parts Available - *Not Shown*

8A	RK 11-1952	Complete Seal Service Kit - 900FV/1000FV Series Filters
8B	RK11-2085	900FV/1000FV Port Plug & Adapter Kit
8C	RK19671	Stainless Steel T-handle with Vacuum Gauge
	RK19672	Vacuum Gauge (30" Hg) - 1/4" NPT back mount
	RK033092	Vacuum Gauge (30" Hg) - 1/4" NPT Remote mount
	RK 19667	Compound Gauge - pressure (15 PSI) and vacuum (30" Hg)
8D	RK 14329	Water Detection Module - 12 vdc
	RK 14321	Water Detection Module - 24 vdc
8E	RK30880E	WIF Sensor/Detection Kit - 1/2"-20 UNF
8F	RK11-1978	Checkball Spring Kit - For use with Primer Pump Kit 8G
8G	RKP1912-IM	Primer Pump Kit - 12 vdc - Adds 3.25" (8.26 cm) to Height
	RKP1924	Primer Pump Kit - 24 vdc - Adds 3.25" (8.26 cm) to Height