

# CHEMLOK® 205A PRIMER

## Technical Data Sheet

Chemlok® 205A primer is designed for use under Chemlok covercoat adhesives to bond a wide variety of vulcanized and unvulcanized rubber compounds to metals and other rigid substrates. Chemlok 205A, a modification of Chemlok 205 adhesive primer, is composed of a mixture of polymers, organic compounds and mineral fillers dissolved or dispersed in a predominately ketone solvent system.

Chemlok 205A primer is also an excellent one-coat adhesive for bonding some nitrile rubber compounds.

### Features and Benefits

**Versatile:** can be used as a primer under a wide variety of Chemlok covercoat adhesives such as the Chemlok 230 series and Chemlok 6100 series adhesives.

**Environmentally Recommended:** dilutable with aromatic solvents, reducing the number of solvents in plant inventory.

**Easy to Apply:** applies easily by brush, dip, spray or roller coat methods; suitable for existing production lines.

**Durable:** provides rubber tearing bonds and outstanding environmental resistance when used in combination with Chemlok covercoat adhesives.

**Convenient:** requires only a single coat application to bond some nitrile rubber compounds to rigid substrates during vulcanization.

### Application

**Surface Preparation:** Thoroughly clean metal surfaces prior to adhesive application. Remove protective oils, cutting oils and greases by solvent degreasing or alkaline cleaning. Remove rust, scale or oxide coatings by suitable chemical or mechanical cleaning methods.

Apply Chemlok 205A primer to stainless steel, aluminum, brass or other nonferrous substrates within one-half hour after cleaning. For ferrous substrates such as steel, a longer layover can be tolerated if no rust is formed.

For further detailed information on surface preparation of specific substrates, refer to Chemlok Adhesives application guide.

**Mixing:** Thoroughly stir primer before use, and agitate sufficiently during use to keep dispersed solids uniformly suspended. If dilution is needed, use ketone-type solvents such as MEK and MIBK or aromatic solvents such as toluene or xylene. Give careful attention to agitation since dilution will accelerate settling. Note proper dilution for the various application methods is best achieved by experience.

**Applying:** Apply primer by brush, dip, roll coat, spray or any method that gives a uniform coating and avoids excessive runs or tears.

Regardless of application method, the dry film thickness of Chemlok 205A primer should be 5.1-10.2 micron (0.2-0.4 mil).

### Typical Properties\*

|   |  |
|---|--|
| Appearance  | Gray Liquid                                  |
| Viscosity<br>cps @ 25°C (77°F)<br>Brookfield LVT<br>Spindle 2, 30 rpm | 85 - 165                                     |
| seconds<br>Zahn Cup #2  | 20 - 40                                      |
| Density<br>kg/m <sup>3</sup><br>(lb/gal)                              | 910.7 - 970.6<br>(7.6 - 8.1)                 |
| Solids Content by Weight, %   | 22 - 26                                      |
| Flash Point (Seta), °C (°F)   | 16 (61)                                      |
| Solvents  | MIBK, MEK, Propylene Glycol Monomethyl Ether |

\*Data is typical and not to be used for specification purposes.

**Drying/Curing:** Thoroughly dry coated parts before applying the covercoat adhesive. This will take approximately 30-60 minutes at room temperature. It is best to use temperatures of 65-93°C (150-200°F) and abundant circulating air; however, forced air drying is possible at temperatures up to 121°C (250°F) for short periods of time. Maximum air flow at minimum temperatures will give the best results.

**Cleanup:** Use MEK to clean primer before heat is applied. Remove cured primer by mechanical abrasion methods.

## Shelf Life/Storage

Shelf life is one year from date of shipment when stored by the recipient at 21-27°C (70-80°F) in original, unopened container.

## Cautionary Information

Before using this or any Parker Lord product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

Verify Volatile Organic Compounds (VOC) requirements with the applicable local, regional and state air quality authorities before importing, selling or using this product. VOC rules, thresholds and reporting obligations vary by jurisdiction; compliance is the responsibility of the importer/seller/owner.

*For industrial/commercial use only.* Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Parker Lord  
**Engineered Materials Group**  
111 LORD Drive  
Cary, NC 27511-7923  
USA  
phone +1 877 275-5673  
[www.parker.com/EPM](http://www.parker.com/EPM)

DS3174 OD 05/26 Rev.5

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

© 2026 Parker Hannifin Corporation



Values stated in this document represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker Lord has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker Lord does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

**WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.**

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.